




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.



LOC	DIST	REVISIONS					
HB	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
		G		CHANGE TE LOGO&DATE CODE	ECO-08-020482	11-SEP-08	HYS YBH



CONNECTION DIAGRAM (BOTTOM VIEW)



DRILLING DIAGRAM (BOTTOM VIEW)



- NOTES:
1. TERMINAL DIMENSIONS BEFORE SOLDER DIP
  2. LAST SUFFIX NON : WASHABLE TYPE
  3. LOT NO. SYSTEM AS FOLLOWING:




Diagram dimension	Tolerance
0.99mm max.	±0.1mm
1 - 2.99mm	±0.2mm
3mm min.	±0.3mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.SASAKI		Tyco Electronics Corporation ShenZhen,China
DIMENSIONS: mm		CHK	N.FUNAYAMA		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	A.NAGAI		NAME
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± ±		PRODUCT SPEC	-		PCH-L2MH CUSTOMER DRAWING
MATERIAL		APPLICATION SPEC	-		
FINISH		WEIGHT	-		SIZE
-		CUSTOMER DRAWING		A3	CAGE CODE
		SCALE 5:1		00779	DRAWING NO
		SHEET 1 OF 2		C-1461353	RESTRICTED TO
		REV H			


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HB	-			SEE SHEET 1	-	-	-

①	1461353-8	PCH-118L2M	107-79019 (TRAY)	108-79670	18V	PCH-118L2MH	h
②	1461353-7	PCH-105L2MH	107-79046 (TUBE) ③	108-79665	5V	PCH-105L2MH	g
	1461353-6	PCH-124L2MH	107-79019 (TRAY)	108-79669	24V	PCH-124L2MH	f
	1461353-5	PCH-112L2MH	107-79019 (TRAY)	108-79668	12V	PCH-112L2MH	e
	1461353-4	PCH-109L2MH	107-79019 (TRAY)	108-79667	9V	PCH-109L2MH	d
	1461353-3	PCH-106L2MH	107-79019 (TRAY)	108-79666	6V	PCH-106L2MH	c
	1461353-2	PCH-105L2MH	107-79019 (TRAY)	108-79665	5V	PCH-105L2MH	b
	1461353-1	PCH-103L2MH	107-79019 (TRAY)	108-79664	3V	PCH-103L2MH	a
	TE PART NO	TE TYPE NAME	PACKING SPECIFICATION	PRODUCT SPEC	PART B	PART A	TYPE

RELAY TYPE

		UV RESIN	UV SEAL(VENT HOLE)	16	
		EPOXY RESIN	SEAL	15	
CLASS E		UEW	MAGNETIC WIRE	14	
	SOLDER DIP	CP WIRE	COIL TERMINAL	13	
		Ag ALLOY	STATONARY CONTACT	12	
		Ag ALLOY	MOVABLE CONTACT	11	
		Cu ALLOY	HINGE SPRING	10	
	SOLDER DIP	Cu ALLOY	NO TERMINAL	9	
	SOLDER DIP	Cu ALLOY	MOVABLE SPRING	8	
UL 94V-0		PA NYLON	CARD	7	
UL 94V-0		PBT	CASE	6	
UL 94HB		PA NYLON	BOBBIN	5	
UL 94V-0		PBT	BASE	4	
		Ni PLATED	STEEL	CORE	3
		CuNi PLATED	STEEL	ARMATURE	2
		CuNi PLATED	STEEL	YOKE	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION	ITEM	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.SASAKI		 Tyco Electronics Corporation ShenZhen,China					
DIMENSIONS: mm		CHK	N.FUNAYAMA							
		APVD	A.NAGAI							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	-							
MATERIAL		FINISH	-		APPLICATION SPEC	NAME	PCH-L2MH CUSTOMER DRAWING			
-		FINISH	-		WEIGHT	-		RESTRICTED TO	-	
CUSTOMER DRAWING					SIZE	CAGE CODE	DRAWING NO	SCALE	SHEET	REV
					A3	00779	C=1461353	5:1	2 OF 2	H