

# Flat Cable EMI Suppression Cores (2643178651)



Part Number: 2643178651

43 FULL FLAT CABLE CORE

Explanation of Part Numbers:

- Digits 1 & 2 = Product Class
- Digits 3 & 4 = Material Grade

**Flat cable suppression core can accommodate multi- conductors flat cables, in widths from 12.7 mm (0.500) up to 77 mm (3.0). These flat cable cores are available in two ferrite material grades to reduce conducted EMI from 1 MHz to hundreds of MHz.**

Our Expanded Cable & Suppressor Kit (part number 0199000005) contains a selection of these flat cable cores and clips.

Flat Cable Cores are available in selected sizes in the Flex Circuit & Ribbon Cable Core Kit (part number 0199000038).

Assembly clips are available for most of the split flat cable cores. See section Flat Cable Cores Assembly clips.

[Catalog Drawing](#)

[3D Model](#)

Weight: 4.1 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	26.5	±0.40	1.043	_
B	21.5	±0.40	0.846	_
C	6	±0.30	0.236	_
D	6.6	±0.25	0.26	_
E	1.6	±0.25	0.063	_

Cable Information			
Max Diameter	Max Dimension	Solid Equivalent	Flat Cable Cores
0	21.10 x 1.35	_	-




Figure 4

**Chart Legend**


- + Test frequency
- For assembly clips see Flat Cable Cores Assembly Clips

Typical Impedance (Ω)	
10 MHz	10
25 MHz <sup>+</sup>	17
100 MHz <sup>+</sup>	34
250 MHz	54

Flat cable suppression cores, split or single cores, are controlled for impedances only. Minimum impedance values are specified for the + marked frequencies. The minimum impedance is listed on our catalog drawing.

[Catalog Drawing](#)

Centered, single turn impedance tests for the 31 and 43 material parts are performed on the E4990A Impedance Analyzer. All tests are made with the shortest practical wire length.



[CSV Download](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fair-Rite:](#)

[2643178651](#)