





Long Life Cermet Potentiometer 2 Million Cycles



FEATURES

- · 2 million cycles
- · Cermet element




RoHS


- 12.5 mm square single turn panel control
- 4, 6 and 6.35 shaft diameters and 29 terminal styles
- Multiple assemblies up to four modules
- Test according to CECC 41000 or IEC 60393-1
- Low temperature coefficient
- · Custom designs on request
- Linearity ± 3 % (± 2 % available)
- Material categorization: For definitions of compliance please see <u>www.vishay.com/doc?99912</u>

VERSATILE MODULAR COMPACT ROBUST


CONFIGURATION EXAMPLE - Dimensions in millimeters (inches) ± 0.5 mm (± 0.02")


Single module, single shaft, vertical mounting, PC pins with support plate, metric bushing and shaft





Dual modules, single shaft, PC pins with front support plates, imperial bushing and shaft







GENERAL SPECIFICATIONS

ELECTRICAL (initial)			
Resistive Element	Cermet		
Electrical Travel	270° ± 10°		
Standard Resistance Values	1 kΩ, 5 kΩ, 10 kΩ, 50 kΩ		
Standard	± 20 %		
Tolerance On Request	± 5 % or ± 10 %		
Taper	100 80 F A L W CLOCKWISE SHAFT ROTATION		
Circuit Diagram	$ \begin{array}{c} a \\ \bigcirc \\ (1) \\ b \\ \downarrow \\ \end{array} $ $ \begin{array}{c} c \\ \bigcirc \\ (3) \\ (3) $ $ \begin{array}{c} c \\ (3) \end{array} $ $ \begin{array}{c} c \\ (3) \end{array} $		
Linear Taper	0.1 W at + 70 °C		
Non-Linear Taper	0.05 W at + 70 °C		
Multiple Assemblies	0.1 W at + 70 °C per module		
Power Rating at 70 °C	0.10 P11L LINEAR TAPER 0 0 20 40 60 70 80 100 120 140 AMBIENT TEMPERATURE IN °C		
Temperature Coefficient (Typical)	± 150 ppm		
Limiting Element Voltage	350 V		
End Resistance (Typical) 2Ω			
Independent Linearity	± 3 % (± 2 % available)		
Insulation Resistance	10 ⁶ MΩ min.		
Dielectric Strength	1500 V _{RMS} min.		
Attenuation	-		
Mechanical Endurance	2 000 000 cycles		



MECHANICAL (initial)		
Mechanical Travel	300° ± 5°	
Operating Torque (Typical)		
Single and Dual Assemblies	0.4 Ncm to 1.7 Ncm max. (0.57 ozinch to 2.55 ozinch max.)	
Three to Four Modules (Per Module)	0.2 Ncm to 0.3 Ncm max. (0.28 ozinch to 0.42 ozinch max.)	
End Stop Torque		
4 mm Dia. Shafts	35 Ncm max. (2.9 lb-inch max.)	
6 mm and 1/4" Dia. Shafts	80 Ncm max. (6.8 lb-inch max.)	
Tightening Torque		
7 mm Dia. Bushings	150 Ncm max. (13 lb-inch max.)	
10 mm and 3/8" Dia. Bushings	250 Ncm max. (21 lb-inch max.)	
Weight	7 g to 9 g per module (0.25 oz. to 0.32 oz.)	

ENVIRONMENTAL		
Operating Temperature Range	- 55 °C to + 125 °C	
Climatic Category	55/125/56	
Sealing	IP64	

MARKING

• Potentiometer Module

Vishay logo, nominal ohmic value, and tolerance (code), identify P11L version, variation law, manufacturing date (four digits), "3" for the lead 3


Switch Module

Version, manufacturing date (four digits), "c" for common lead


PACKAGING


Box


PERFORMANCES				
TESTS	CONDITIONS	TYPICAL VALUES AND DRIFTS		
12313	CONDITIONS	$\Delta R_{T}/R_{T}$ (%)	$\Delta R_{1-2}/R_{1-2}$ (%)	OTHER
Electrical Endurance	1000 h at rated power 90'/30' - ambient temp. 70 °C	± 2 %	-	-
Climatic Sequence	Dry heat at + 125 °C/damp heat cold - 55 °C/damp heat, 5 cycles	± 1 %	-	-
Damp Heat, Steady State	+ 40 °C, 93 % relative humidity 56 days	± 2 %	-	Insulation resistance: > 1000 $M\Omega$
Change of Temperature	- 55 °C to + 125 °C, 5 cycles	± 0.2 %	-	-
Mechanical Endurance	2 million cycles turn angle: ± 60° temperature: 20 °C	± 20 %	-	Independent linearity: ± 10 %
Shock	50 g's, 11 ms 3 shocks - 3 directions	± 0.2 %	± 0.5 %	-
Vibration	10 Hz to 55 Hz 0.75 mm or 10 g's, 6 h	± 0.2 %	-	$\Delta V_{1-2}/V_{1-3} = \pm 0.5 \%$



STANDARD RESISTANCE ELEMENT DATA					
STANDARD	LINEAR	TAPER	NON-LINE	AR TAPER	
RESISTANCE VALUES	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	MAX. POWER AT 70 °C	MAX. WORKING VOLTAGE	
Ω	w	V	w	V	
1K	0.1	10.0	0.05	7.1	
5K	0.1	22.4	0.05	15.8	
10K	0.1	31.6	0.05	22.4	
50K	0.1	70.7	0.05	50.0	








BUSHINGS			mm (± 0.5)	mm (± 0.5)	INCHES (± 0.02)
	BUSHINGS		V	Q	F
Α	Shafts	Ø	6	4	1/4
В	Bushing	Ø	10	7	3/8
С		L	9.5	8	3/8
J	Lead versions X Y		7	5	0.278
	K		11.1	9.1	0.436
G	Panel		8.2	6.2	0.323
Н	Cutout	Ø	10.5	7.5	0.394
	Thread		0.75	0.75	32 thread/inch
	Wrench nut		12	10	0.500

Note

• Hardware supplied in separate bags




LOCATING PEGS (anti-rotation lug)

The locating peg is provided by a plate mounted on the bushing and positioned by the module sides. Four set positions are available, clock face orientation: 12, 3, 6, 9.


All P11 bushings have a double flat. When panel mounting holes have been punched accordingly, an anti-rotation lug is not necessary.

Locating peg code C not available for bushing Q.



CODE	Ø d (mm)	L (mm)	e (mm)
Α	2	6.2	0.7
В	2	7.75	0.7
С	3.5	13.5	1.1

Locating pegs are supplied in separate bags with nuts and washers



SHAFTS - Dimensions in millimeters (inches) **SPLINED SHAFT** The shaft length is always measured from the mounting face. Standard shafts are designed by a 3 letters code (3 digits). Shafts slots are aligned to $\pm 10^{\circ}$ of the wiper position. Bushing: Q All standard shafts are slotted except flatted and splined, see FHK Shaft: exeptions for bushing. 07 **FLATTED SHAFT** Ø6 Bushing: **GHF** Shaft: **CUSTOM SHAFTS** When special shafts are required - flat, threated ends, special shaft lengths, etc. a drawing is required. Ø 6.35

STANDARD COMBINATION OF SHAFT STYLES AND BUSHINGS							
SHAFT DIA.	BUSHING CODE	SHAFT LENGTH AND STYLE AVAILABLE IN STANDARD (others on request)					
6	V	FGS	FLS	FRS			
6.35	F	GGS	GHS	GJS	GLS	GOS	GHF
4	Q	EAS	EBS	EJS	FHK		



ORDERING INFORMATION (part number) Ρ 2 G 0 s 0 0 5 0 2 Κ Α RESISTANCE CODE/ NUMBER OF LOCATING **SHAFT** MODEL **BUSHING** SHAFT **LEADS** TOLERANCE/ **MODULES** PEG STYLE TAPER OR SPECIAL Available leads W00 X00 Y00 Z00 Z03 W10 X03 Y03 W20 X04 Z04 A13 Y04 A14 X10 Z10 A20 X13 Z13 A23 X14 Z14 A24 X20 Z20 Z23

	FIRST DIGIT				
Υ	Soldering lugs				
Х	PCB pins				
Z	PCB pins with front support plate				
Α	PCB pins with front and back support plates				
w	PCB pins - vertical mounting with 2 extra pins - 1 module only				

0	Y = 4.65 (0.183") A, X, Z, W = 5.08 (0.200") pin spacing pins section 0.9 x 0.3 (0.035" x 0.012")
1	2.54 (0.100") pin spacing pin section 0.6 x 0.3 (0.024" x 0.012")
2	5.08 (0.200") pin spacing pins section 0.6 x 0.3 (0.024" x 0.012")


SECOND DIGIT


THIRD DIGIT			
0	5.08 (0.200") space between modules		
3	7.62 (0.300") space between modules		
4	10.16 (0.400") space between modules		

Z24

X23

X24






SPECIAL CODES GIVEN BY VISHAY

Option available:


- Custom shaft
- Specific design on request
- · Specific linearity
- Multiple assemblies with various modules







P11L OPTION: ROTARY SWITCH MODULES



- Rotary switchs
- · Current up to 2 A
- Actuation CW or CCW position
- Sealing IP60

MODULES: RS ON/OFF SWITCH RSI CHANGEOVER SWITCH

The position of each module is free.

RS and RSI rotary switches are housed in a standard P11L module size 12.7 mm x 12.7 mm x 5.08 mm (0.5" x 0.5" x 0.2"). They have the same terminal styles as the assembled electrical modules.

An assembly can comprise 1 or more switch modules.

Switch actuation is described as seen from the shaft end.

D: Means actuation in maximum CCW position

F: Means actuation in maximum CW position

The switch actuation travel is 25° with a total mechanical travel of 300° \pm 5° and electrical travel of electrical modules is 238° \pm 10°.

Leads finish: Gold plated

RDS SINGLE POLE SWITCH, NORMALLY OPEN

In full CCW position, the contact between 1 and 3 is open. It is made at the beginning of the travel in CW direction.

RSF SINGLE POLE SWITCH, NORMALLY OPEN

In full CW position, the contact between 1 and 3 is open. It is made at the beginning of the travel in CCW direction.

RSID SINGLE POLE CHANGEOVER

In full CCW position, the contact is made between 3 and 2 and open between 3 and 1. Switch actuation (CW direction) reverses these positions.


RSIF SINGLE POLE CHANGEOVER

In full CW position, the contact is made between 1 and 2 and open between 1 and 3. Switch actuation (CCW direction) reverses these positions.

SWITCH SPE			
Switching Pov	Switching Power Maximum		
Switching Cur	rrent Maximum	0.1 A, 5 V =	
Maximum Cu	rrent Through Element	2 A	
Contact Resis	stance	100 mΩ	
Dielectric	Terminal to Terminal	1000 V _{RMS}	
Strength	Terminal to Bushing	2000 V _{RMS}	
Maximum Vol	tage Operation	5 V =	
Insulation Res	sistance Between Contacts	$10^6~{ m M}\Omega$	
Life at P _{max.}		100 000 actuations	
Minimal Trave	25°		
Operating Ter	mperature	- 40 °C to + 85 °C	

ELECTRICAL DIAGRAM

RSD	RSID	RSIF	
RSF	CCW POSITION	CW POSITION	





Note

(1) Common

ORDERING INFORMATION (First order only)

RSID

RSD SPST: Single pole, open switch in CCW position - 2 pins
RSF SPST: Single pole, open switch in CW position - 2 pins
RSID SPDT: Single pole, changeover switch in CCW position - 3 pins
RSIF SPDT: Single pole, changeover switch in CW position - 3 pins

P11L OPTION: DETENT MODULES

The detents mechanism is housed in a standard P11L module. Up to 21 detent positions available.

Count detents as follows: 1 for CCW position, 1 for full CW position, plus the other positions forming equal resistance increments (linear taper) - not equal angles.

Available: CVID - CVIF - CVIM

CV3 - CV11 - CV21

CVID CVIM CVIF CV11 $\alpha = \frac{270^{\circ}}{n-1}$ $\beta = \alpha + 15^{\circ}$

Mechanical endurance: 50 000 cycles

ORDERING INFORMATION (First order only for special code creation)

CV1M

CV1M 1 detent at half travel CV1D 1 detent at CCW position CV1F 1 detent at CW position

CV3 3 detents CV11 11 detents CV21 21 detents

P11L OPTION: NEUTRAL MODULES "EN"

Neutral or screen module is housed in a standard P11L module.

It is used as a screen between two electrical modules.


The leads can be connected to ground.

ORDERING INFORMATION (First order only for special code creation)

ΕN

EN Neutral module

P11L OPTION: SPECIAL LINEARITY - CONFORMITY



The independent linearity (conformity for the non-linear laws) is the maximum gap ΔV between the actual variation curve and the theorical variation curve the nearest to it. The linearity and the conformity are expressed in percentage of the total applied voltage E

linearity conformity =
$$\frac{\pm \Delta V_{max.}}{E}$$

They are measured over 90 % of actual electrical travel (centered).

On request linearity can be guaranteed in linear taper.

ORDERING INFORMATION (First order only)

J123

J123 Independent linearity ± 3 % (linear law)
J145 Independent linearity ± 2 % (linear law)

For other request, contact us.



е3

LEAD

(Pb)-FREE



P11L

MODEL

3

MODULES

BUSHING

Vishay Sfernice

T1927

SPECIAL

SPECIAL

EXAMPLES OF FIRST ORDER INFORMATION							
FIRST EXAMPLE: Triple module (switch is counted as a module)							
P 1 1 L 3	V A F G	S Y 0	0				
MODEL 3 MODULES BUS	SHING V LOCATING PEG	STANDARD SHAFT 16 mm FMS SLOTTED	SOLDER LUGS	SPECIAL TO BE DEFINED BY VISHAY			
ORDERING INFORMATION:							
PART NUMBER	P11L3VAFGSY00]				
SHAFT AND BUSHING	See drawing of special shaft attached]				
MODULE NO. 1	503 M A						
MODULE NO. 2	103 M A J1	23					
MODULE NO. 3	503 M A						
PART NUMBER DESCRIPTION (used on some Vishay document or label, for information only)							

FG

SHAFT

s

SHAFT

STYLE

Y00

LEADS

VALUE

TOL.

TAPER

Α

LOCATING

PEG



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000