

RF/Microwave Capacitors

RF/Microwave C0G (NP0) Capacitors

Ultra Low ESR "U" Series, C0G (NP0) Capacitors (RoHS)


Automotive, AEC Q200 Qualified



GENERAL INFORMATION


Automotive "U" Series capacitors are C0G (NP0) chip capacitors specially designed for "Ultra" low ESR for applications in the automotive market. Max ESR and effective capacitance are met on each value producing lot to lot uniformity. Sizes available are EIA chip sizes 0402 and 0603.

DIMENSIONS: inches (millimeters)



	inches (mm)				
Size	A	B	C	D	E
0402	0.039±0.004 (1.00±0.1)	0.020±0.004 (0.50±0.1)	0.024 max (0.6)	N/A	N/A
0603	0.060±0.010 (1.52±0.25)	0.030±0.010 (0.76±0.25)	0.036 max (0.91)	0.010±0.005 (0.25±0.13)	0.030 min (0.76)

HOW TO ORDER



ELECTRICAL CHARACTERISTICS

Capacitance Values and Tolerances:

Size 0402 - 0.2 pF to 22 pF @ 1 MHz

Size 0603 - 1.0 pF to 100 pF @ 1 MHz

Temperature Coefficient of Capacitance (TC):

0±30 ppm/°C (-55° to +125°C)

Insulation Resistance (IR):

10¹² Ω min. @ 25°C and rated WVDC

10¹¹ Ω min. @ 125°C and rated WVDC

Working Voltage (WVDC):

Size Working Voltage

0402 - 100, 50, 25 WVDC

0603 - 200, 100, 50 WVDC

Dielectric Working Voltage (DWV):

250% of rated WVDC

Equivalent Series Resistance Typical (ESR):

0402 - See Performance Curve, page 303

0603 - See Performance Curve, page 303

Automotive Specifications

Meets or exceeds the requirements of AEC Q200



LEAD-FREE
LEAD-FREE COMPATIBLE
COMPONENT



RF/Microwave Capacitors

RF/Microwave C0G (NP0) Capacitors

Ultra Low ESR "U" Series, C0G (NP0) Capacitors (RoHS)

Automotive, AEC Q200 Qualified



CAPACITANCE RANGE

Cap (pF)	Available Tolerance	Size 0402	Size 0603
0.2	B,C	50V	N/A
0.3			
0.4			
0.5	B,C		
0.6	B,C,D		
0.7			
0.8	B,C,D		
0.9			


Cap (pF)	Available Tolerance	Size 0402	Size 0603
1.0	B,C,D	50V	200V
1.1			
1.2			
1.3			
1.4			
1.5			
1.6			
1.7			
1.8			
1.9			
2.0			
2.1			
2.2			
2.4			
2.7			
3.0			
3.3			
3.6			
3.9			
4.3			
4.7			
5.1			
5.6			
6.2	B,C,D		
6.8	B,C,J,K,M		

Cap (pF)	Available Tolerance	Size 0402	Size 0603
7.5	B,C,J,K,M	50V	200V
8.2			
9.1	B,C,J,K,M		
10	FG,J,K,M		
11			
12			
13			
15			
18			
20			200V
22			100V
24			
27			
30		50V	
33		N/A	
36			
39			
43			
47			
51			
56			
68			
75			
82			
91			


Cap (pF)	Available Tolerance	Size 0402	Size 0603
100	FG,J,K,M	N/A	100V
110			50V
120			50V
130			N/A
140			
150			
160			
180			
200			
220			
270			
300			
330			
360			
390			
430			
470			
510			
560			
620			
680			
750			
820			
910			
1000	FG,J,K,M		

ULTRA LOW ESR, "U" SERIES


TYPICAL ESR vs. FREQUENCY
0402 "U" SERIES



TYPICAL ESR vs. FREQUENCY
0603 "U" SERIES



TYPICAL
SERIES RESONANT FREQUENCY
"U" SERIES CHIP



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

KYOCERA AVX:

[04025U100F4T2A](#) [04025U5R6B4T2A](#) [06032U2R7B4T2A](#) [06032U3R9B4T2A](#) [06035U100F4T2A](#) [04025U8R2C4T2A](#)
[04025U220F4T2A](#) [04025U3R0B4T4A](#) [04025U240F4T2A](#) [04025U2R7B4T2A](#) [04025U1R5C4T2A](#)
[04025U3R9C4T2A](#) [04025U4R7B4T2A](#) [04025U4R7C4T2A](#) [04025U7R5B4T2A](#) [04025U8R2B4T2A](#) [04025U3R3C4T2A](#)
[04025U0R7C4T2A](#) [04025U6R8C4T2A](#) [04025U3R6C4T2A](#) [04025U3R9B4T4A](#) [04025U1R2C4T2A](#)
[04025U3R9B4T2A](#) [04025U4R1C4T2A](#) [04025U8R0B4T2A](#) [04025U8R4C4T2A](#) [04025U5R0B4T2A](#) [04025U2R2B4T2A](#)
[04025U7R0C4T2A](#) [04025U160F4T2A](#) [04025U150F4T2A](#) [04025U8R0C4T2A](#) [04025U100G4T2A](#) [04025U300J4T2A](#)
[04025U7R0B4T2A](#) [04025U3R0B4T2A](#) [04025U6R6C4T2A](#) [04025U9R1C4T2A](#) [04025U1R0C4T2A](#)
[04025U110F4T2A](#) [04025U0R5C4T2A](#) [04025U6R0D4T2A](#) [04025U6R8B4T2A](#) [04025U5R0C4T2A](#) [04025U9R1B4T2A](#)
[04025U120G4T2A](#) [04025U270F4T2A](#) [04025U1R8C4T2A](#) [04025U3R3B4T2A](#) [04025U120F4T2A](#) [04023U130F4T2A](#)
[04025U300F4T2A](#) [04025U130F4T2A](#) [06031U101J4T2A](#)