

## Within Series Adaptor 32\_BNC-75-0-1/133\_N

### Description

Adaptor plug/plug  
BNC plug (male) / BNC plug (male)

Interface standard  
Series BNC - Compatible with IEC 61169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance 75 Ω  
Interface frequency max. 1 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0188 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS) compliant

#### Material Data

Interface - BNC plug (male)

| Piece Parts    | Material   | Surface Plating                   |
|----------------|------------|-----------------------------------|
| Centre contact | Brass      | Gold Plating (Nickel underplated) |
| Outer contact  | Brass      | SUCOPLATE (R) Plating             |
| Body           | Brass      | SUCOPLATE (R) Plating             |
| Insulator      | PFA / PTFE |                                   |
| Coupling nut   | Brass      | SUCOPLATE (R) Plating             |

Interface - BNC plug (male)

| Piece Parts    | Material   | Surface Plating                   |
|----------------|------------|-----------------------------------|
| Centre contact | Brass      | Gold Plating (Nickel underplated) |
| Outer contact  | Brass      | SUCOPLATE (R) Plating             |
| Body           | Brass      | SUCOPLATE (R) Plating             |
| Insulator      | PFA / PTFE |                                   |
| Coupling nut   | Brass      | SUCOPLATE (R) Plating             |

### Related Documents

Catalogue drawing DCA-00013766

### Ordering Information

Single package 32\_BNC-75-0-1/133\_NE