


STMPS2141, STMPS2151, STMPS2161, STMPS2171

Enhanced single channel power switches

Datasheet - production data



Features

- 90 mW high-side MOSFET switch
- 500/1000 mA continuous current
- Thermal and short-circuit protection with overcurrent logic output
- Operating range from 2.7 to 5.5 V
- CMOS and TTL compatible enable input
- Undervoltage lockout (UVLO)
- 12 μA maximum standby supply current
- Ambient temperature range, -40 to 85 °C
- ESD protection: 8 kV HBM
- Reverse current protection
- Fault blanking
- UL recognized components (UL file number: E354278)

Description

The STMPS2141, STMPS2151, STMPS2161, STMPS2171 power distribution switches are intended for applications where heavy capacitive loads and short-circuits are likely to be encountered. These devices incorporate 90 mW N-channel MOSFET high-side power switches for power distribution. These switches are controlled by a logic enable input.

When the output load exceeds the current limit threshold or a short is present, the device limits the output current to a safe level by switching into a constant current mode. When continuous heavy overloads and short-circuits increase the power dissipation in the switch, causing the junction temperature to rise, a thermal protection circuit shuts the switch off to prevent damage. Recovery from a thermal shutdown is automatic once the device has cooled sufficiently. Internal circuitry ensures the switch remains off until a valid input voltage is present.

Table 1. Device summary

	Order codes		Rated continuous output current	Enable
SO-8	SOT23-5L	MSOP8 ⁽¹⁾	(mA)	Ellable
STMPS2141MTR	STMPS2141STR	STMPS2141TTR	500	Active low
STMPS2151MTR	STMPS2151STR	STMPS2151TTR	500	Active high
STMPS2161MTR	STMPS2161STR	STMPS2161TTR	1000	Active low
STMPS2171MTR	STMPS2171STR	STMPS2171TTR	1000	Active high

^{1.} MSOP8 package is also known as "TSSOP8".

February 2022 DocID013793 Rev 7 1/39

Contents

1	Bloc	k diagr	am	7
2	Pin	settings	·	8
	2.1	Pin co	nnections	8
	2.2	Pin de	scription	8
3	Fund	ctional	description	9
	3.1	Fault b	olanking	9
	3.2	Overc	urrent/overtemperature protection	9
	3.3	Fault o	conditions	9
	3.4	Revers	sed current blocking	10
	3.5			
4	Amb	ient ter	mperature	11
5	Max	imum ra	atings	12
	5.1	Absolu	ute maximum ratings	12
	5.2	Recon	nmended operating conditions	12
6	Elec	trical sp	pecifications	13
7	Deta	il devic	e characteristics	17
	7.1	STMP	S2141, STMPS2151 additional electrical charts	17
		7.1.1	Turn-on/off characteristics at V _{OUT} = 5.0 V	17
		7.1.2	Turn-on/off characteristics at V _{OUT} = 3.0 V	
		7.1.3	UVLO	19
		7.1.4	OC protection characteristics	19
		7.1.5	Other electrical characteristics	20
	7.2	STMP	S2161, STMPS2171 electrical charts	23
		7.2.1	Turn-on/off characteristics at V _{OUT} = 5.0 V	23
		7.2.2	Turn-on/off characteristics at V _{OUT} = 3.0 V	24
		7.2.3	UVLO	25
		7.2.4	OC protection characteristics	25
		7.2.5	Other electrical characteristics	26

SIMPS	52141, STMPS2151, STMPS2161, STMPS2171	Contents
8	Package mechanical data	29
9	Ordering information	37
10	Revision history	38



List of tables

Table 1.	Device summary	1
Table 2.	Pin description	7
Table 3.	Fault conditions	8
Table 4.	SOT23-5L (191 °C/W)	. 10
Table 5.	MSOP8 (220 °C/W)	. 10
Table 6.	SO-8 (160 °C/W)	. 10
Table 7.	Absolute maximum ratings	. 11
Table 8.	Recommended operating conditions	. 11
Table 9.	SOT-23-5L electrical characteristics	. 12
Table 10.	MSO8P/SO-8 electrical characteristics	. 12
Table 11.	Current limit characteristics	
	$(V_{IN} = 5.5 \text{ V}, I_{OUT} = \text{rated current}, T_J = 25 ^{\circ}\text{C}, \text{ unless otherwise specified}) \dots$. 13
Table 12.	Supply current characteristics	
	$(V_{IN} = 5.5 \text{ V}, I_{OUT} = \text{rated current}, T_J = 25 ^{\circ}\text{C}, \text{ unless otherwise specified}) \dots$. 13
Table 13.	Thermal characteristics	
	$(V_{IN} = 5.5 \text{ V}, I_{OUT} = \text{rated current}, T_J = 25 ^{\circ}\text{C}, \text{ unless otherwise specified}) \dots$. 14
Table 14.	UVLO characteristics	
	$(V_{IN} = 5.5 \text{ V}, I_{OUT} = \text{rated current}, T_J = 25 ^{\circ}\text{C}, \text{ unless otherwise specified}) \dots$. 14
Table 15.	FAULT pin characteristics	
	$(V_{IN} = 5.5 \text{ V}, I_{OUT} = \text{rated current}, T_J = 25 \text{ °C}, \text{ unless otherwise specified}) \dots$. 14
Table 16.	EN pin characteristics	
	$(V_{IN} = 5.5 \text{ V}, I_{OUT} = \text{rated current}, T_J = 25 \text{ °C}, \text{ unless otherwise specified}) \dots$	
Table 17.	SOT23-5L package mechanical data	
Table 18.	SOT23-5L footprint dimensions	
Table 19.	SO-8 mechanical data	
Table 20.	MSOP8 package mechanical data	
Table 21.	Reel mechanical data	
Table 22.	Order codes	
Table 23.	Document revision history	. 37



List of figures

Figure 1.	Block diagram	
Figure 2.	SOT23-5L, SO-8 and MSOP8 pin connections	
Figure 3.	Voltage output turn-on delay time (STMPS2141/2151, 5 V)	
Figure 4.	Voltage output turn-off delay time (STMPS2141/2151, 5 V)	
Figure 5.	Current output turn-on delay time (STMPS2141/2151, 5 V)	
Figure 6.	Current output turn-off delay time (STMPS2141/2151, 5 V)	
Figure 7.	Voltage output turn-on delay time (STMPS2141/2151, 3 V)	
Figure 8.	Voltage output turn-off delay time (STMPS2141/2151, 3 V)	
Figure 9.	Current output turn-on delay time (STMPS2141/2151, 3 V)	
Figure 10.	Current output turn-off delay time (STMPS2141/2151, 3 V)	
Figure 11.	UVLO rising (STMPS2141/2151)	
Figure 12.	UVLO falling (STMPS2141/2151)	
Figure 13.	OC protection at V _{OUT} = 3.0 V (STMPS2141/2151)	
Figure 14.	OC protection at V _{OUT} = 3.0 V (STMPS2141/2151 - details)	
Figure 17.	I _{CC} vs. V _{IN} (enabled) (STMPS2141/2151)	
Figure 18.	I _{CC} vs. temperature (enabled) (STMPS2141/2151)	
Figure 15.	OC protection at V _{OUT} = 5.0 V (STMPS2141/2151)	20
Figure 16.	OC protection at V _{OUT} = 5.0 V (STMPS2141/2151 - details)	
Figure 19.	I _{CC} vs. V _{IN} (disabled) (STMPS2141/2151)	
Figure 20.	I _{CC} vs. temperature (disabled) (STMPS2141/2151)	
Figure 21.	R _{ON} vs. V _{IN} (STMPS2141/2151)	
Figure 22.	R _{ON} vs. temperature (STMPS2141/2151)	
Figure 23.	I _{OS} vs. temperature (STMPS2141/2151)	
Figure 24.	Switch leakage vs. temperature (STMPS2141/2151)	
Figure 25.	Output rise time vs. V _{IN} (STMPS2141/2151)	
Figure 26.	Output fall time vs. V _{IN} (STMPS2141/2151)	
Figure 27.	UVLO vs. temperature (STMPS2141/2151)	
Figure 28.	Voltage output turn-on delay time (STMPS2161/2171, 5 V)	
Figure 29.	Voltage output turn-off delay time (STMPS2161/2171, 5 V)	
Figure 30.	Current output turn-on delay time (STMPS2161/2171, 5 V)	
Figure 31.	Current output turn-off delay time (STMPS2161/2171, 5 V)	
Figure 32.	Voltage output turn-on delay time (STMPS2161/2171, 3 V)	
Figure 33.	Voltage output turn-off delay time (STMPS2161/2171, 3 V)	
Figure 34.	Current output turn-on delay time (STMPS2161/2171, 3 V)	
Figure 35.	Current output turn-off delay time (STMPS2161/2171, 3 V)	
Figure 36.	UVLO rising (STMPS2161/2171)	
Figure 37.	UVLO falling (STMPS2161/2171)	
Figure 38.	OC protection at V _{OUT} = 3.0 V (STMPS2161/2171)	
Figure 39.	OC protection at V _{OUT} = 3.0 V (STMPS2161/2171- detail)	
Figure 42.	I _{CC} vs. V _{IN} (enabled) (STMPS2161/2171)	
Figure 43.	I _{CC} vs. temperature (enabled) (STMPS2161/2171)	26
Figure 40.	OC protection at V _{OUT} = 5.0 V (STMPS2161/2171)	
Figure 41.	OC protection at V _{OUT} = 5.0 V (STMPS2161/2171- detail)	
Figure 44.	I _{CC} vs. V _{IN} (disabled) (STMPS2161/2171)	
Figure 45.	I _{CC} vs. temperature (disabled) (STMPS2161/2171)	
Figure 46.	R _{ON} vs. V _{IN} (STMPS2161/2171)	27
Figure 47.	R _{ON} vs. temperature (STMPS2161/2171)	2/
Figure 48.	I _{OS} vs. temperature (STMPS2161/2171)	



STMPS2141, STMPS2151, STMPS2161, STMPS2171

Figure 49.	Switch leakage vs. temperature (STMPS2161/2171)	27
Figure 50.	Output rise time vs. V _{IN} (STMPS2161/2171)	27
Figure 51.	Output fall time vs. V _{IN} (STMPS2161/2171	27
Figure 52.	UVLO vs. temperature (STMPS2161/2171)	28
Figure 53.	SOT23-5L package outline	29
Figure 54.	SOT23-5L footprint recommendations	30
Figure 55.	SOT23-5L carrier tape	31
Figure 56.	SO-8 package outline	32
Figure 57.	SO-8 carrier tape	33
Figure 58.	MSOP8 package outline	34
Figure 59.	MSOP8 carrier tape	34
Figure 60.	Reel information	36



Block diagram 1

 v_{OUT} V_{IN} Current sense ΕN Driver UVLO **FAULT** Thermal Fault blanking/reporting driver control unit sense AM14648

Figure 1. Block diagram

Pin settings 2

Pin connections 2.1

Figure 2. SOT23-5L, SO-8 and MSOP8 pin connections OUT [IN GND [2 FAULT [] EN SOT23-5L GND [OUT 2 OUT OUT 3 6 ∃ FAULT SO-8 / MSOP8

Pin description 2.2

Table 2. Pin description

143.5 21 111 4555					
Pin number			Name	Function	
SO-8	MSOP8	SOT23-5L	Name	Function	
1	1	2	GND	Ground	
2	2	5	IN	2.7 - 5.5 V input	
3	3	-	IN	2.7 - 5.5 V input	
4	4	4	EN	Enable for power switch	
5	5	3	FAULT	Open drain FAULT indicator, active low	
6	6	1	OUT	Output of power switch	
7	7	-	OUT	Output of power switch	
8	8	-	OUT	Output of power switch	

3 Functional description

3.1 Fault blanking

The STMPS devices feature a 10 ms fault blanking. Fault blanking allows current limit faults, including momentary short-circuit faults that occur when hot-swapping a capacitive load, and also ensures that no fault is issued during power-up. When a load transient causes the device to enter current limit, an internal counter starts. If the load fault persists beyond the 10 ms fault blanking timeout, the FAULT output asserts "low". Load transient faults less than 10 ms (typ.) do not cause a FAULT output assertion. Only current limit faults are blanked. Die overtemperature faults and input voltage drops below the UVLO threshold cause an immediate fault output.

3.2 Overcurrent/overtemperature protection

In overcurrent or short-circuit condition, the switch limits the current at a value of about 120% of the rated current. If the temperature of the die goes above the limit value, the switch turns off.

3.3 Fault conditions

In power switch applications, 4 types of fault conditions are common. These fault conditions and the response of the STMPS21x1 power switches are described in *Table 3*.

Fault Condition STMPS21x1 action Output shorted to GND via resistance Reduces output voltage to reduce the Short-circuit path of $< 1 \Omega$, causing a rapid current current. Asserts FAULT pin after surge. a blanking period Reduces output voltage to reduce the Output connected to a load that sinks Overcurrent current. Asserts FAULT pin after current above threshold. a blanking period. Turn OFF output until temperature falls Temperature of junction exceeds 135 °C Overheating below 125 °C. Asserts FAULT pin due to any reason. immediately. Turn OFF output until input voltage rises Input voltage drops below the UVLO above the UVLO threshold plus Undervoltage threshold. hysteresis. Asserts FAULT pin immediately.

Table 3. Fault conditions

3.4 Reversed current blocking

When the switch is OFF (disabled through the EN pin), or when the STMPS device is unpowered ($V_{IN} = 0 \text{ V}$) the switch behaves as an Hi-Z at the output pin, ensuring that no reverse current will flow into the device when $V_{IN} < V_{OUT}$.

Note:

In the case where the switch is ON, and a voltage higher than V_{IN} is applied to the OUT pin, a reverse current occurs. This operating condition is not allowed.

3.5 UVLO

When the input voltage drops below critical values, the power switch turns off to prevent improper operation due to low voltage.



4 Ambient temperature

In "Enable" operating mode, an amount of power is dissipated as heat in the power switch due to the on-resistance. The power dissipation is: $P = I^2R$.

Table 4. SOT23-5L (191 °C/W)

Part number	Max. current	Max. R _{ON} at 5 V	Power dissipation	Temperature difference (junction - ambient)	Maximum ambient temperature (at junction temperature 125 °C)	
STMPS2141	0.50 A	135 mΩ	33.8 mW	6.5	118.5	
STMPS2151			00.0 111	0.5	110.5	
STMPS2161	1.00 A	135 mΩ	135.0 mW	25.8	99.2	
STMPS2171	1.00 A	133 11122	133.0 11100	23.0	33.2	

Table 5. MSOP8 (220 °C/W)

Part number	Max. current	Max. R _{ON} at 5 V	Power dissipation	Temperature difference (junction - ambient)	Maximum ambient temperature (at junction temperature 125 °C)
STMPS2141	0.50 A	140 mΩ	35.0 mW	7.7	117.3
STMPS2151		140 11122	33.0 mv	7.1	117.5
STMPS2161	1.00 A	140 mΩ	140.0 mW	30.8	94.2
STMPS2171	1.00 A	140 11122	140.0 11100	30.0	34.2

Table 6. SO-8 (160 °C/W)

Part number	Max. current	Max. R _{ON} at 5 V	Power dissipation	Temperature difference (junction - ambient)	Maximum ambient temperature (at junction temperature 125 °C)
STMPS2141	0.50 A	140 mΩ	35.0 mW	5.6	119.4
STMPS2151 0.50 A		140 11152	33.0 mv	3.0	115.4
STMPS2161	1.00 A	140 mΩ	140.0 mW	22.4	102.6
STMPS2171	1.00 A	140 11152	140.011100	22.4	102.0

5 Maximum ratings

Stressing the device above the rating listed in *Table 7: Absolute maximum ratings* may cause permanent damage to the device. These are stress ratings only and operation of the device at these or any other conditions above those indicated in *Section 5.2:**Recommended operating conditions of this specification is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

5.1 Absolute maximum ratings

Table 7. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V _{IN}	Input voltage range	-0.3 - 6.0	V
V _{OUT}	Output voltage range	$-0.3 - (V_{IN} + 0.3)$	V
V _{IENX}	EN Input voltage range	-0.3 – 6.0	V
I _{OUT}	Continuous output current	Internally limited	-
ESD	ESD protection level (HBM)	8	kV
TJ	Junction operating temperature	-40 to 125	°C
T _{STG}	Storage temperature	-55 to 150	°C
T _R	Thermal resistance (MSOP8)	220	°C/W
T _R	Thermal resistance (SOT23-5L)	191	°C/W
T _R	Thermal resistance (SO-8)	160	°C/W

5.2 Recommended operating conditions

Table 8. Recommended operating conditions

Symbol	Parameter		Unit		
Symbol	Farameter	Min.	Тур.	Max.	Offic
V _{IN}	Input voltage	2.7	5.0	5.5	V
V _{OUT}	Output voltage	0	5.0	5.5	V
I _{OUT} (STMPS2141 STMPS2151)	Continuous output current	0	-	500	mA
I _{OUT} (STMPS2161 STMPS2171)	Continuous output current	0	-	1000	mA

DocID013793 Rev 7

12/39

6 Electrical specifications

Table 9. SOT-23-5L electrical characteristics

Symbol	Parameter	Test condition		Value		- Unit
Symbol	Farameter	rest condition	Min.	,,		Oilit
	Static drain source ON state resistance	$V_{IN} = 2.7 \text{ V}; T_J = 25 \text{ °C};$	-	120	160	mΩ
R _{ON}	SOT23-5L package load = 500 mA (STMPS2141/ STMPS2151)	V _{IN} = 5.0 V; T _J = 25 °C;	-	90	110	mΩ
	load = 1000 mA (STMPS2161/ STMPS2171)					
R _{ON}	Static drain source ON state resistance	V _{IN} = 2.7 V; -40 < T _J < 125 °C	-	-	200	mΩ
TON		V _{IN} = 5.0 V; -40 < T _J < 125 °C		-	135	11122
t _r	Output rise time	V_{IN} = 5.0 V R_L = 10 Ω C_L = 1 μF	0.05	-	2	ms

Table 10. MSO8P/SO-8 electrical characteristics

Symbol	Symbol Parameter Test condition			Value		Unit
Symbol	Faiailletei	rest condition	Min.	Тур.	Max.	Oilit
	Static drain source	V _{IN} = 2.7 V; T _J = 25 °C	-	130	170	mΩ
R _{ON}	ON state resistance SO-8 and MSO8 package load = 500 mA (STMPS2141/ STMPS2151) load = 1000 mA (STMPS2161/ STMPS2171)	V _{IN} = 5.0 V; T _J = 25 °C	-	110	125	mΩ
R _{ON}	Static drain source	V _{IN} = 2.7 V -40 < T _J < 125 °C	-	-	200	mΩ
ON	ON state resistance	V _{IN} = 5.0 V -40 < T _J < 125 °C	-	-	140	
t _r	Output rise time	V_{IN} = 5.0 V R_L = 10 Ω C_L = 1 μF	0.05	-	2	ms



Table 11. Current limit characteristics (V_{IN} = 5.5 V, I_{OUT} = rated current, T_J = 25 °C, unless otherwise specified)

Symbol	Parameter	Test condition		Value		Unit
Symbol	Farameter	rest condition	Min.	Тур.	Max.	Oilit
I _{OS} (STMPS2141 STMPS2151)	Overcurrent limiting threshold	V _{IN} = 5.5 V V _{OUT} = 5.0 V	0.60	0.80	1.00	Α
I _{OS} (STMPS2161 STMPS2171)	Overcurrent limiting threshold	V _{OUT} = 5.0 V	1.10	1.50	1.90	Α
I _{OS} (2141, 2151)	Short-circuit output current	V _{IN} = 5.5 V, OUT connected to GND,	1	-	0.9	Α
I _{OS} (2161, 2171)	Short-circuit output current	device enabled into short-circuit	-	-	1.8	Α

Table 12. Supply current characteristics (V_{IN} = 5.5 V, I_{OUT} = rated current, T_J = 25 °C, unless otherwise specified)

	Davamatar	Took oon dikion		Value		l lmia
Symbol	Parameter	Test condition	Min.	Тур.	Max.	- Unit - μΑ - μΑ
		No load	-	6.0	12	
l _{OFF}	Switch turned off	No load; -40 < T _J < 125 °C	-	-	15	μΑ
		No load	-	40	60	
I _{ON}	Switch turned on	No load; -40 < T _J < 125 °C	-	-	70	μΑ
	Output lookage	Output grounded, switch is OFF	-	-	2	
I _{leakage}	Output leakage current ⁽¹⁾	Output grounded, switch is OFF; -40 < T _J < 125 °C	-	-	5	μА
	Reversed leakage	Switch is off, V _{IN} < V _{OUT} , output connected to 5.5 V, 25 °C	-	0.5	2	
^I reverse	current	Switch is off, V _{IN} < V _{OUT} , output connected to 5.5 V, 125 °C	-	0.5	3	μΑ

^{1.} $I_{leakage} = I_{OFF-ground} - I_{OFF}$, where $I_{OFF-ground} = current$ into V_{IN} when switch is off and output is grounded.

57

Table 13. Thermal characteristics (V_{IN} = 5.5 V, I_{OUT} = rated current, T_J = 25 °C, unless otherwise specified)

Comphal	Dovernotor	Took condition		Value	11:4	
Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
T1	Thermal shutdown threshold		-	-	145	°C
T2	Recovery from thermal shutdown		120	-	-	°C
Hysteresis	-		-	14	-	°C

Table 14. UVLO characteristics (V_{IN} = 5.5 V, I_{OUT} = rated current, T_J = 25 °C, unless otherwise specified)

Cymbol	Parameter	Test condition	Value		Unit	
Symbol	Parameter	rest condition	Min.	Тур.	Max.	Offic
V _{UVLO}	Undervoltage lockout threshold		2.0	-	2.5	V
Hysteresis	-		40	75	110	mV

Table 15. FAULT pin characteristics (V $_{IN}$ = 5.5 V, I_{OUT} = rated current, T_J = 25 $^{\circ}C,$ unless otherwise specified)

Cumbal	Dovomotov	Toot condition		Value			
Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit	
OC blanking	FAULT assertion and de- assertion		4	8	15	ms	
V _{OUT}	Output low voltage	I _{OUT} = 5 mA	-	-	0.4	V	
l _{OFF}	Off current	V _{FAULT} = 2.7 V, 5.5 V (no OC condition)	-	-	1.0	μΑ	

Table 16. EN pin characteristics (V_{IN} = 5.5 V, I_{OUT} = rated current, T_J = 25 °C, unless otherwise specified)

Cumbal	Dozomotov	Toot condition		Value		Unit	
Symbol	Parameter	Test condition	Min.	Тур.	Max.	Ollit	
V_{IH}	High level input voltage	V _{IN} = 2.7 to 5.5 V	2.0	-	-	V	
V	Low level input voltage	V _{IN} = 4.5 to 5.5 V	-	-	0.8	V	
V _{IL} I	Low level input voltage	V _{IN} = 2.7 to 4.5 V	-	-	0.4	V	
I _{IN}	Input current	V _{IEN} = 0 V or V _{IN}	-0.5	-	0.5	μΑ	



DocID013793 Rev 7

Table 16. EN pin characteristics (V $_{IN}$ = 5.5 V, I $_{OUT}$ = rated current, T $_{J}$ = 25 $^{\circ}C,$ unless otherwise specified)

t _{ON}	Turn-ON time ⁽¹⁾	$R_L = 10 \Omega$ $C_L = 100 \mu F$	-	-	5	ms
t _{OFF}	Turn-OFF time ⁽¹⁾	$R_L = 10 \Omega$ $C_L = 100 \mu F$	-	-	10	ms

^{1.} Not tested in production, specified by design.

57

7 Detail device characteristics

7.1 STMPS2141, STMPS2151 additional electrical charts

The waveforms displayed in *Section 7.1* are captured with the STMPS2141 device. The STMPS2151 device is expected to have the same characteristics with EN in the opposite polarity.

7.1.1 Turn-on/off characteristics at $V_{OUT} = 5.0 \text{ V}$


Figure 3. Voltage output turn-on delay time (STMPS2141/2151, 5 V)

(STMPS2141/2151, 5 V) IL = 500 mA IL = 500 mA EN EN 1 V/DIV 1 V/DIV 100 µF Vout VOUT 1 V/DIV 470 µF 1 V/DIV 470 uF 1 µF 1 µF 100 µF Time base = 5 ms/DIV Time base = 5 ms/DIV

Figure 5. Current output turn-on delay time (STMPS2141/2151, 5 V)

Figure 6. Current output turn-off delay time (STMPS2141/2151, 5 V)


Figure 4. Voltage output turn-off delay time



7.1.2 Turn-on/off characteristics at $V_{OUT} = 3.0 \text{ V}$

Figure 7. Voltage output turn-on delay time (STMPS2141/2151, 3 V)

Figure 8. Voltage output turn-off delay time (STMPS2141/2151, 3 V)








Figure 9. Current output turn-on delay time (STMPS2141/2151, 3 V)

Figure 10. Current output turn-off delay time (STMPS2141/2151, 3 V)






577

7.1.3 UVLO

Figure 11. UVLO rising (STMPS2141/2151)

Figure 12. UVLO falling (STMPS2141/2151)



7.1.4 OC protection characteristics

Figure 13. OC protection at V_{OUT} = 3.0 V (STMPS2141/2151)

Figure 14. OC protection at V_{OUT} = 3.0 V (STMPS2141/2151 - details)





Figure 15. OC protection at $V_{OUT} = 5.0 \text{ V}$ (STMPS2141/2151)

Figure 16. OC protection at $V_{OUT} = 5.0 \text{ V}$ (STMPS2141/2151 - details)



7.1.5 Other electrical characteristics

Figure 17. I_{CC} vs. V_{IN} (enabled) (STMPS2141/2151)

Figure 18. I_{CC} vs. temperature (enabled) (STMPS2141/2151)




Figure 19. I_{CC} vs. V_{IN} (disabled) (STMPS2141/2151)

Figure 20. I_{CC} vs. temperature (disabled) (STMPS2141/2151)





Figure 21. R_{ON} vs. V_{IN} (STMPS2141/2151)

Figure 22. R_{ON} vs. temperature (STMPS2141/2151)







Figure 23. I_{OS} vs. temperature (STMPS2141/2151)

Figure 24. Switch leakage vs. temperature (STMPS2141/2151)








Figure 25. Output rise time vs. V_{IN} (STMPS2141/2151)

Figure 26. Output fall time vs. V_{IN} (STMPS2141/2151)





2.3
Rising
2.1
Falling

Temperature (°C)

Figure 27. UVLO vs. temperature (STMPS2141/2151)

577


7.2 STMPS2161, STMPS2171 electrical charts

The waveforms displayed in *Section 7.2* are captured with the STMPS2161 device. The STMPS2171 device is expected to have the same characteristics with EN in the opposite polarity.

7.2.1 Turn-on/off characteristics at $V_{OUT} = 5.0 \text{ V}$

Figure 28. Voltage output turn-on delay time (STMPS2161/2171, 5 V)

Figure 29. Voltage output turn-off delay time (STMPS2161/2171, 5 V)








Figure 30. Current output turn-on delay time (STMPS2161/2171, 5 V)

Figure 31. Current output turn-off delay time (STMPS2161/2171, 5 V)






7.2.2 Turn-on/off characteristics at V_{OUT} = 3.0 V

Figure 32. Voltage output turn-on delay time (STMPS2161/2171, 3 V)

Figure 33. Voltage output turn-off delay time (STMPS2161/2171, 3 V)








Figure 34. Current output turn-on delay time (STMPS2161/2171, 3 V)

Figure 35. Current output turn-off delay time (STMPS2161/2171, 3 V)







57/

7.2.3 UVLO

Figure 36. UVLO rising (STMPS2161/2171)

Figure 37. UVLO falling (STMPS2161/2171)






7.2.4 OC protection characteristics

Figure 38. OC protection at V_{OUT} = 3.0 V (STMPS2161/2171)

Figure 39. OC protection at V_{OUT} = 3.0 V (STMPS2161/2171- detail)







Figure 40. OC protection at $V_{OUT} = 5.0 \text{ V}$ (STMPS2161/2171)

Figure 41. OC protection at V_{OUT} = 5.0 V (STMPS2161/2171- detail)



7.2.5 Other electrical characteristics

Figure 42. I_{CC} vs. V_{IN} (enabled) (STMPS2161/2171)

Figure 43. I_{CC} vs. temperature (enabled) (STMPS2161/2171)




Figure 44. I_{CC} vs. V_{IN} (disabled) (STMPS2161/2171)

Figure 45. I_{CC} vs. temperature (disabled) (STMPS2161/2171)





Figure 46. R_{ON} vs. V_{IN} (STMPS2161/2171)

Figure 47. R_{ON} vs. temperature (STMPS2161/2171)







Figure 48. I_{OS} vs. temperature (STMPS2161/2171)

Figure 49. Switch leakage vs. temperature (STMPS2161/2171)








Figure 50. Output rise time vs. V_{IN} (STMPS2161/2171)

Figure 51. Output fall time vs. V_{IN} (STMPS2161/2171





2.3
Rising
2.1
Falling

-50
0
50
100
150
Temperature (°C)

Figure 52. UVLO vs. temperature (STMPS2161/2171)



8 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: www.st.com. ECOPACK is an ST trademark.




Figure 53. SOT23-5L package outline

Table 17. SOT23-5L package mechanical data

			Dimen	sions		
Symbol		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	0.90	-	1.45	35.4	-	57.1
A1	0.00	-	0.10	0.0	-	3.9
A2	0.90	-	1.30	35.4	-	51.2
b	0.35	-	0.50	13.7	-	19.7
С	0.09	-	0.20	3.5	-	7.8
D	2.80	-	3.00	110.2	-	118.1
Е	1.50	-	1.75	59.0	-	68.8
е	-	0.95	-	-	37.4	-
Н	2.60	-	3.00	102.3	-	118.1
L	0.10	-	0.60	3.9	-	23.6



Figure 54. SOT23-5L footprint recommendations




Table 18. SOT23-5L footprint dimensions

Footprint data						
Symbol	Dime	nsions				
Symbol	Millimeters	Inches				
А	3.50	0.138				
В	1.10	0.043				
С	0.60	0.024				
D	0.95	0.037				
E	1.20	0.047				
F	2.30	0.090				

Y/

4.0 \emptyset 1.5 + 0.1/-0.0 2.0 ± 0.05 -0.20 ± 0.03 В 1.75 3.5 ± 0.05 Во 8.0 + 0.3/-0.1 ∠ Ø 1.0 min. 4.0 Κo Ao SECTION A-A Ao = 3.15 mm Bo = 3.20 mm Ko = 1.4 mm SECTION B-B SOT23-5L-cr

Figure 55. SOT23-5L carrier tape






Figure 56. SO-8 package outline

1. Drawing is not to scale.

Table 19. SO-8 mechanical data

			Dimen	sions		
Symbol		Millimeters		Inches		
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	1.35	-	1.75	0.053	-	0.069
A1	0.10	-	0.25	0.004	-	0.010
A2	1.10	-	1.65	0.043	-	0.065
В	0.33	-	0.51	0.013	-	0.020
С	0.19	-	0.25	0.007	-	0.010
D ⁽¹⁾	4.80	-	5.00	0.189	-	0.197
Е	3.80	-	4.00	0.15	-	0.157
е	-	1.27	-	-	0.050	-
Н	5.80	-	6.20	0.228	-	0.244
h	0.25	-	0.50	0.010	-	0.020
L	0.40	-	1.27	0.016	-	0.050
k		+	0° (min.), 8	B° (max.)	1	1
ddd	-	-	0.10	-	-	0.004

Dimension D does not include mold flash, protrusions or gate burrs. Mold flash, potrusions or gate burrs shall not exceed 0.15 mm (0.006 inch) in total (both sides).

4

P₂ 2.0 ± 0.1 P₀ 4.0 ± 0.1 0.30 ± 0.05 ø 1.55 ± 0.05-_{1.75} ± 0.1 \bigoplus ø 1.6 ± 0.1 -REF. 4.2 R 0.2 Typical x -Αo SECTION X - X REF. 4.18 REF. 3.65 Αo 6.50 +/- 0.1 Bo Ko 5.30 +/- 0.1 2.20 +/- 0.1 REF 0.3 K1 1.90 +/- 0.1 Ę 5.50 +/- 0.1 8.00 +/- 0.1 12.00 +/- 0.3 REF 0.57 F 8.00 12.00 Р1 SECTION Y - Y

Figure 57. SO-8 carrier tape



D E1 POA 7113595

Figure 58. MSOP8 package outline

1. Drawing not to scale.

Table 20. MSOP8 package mechanical data

	Dimensions						
Symbol	Millimeters			Inches			
=	Min.	Тур.	Max.	Min.	Тур.	Max.	
Α	-	-	1.10	-	-	0.043	
A1	0.05	-	0.15	0.002	0.004	0.006	
A2	0.75	0.85	0.95	0.031	0.034	0.037	
b	0.25	-	0.40	0.010	0.013	0.016	
С	0.13	-	0.23	0.005	0.007	0.009	
D	2.90	3.00	3.10	0.114	0.118	0.122	
E	4.65	4.90	5.15	0.187	0.193	0.199	
E1	2.90	3.00	3.10	0.114	0.118	0.122	
е	-	0.65	-	-	0.026	-	
L	0.40	0.55	0.70	0.016	0.022	0.028	
L1	-	0.95	-	-	0.037		
K	0°	-	6°	0°	-	6°	
CCC			0.10			0.004	

Figure 59. MSOP8 carrier tape






Figure 60. Reel information

Table 21. Reel mechanical data

Cymphol	Dimensions (mm)				
Symbol	Min.	Тур.	Max.		
A SOT23-5L S0-8, MSOP8	-	-	180 330		
С	12.8	13.0	13.2		
D	20.2	-	-		
N	60	-	-		
Т	-	-	22.4		

57

9 Ordering information

Table 22. Order codes

Part number	Package	Marking
STMPS2141MTR		2141E
STMPS2151MTR	SO-8	2151E
STMPS2161MTR		2161E
STMPS2171MTR		2171E
STMPS2141STR		2141
STMPS2151STR	SOT23-5L	2151
STMPS2161STR	30123-3L	2161
STMPS2171STR		2171
STMPS2141TTR		2141
STMPS2151TTR	MSOP8	2151
STMPS2161TTR		2161
STMPS2171TTR		2171

10 Revision history

Table 23. Document revision history

Date	Revision	Changes	
01-Aug-2007	1	Initial release.	
18-Dec-2007	2	Minor text changes, updated Figure 53 on page 28, added Section Detail device characteristics on page 16.	
24-Jan-2008	3	Footnote added in Table 1 on page 1, replaced Figure 58 on page 3 and Table 20 on page 32, TSSOP8 package name replaced with MSOP8.	
17-Jul-2009	4	Updated Chapter 3, test conditions modified for Ireverse in Table 12 on page 14 and Chapter 7. Added: Figure 55, Figure 56, Figure 59, Figure 59 and Figure 60.	
21-Nov-2012	5	Updated Table 1 (replaced "Current limit" by "Rated continuous output current"). Updated values and units in Table 4 to Table 6. Corrected Figure 1 and Figure 2 (replaced EN_N by EN). Replaced I ₁ by I _{1N} , I _{LIMIT} by I _{OS} , I _O by I _{OUT} , mS by ms, OC by FAULT, R _{ds(on)} by R _{ON} , V ₁ and V _{CC} by V _{1N} , V _O by V _{OUT} , in the whole document. Updated Section 5 (added cross-references). Updated Table 9 and Table 10 (replaced Tr by t _r), Table 11 (updated test conditions). Updated Table 15 (replaced Fault, OCx, and V _{OC} by FAULT). Updated Table 16 (replaced V _{IENX} by V _{IEN} , mF by μ F). Updated titles of Figure 3 to Figure 52 (added conditions). Updated Figure 3 to Figure 16, Figure 25, Figure 26, Figure 28 to Figure 41, Figure 50 and Figure 51 (replaced R _L by I _L , mS by ms, and uF by μ F). Updated Figure 55, Figure 59, and Figure 59 (removed superfluous references to notes). Reformatted Section 8 (moved Figure 57 on page 31). Removed Figure 56. Updated Table 21 (added SOT23-5L, SO-8, and MSOP package and max. value for SOT23-5L package). Added Section 9. Minor corrections throughout document.	
25-Jan-2013	6	Updated Features (added UL recognized components).	
14-Feb-2022	7	Updated Features on the cover page, Figure 21, Figure 22, Figure 46 and Figure 47.	



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2022 STMicroelectronics - All rights reserved



DocID013793 Rev 7

39/39