

### 2.0x1.25mm SMD CHIP LED LAMP

Part Number: KPT-2012SYCK

Super Bright Yellow


### **Features**

- 2.0mm x1.25mm SMT LED,0.75mm thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Various colors and lens types available.
- Package: 2000pcs / reel.
- Moisture sensitivity level : level 3.
- RoHS compliant.

## **Description**

The Super Bright Yellow device is made with AlGaInP (on GaAs substrate) light emitting diode chip.

## **Package Dimensions**



- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is ±0.1(0.004") unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
   The device has a single mounting surface. The device must be mounted according to the specifications.





SPEC NO: DSAB1887 **REV NO: V.18B DATE: NOV/19/2013** PAGE: 1 OF 5 APPROVED: WYNEC **CHECKED: Allen Liu** DRAWN: Q.M.Chen ERP: 1203001892

## **Selection Guide**

Part No.	No. Dice Lens Type		lv (mcd) [2] @ 20mA		Viewing Angle [1]
		-	Min.	Тур.	201/2
KPT-2012SYCK	Super Bright Yellow (AlGaInP)	Water Clear	80	150	120°

### Notes:

- 1. 01/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
  2. Luminous intensity/ luminous Flux: +/-15%.
  3. Luminous intensity value is traceable to the CIE127-2007 compliant national standards.

# Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Super Bright Yellow	590		nm	IF=20mA
λD [1]	Dominant Wavelength	Super Bright Yellow	590		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Super Bright Yellow	20		nm	IF=20mA
С	Capacitance	Super Bright Yellow	20		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Super Bright Yellow	2	2.5	V	IF=20mA
lR	Reverse Current	Super Bright Yellow		10	uA	V <sub>R</sub> =5V


- Notes:
  1.Wavelength: +/-1nm.
  2. Forward Voltage: +/-0.1V.
  3. Wavelength value is traceable to the CIE127-2007 compliant national standards.

# Absolute Maximum Ratings at TA=25°C


Parameter	Super Bright Yellow	Units	
Power dissipation	75	mW	
DC Forward Current	30	mA	
Peak Forward Current [1]	175	mA	
Reverse Voltage	5	V	
Operating Temperature	-40°C To +85°C		
Storage Temperature	-40°C To +85°C		


Note: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.


SPEC NO: DSAB1887 **REV NO: V.18B DATE: NOV/19/2013** PAGE: 2 OF 5 **APPROVED: WYNEC CHECKED: Allen Liu** ERP: 1203001892 DRAWN: Q.M.Chen





Super Bright Yellow KPT-2012SYCK












 SPEC NO: DSAB1887
 REV NO: V.18B
 DATE: NOV/19/2013
 PAGE: 3 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Q.M.Chen
 ERP: 1203001892

### KPT-2012SYCK

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.



- NOTES:

  1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


  2.Don't cause stress to the epoxy resin while it is exposed to high temperature.
- to high temperature.

  3.Number of reflow process shall be 2 times or less.


Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)



# **Reel Dimension**



Tape Dimensions (Units: mm)





 SPEC NO: DSAB1887
 REV NO: V.18B
 DATE: NOV/19/2013
 PAGE: 4 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Q.M.Chen
 ERP: 1203001892

# PACKING & LABEL SPECIFICATIONS

### KPT-2012SYCK







### Terms and conditions for the usage of this document

- 1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6.All design applications should refer to Kingbright application notes available at <a href="http://www.kingbright.com/application">http://www.kingbright.com/application</a> notes

 SPEC NO: DSAB1887
 REV NO: V.18B
 DATE: NOV/19/2013
 PAGE: 5 OF 5

 APPROVED: WYNEC
 CHECKED: Allen Liu
 DRAWN: Q.M.Chen
 ERP: 1203001892