


SFN4[

RELA

Panasonic



Tolerance ±0.3 mm Weight approx. 42 g

Low profile safety relay with forcibly guided double contacts



- Relay complies with EN 50205, Type B
- Polarized magnet system with snap action function
- Extremely small total power loss
 - Nominal coil power consumption of 390mW
 - Double contacts with low contact resistance, e.g. [(6A)² × 2.5m Ω] × 4NO = 360mW
- Relay height, 14.5mm
- **Reinforced insulation according to EN 50178** - between coil-contacts and contacts-contacts
 - rated voltage of the circuits 230 / 400V or 277 / 480Vrms
- rated impulse voltage of 6kV \rightarrow clearance \geq 5.5 mm
- pollution degree 2 \rightarrow creepage distance \geq 5.5mm

SPECIFICATIONS

Co	nta	ct

oontaot	
Contact configuration (a = normally open / NO, b = normally closed / NC)	4a2b
Contact material	AgSnO ₂ , with Au flash
Contact resistance (initial at 6V DC, 1A) Typical contact resistance	≤30mΩ 2.5mΩ
Max. switching capacity	6A/8A ^{*1} 250V AC
Max. switching voltage	500V AC / DC
Min. switching voltage / min. switching current	Reference 10V / 10mA
Pick-up / drop-out / bounce time (approx. values at U _{nominal})	23 / 6 ^{*2} / 2ms
Mechanical life	10 ⁷ ops

75% / 25%

min. 48%

219-236 / 390-420mW

Characteristics

Max. switching frequency (without load)	5Hz
Permissible ambient temperature at nominal power consumption * ³	-25°C to 92°C
Upper temperature limit	105°C
Test voltage: open contact / contact-contact / contact-coil	2500 / 4000 / 5000V _{rms}
Insulation resistance at 500V DC (initial)	10 ⁹ Ω
Shock resistance (11ms) NO/NC ^{*4}	20 / 15G
Vibration resistance $10 - 200$ Hz ($10 - 55$ Hz, amplitude 2 mm) ^{*4}	10G
Degree of protection	RT III ^{*5}
Unit weight	42g

Important: Relay characteristics may be influenced by:

· strong external magnetic fields

· magnetic conductive materials near the relay

• narrow top-to-top mounting (printed surface to printed surface)

1 See "ELECTRICAL LIFE (Reference Data)" on page 2.

*2 Without diode

Operate / release

Coil

*3 See also "REFERENCE DATA" on page 3. *4 Contact interruption <10µs

*5 According to EN 61810-1: 2004, table 2

and holding at 20°C (% of $U_{nominal}$)^{*3}

Pick-up/nominal power consumption

ORDERING INFORMATION

Ex. SFN4D — DC12 V Coil voltage (DC) 5, 9, 12, 16, 18, 21 24, 36, 48, 60

> Notes: 1) Standard packing; Tube: 10 pcs. Case 100 pcs. 2) Other coil voltage available upon request

COIL DATA (at 20°C)

Part number	Coil nominal voltage V DC	Operate voltage ^{*1} V DC	Release voltage ^{*1} V DC	Coil resistance Ω (±10%, 20°C)
SFN4D-DC5V	5	3.75	1.25	64.1
SFN4D-DC9V	9	6.75	2.25	207.7
SFN4D-DC12V	12	9.00	3.00	369.2
SFN4D-DC16V	16	12.00	4.00	656.4
SFN4D-DC18V	18	13.5	4.50	830.8
SFN4D-DC21V	21	15.75	5.25	1130.8
SFN4D-DC24V	24	18.00	6.00	1476.9
SFN4D-DC36V	36	27.00	9.00	3085.7
SFN4D-DC48V	48	36.00	12.00	5485.7
SFN4D-DC60V	60	45.00	15.00	8571.4

*1 Operate and release voltage at different temperatures, see "REFERENCE DATA" on page 3, coil voltage characteristics.

SWITCHING CAPABILITY

- Making / breaking capacities according to EN 60947-5-1: 2000, table 4 / 5; AC15: 6A 230V AC / DC13: 6A 24V DC
- Endurance / overload test according to UL 508 16 edition, sections 42 / 43; 6A 250V AC / 6A 24V DC; B300 / R300; File E120782

ELECTRICAL LIFE (Reference Data)


Voltage	Current (A)	Load type	Frequency	Duty cycle	No. of contacts	No. of ops.
230V AC	8	AC 1	0.25Hz	25%	4	85,000
230V AC	6	AC 1	0.25Hz	25%	4	200,000
230V AC	2.5	AC 1	0.25Hz	25%	4	1,500,000
230V AC	60 / 6	AC 15	0.20Hz	20%	3	40,000
24V DC	6	DC 1	0.25Hz	25%	4	2,000,000
250V DC	0.27	DC 13	0.10Hz	10%	4	1,000,000

*Test conditions: Room temperature, breathing hole closed, dielectric strength according to EN61810-1:2004.

DIMENSIONS


Outer dimensions


CAD Data




General tolerance: ± 0.3 Projection mode:

Schematic (Bottom view)






PC board pattern (Bottom view)



Download CAD Data from our Web site.


SFN4D REFERENCE DATA


Coil voltage characteristics




Thermic operating range









REFERENCE DATA, continued




Load limit curve





SFN4D APPLICATION NOTES The SFN4D Safety Relay



Legend for interpreting contact conditions

Contact	NC (Normally Closed)			NC (Normally Closed) NO (Normally Open)				
Condition	Closed	Fully open	Open	Open or closed	Closed	Fully open	Open	Open or closed
Symbol		ļ	Ļ			ļ	ļ	
Contact gap	0	Maximum (~1.5mm)	>0.5mm (forcibly guided)	Not defined	0	Maximum (~1.5mm)	>0.5mm (forcibly guided)	Not defined

The SFN4D under normal operating conditions

Condition	Illustration of Relay State	Condition of Contacts
 Coil deenergized. Armature in deenergized position. NC contacts closed. NO contacts have a contact gap of approx. 1.5mm. 		$ \begin{array}{cccccccccccccccccccccccccccccccccccc$
 Coil energized. Armature in energized position. NO contacts closed. NC contacts have a contact gap of approx. 1.5mm. 		$ \begin{array}{cccccccccccccccccccccccccccccccccccc$


SFN4D

The SFN4D safety relay with welded contacts Condition **Illustration of Relay State Condition of Contacts** - NC 5-6 welded. - Coil energized. - All NO contacts are forcibly - Armature nearly in guided. deenergized position. 70 90 120 140 160 60 88 100 110 130 15- The NO contact gaps are min. 0.5mm. - For NC 16-15, the contact condition is not defined. - NC 16-15 welded. - Coil energized. - All NO contacts are forcibly - Armature nearly in deenergized position. guided. - The NO contact gaps are 13 15 min. 0.5mm. - For NC 5-6, the contact condition is not defined. - NO 12-11 welded. - Coil deenergized. - All (both) NC contacts are - Armature nearly in forcibly guided. energized position. - The NC contact gaps are min. 0.5mm. - For all NO contacts, the contact condition is not defined. - NO 14-13 welded. - Coil deenergized. - All (both) NC contacts are - Armature in nearly forcibly guided. energized position. - The NC contact gaps are min. 5 ~ 7 9 12 14 16 -6 8 10 11 11 13 15 0.5mm. - For all NO contacts, the contact condition is not defined. - NO 7-8 welded. - NC 16-15 is closed!! - Coil deenergized. - All non-welded NO - Armature in deenergized contacts show their max. 5 - 7, 7 - 9, 12 - 14, 16 - 6, 8 - 70, 10 - 11, 13 - 15, 15 - 7position. contact gap. - NC 5-6 forcibly guided to the welded contact by sub card 1. The contact gap is min. 0.5mm. - NO 9-10 welded. - NC 16-15 is closed!! - Coil deenergized. - All non-welded NO - Armature in deenergized contacts show their max. position. 120 140 160 1 111₁ 13₁ 150 contact gap. - NC 5-6 forcibly guided to the welded contact by sub card 2. The contact gap is min. 0.5mm.


SFN4D

Failure modes, application examples

1) Feedback loop, 2) Self-holding circuit, 3) Safety circuit, 4) Auxiliary contacts



Wiring for application examples 2.1 and 2.2



For Cautions for Use, see Relay Technical Information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panasonic:

<u>SFN4D-DC12V</u> <u>SFN4D-DC16V</u> <u>SFN4D-DC18V</u> <u>SFN4D-DC21V</u> <u>SFN4D-DC24V</u> <u>SFN4D-DC36V</u> <u>SFN4D-DC48V</u> SFN4D-DC5V SFN4D-DC60V SFN4D-DC9V