

CLW-2412-W2E-EA series

12V / 2A Wall Mounted Type Constant Voltage Power Supply



■ Features:

- Universal AC input / Full range
- ErP step II / CEC level VI compliance
- Protections: Over current / Short circuit



ELECTRICAL SPECIFICATION

MODEL	CLW 2412 W2E EA
-------	-----------------

OUTPUT

Rated Voltage	12V
Rated Current	2A
Current Range	0 ÷ 2A
Rated Power	24W
Line Regulation	± 2%
Load Regulation	± 5%
Tolerance [3]	± 5%
Ripple & Noise (max.) [2]	150mV _{p-p}
Setup, Rise Time [4]	100ms / 230VAC at full load
Hold up Time (typ.)	3ms / 230VAC at full load

INPUT

Voltage Range	90 ÷ 264VAC
Frequency Range	47 ÷ 63Hz
Efficiency (typ.)	86.04%
AC Current (typ.)	0.6A / 230VAC
Inrush Current (typ.)	60A / 230VAC
No load Power Consumption (max.)	< 0.1 W

PROTECTIONS

Over Current	Type: hiccup mode, auto-recovery.
Short Circuit	Type: hiccup mode, auto-recovery.

CLW-2412-W2E-EA series



12V / 2A Wall Mounted Type Constant Voltage Power Supply

WORKING ENVIRONMENT

Working Temperature	0°C ÷ 40°C
Working Humidity	10 ÷ 90% RH non-condensing
Storage Temperature and Humidity	-20°C ÷ 85°C, 5 ÷ 90% RH non-condensing

SAFETY and EMC REGULATIONS

Safety Standards	Compliance to EN 62368
Withstand Voltage	IN/OUT: 3600 VAC
Isolation Resistance	IN/OUT: 50MΩ/500VDC/25°C/70%
EMC Emission	Compliance to EN55032
EMC Immunity	Compliance to EN61000-4-2, -3, -4, -5
Harmonic Current	Compliance to EN61000-3-3; EN61000-3-2

OTHERS

Dimensions	70x 30.0 x 64.5mm (L x W x H)
Weight	152g

MECHANICAL SPECIFICATION

