III TRACO POWER

Industrial Power Supplies

TIB 080 Series, 80 Watt

- Slim profile, for DIN-rail mounting
- Alternative side-mounting for flat panels
- High power factor by active power correction
- Very high efficiency up to 90%
- Back power immunity
- 150% peak current for 4 sec.
- Operating temperature range:
 -40°C to +70°C max.
- Adjustable output voltage
- DC-OK indicator
- Short circuit and overload protection
- Class I, division 2 approval and ATEX certification for EX-models
- 5-year product warrenty for EX-models

















Other output power of same series: www.tracopower.com/overview/tib

This generation of DIN-rail power supplies combines the most efficient circuit topology with optimized cost/performance ratio for industrial environments and for electrical control cabinets.

They have a very high efficiency of up to 90.0% which allows a very slim package design. The output voltage is adjustable from -2% to +17%. The case offers the potentially useful feature to fix the DIN-rail clip to the side wall for the mounting inside flat panels. Over a period of minimum 4 seconds they can operate with a boost power of 150%. The boost power facilitates the activation of stepper motors, solenoids or actuators. The units operate with a high power factor by active power factor correction which also keeps the input inrush current low. The TIB series are also available with higher nominal power of 120, 240 or 480 Watt (+50% boost power). They come with the safety standard approvals for IEC/EN 60950-1, UL 60950-1 and UL 508.

Models						
Order Code	Output Power	Output Voltage nom. (adjustable)	Output Current	Efficiency		
	(max.)	nom. (adjustable)	(max.)	(typ.)		
TIB 080-112	80 W	12 VDC (11.8–15.0)	6.7 A	88.0 %		
TIB 080-112EX	80 W					
TIB 080-124	00.111	24 VDC (23.5-28.0)	3.4 A	90.0 %		
TIB 080-124EX	80 W					
TIB 080-148	90 W	48 VDC (47.0-56.0)	1.7 A	90.0 %		
TIB 080-148EX	80 W					

www.tracopower.com Page 1 of 6



Input Specification	ns		
Input voltage	nominal rangeseffective ranges		100 - 240 VAC 85 - 264 VAC (below 90 VAC a derating of 3%/V is required)
Input voltage frequency			45 – 65 Hz
Standby power cunsumpt	tion		0.9/1.45 W (115/230 VAC)
Power Factor Correction	(PFC)		0.48/0.48 (115/230 VAC)
Harmonic limits	– acc. EN 61000-3-2		class A
Inrush current			15/30A max. (115/230 VAC)
Output Specificat	ions		
Output voltage adjustmer	nt 1)	12 Vout models: 24 Vout models: 48 Vout models:	23.5 – 28.0 V
Regulation	Input variationLoad variation (10–90 %)		0.1 % max. 0.5 % max.
Temperature coefficient			0.02 %/K
Hold-up time			20/160 ms min. (115/230 VAC)
Start-up time			2s max.
Ripple and Noise (20MHz bandwidth)		12 & 24 Vout models: 48 Vout models:	100 mVp-p max. 200 mVp-p max.
Output overvoltage protection (OVP) 2)		12 Vout models: 24 Vout models: 48 Vout models:	32 – 35 V
Power back immunity 3)			< OVP level
Operation	Nominal operationPeak power operationConstant current (cc)		100 % of lout nom. 105 – 150 % of lout nom. > 155 % of lout nom.
Duty cycle 4) (for peak and cc mode)	ThresholdCC or peak opeartion timernormal operation / off period		> 105 % 4 s max. (switch off) 6 s typ. (automatic restart after switch off or peak and cc operation timer reset)
Short circuit			Switch off after 4s delay, automatic restart
DC OK signal	- Threshold for Vout	12 Vout models: 24 Vout models: 48 Vout models:	on: > 10.9 V typ., off: < 10.7 V typ. on: > 22.5 V typ., off: < 21.5 V typ. on: > 45 V typ., off: < 43 V typ.
	– DC ON		relay contact closed, 1 A max., < 100 mOhn (also indicated by green LEDs: front and side)
	– DC OFF		relay contact open, 30 V max.

¹⁾ Output voltage can be adjusted as indicated. However, output power has to be maintained at nominal value. This means the output nominal current has to be reduced in accordance with the increase of output voltage.

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

www.tracopower.com Page 2 of 6

²⁾ In case of an internal error a second voltage regulation loop keeps the output voltage at a save level, the power supply turns off and restarts after typ. 6 seconds.

³⁾ When external voltage is supplied above set output voltage and below OVP threshold, the power supply will function normally without switch off or destruction, even if external voltage is applied continuously.

⁴⁾ In case of overload or short circuit, the unit switches the output voltage off after 4 seconds and tries to restart every typ. 6 seconds.




Operating temperature rai	nge	-40°C to +70°C max.		
Derating temperature range		2 %/K above +60°C		
Cooling		convection cooling, no internal fan		
Overtemperature protection		switch off at overtemperature		
Humidity (non condensing)		5-95 % rel. H max.		
Altitude during operation		2000 m max.		
Isolation Voltage	Input/OuputInput/ChassisOuput/Chassis	4250 VDC 1500 VDC 750 VDC		
Creepage Clearance	Input/OuputInput/ChassisOutput/Chassis	8 mm 4 mm 1.5 mm		
MTBF (acc. to IEC 61709 at	25°C)	> 1'950'000 h		
Safety standards	 Information technology equipment Safety low voltage switchgear and controlgear ATEX for hazardous location (EX models only) UL HazLoc (EX models only) Certification documents 	IEC/EN 60950-1, UL 60950-1 CSA 22.2 No 60950-1-03 UL 508 EN 60079-0, EN 60079-7, EN 60079-15 (EX II3G Ex ec nC IIC GC) Class I, Division 2 www.tracopower.com/overview/tib		
Electromagnetic compatib	oility (EMC), Emissions - Conducted emission input - Radiated RI emission	EN 61000-6-3, EN 61204-3 EN 55032, EN 55011 class B EN 55032, EN 55011 class B		
Electromagnetic compatib	- Railway applications signalling apparatus - Railway applications rolling stock apparatus - Electrostatic discharge (ESD) - Radiated RF field immunity - Electrical fast transient / burst immunity - Surge immunity - Immunity to conducted RF disturbances - Power frequency field immunity - Mains voltage dips and interruptions - Voltage sag immunity	EN 61000-6-2, EN 61204-3 EN 50121-4 EN 50121-3-2 IEC/EN 61000-4-2 4 kV/8 k' IEC/EN 61000-4-3 10 V/m IEC/EN 61000-4-4 2 kV IEC/EN 61000-4-5 1 kV/2 k' IEC/EN 61000-4-6 10 V IEC/EN 61000-4-8 30 A/m IEC/EN 61000-4-11 SEMI F47 (230 VAC)	criteria A criteria B	
Environment	Railway applications shock and vibrationVibration acc. IEC 60068-2-6-3Shock acc. IEC 60068-2-27	according EN 61373 3 axis, 2 g sine sweep, 10-55 Hz, 11 okt/min 3 axis, 25 g half sine, 11 ms		
Enclosure material	– Chassis – Cover	aluminium stainless steel		
Mounting	– DIN-rail mounting	for DIN-rails as per EN 50022-35×15/7.5		
Environmental compliance		www.tracopower.com/info/reach-declaration.pdf RoHS directive 2011/65/EU		
	- RoHS	ROHS directive 2011/65/EU		

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.


www.tracopower.com Page 3 of 6



Function Specification



Output Characteristic




Characteristic: Output voltage vs output current for overload conditions until switch off after 4 s at nominal input voltages


www.tracopower.com Page 4 of 6



Output Characteristic (continued)



Derating: max load vs input voltage




Derating: Load vs ambient temperature


www.tracopower.com Page 5 of 6




Outline Dimensions



* Measurement from fron panel to DIN-Rail





Weight: 367g (12.95 oz)

Alternative side mounting:

