

## Product Summary

|                               |       |
|-------------------------------|-------|
| $V_{RRM}$                     | 650 V |
| $I_F (T_c=150^\circ\text{C})$ | 15 A  |
| $Q_c$                         | 46 nC |

## Features

- Extremely low reverse current
- No reverse recovery current
- Temperature independent switching
- Positive temperature coefficient on  $V_F$
- Excellent surge current capability
- Low capacitive charge

## Benefits

- Essentially no switching losses
- System efficiency improvement over Si diodes
- Increased power density
- Enabling higher switching frequency
- Reduction of heat sink requirements
- System cost savings due to smaller magnetics
- Reduced EMI

## Applications

- Switch mode power supplies (SMPS)
- Uninterruptible power supplies
- Motor drivers
- Power factor correction

## Package Pin Definitions

- Pin1 and backside - Cathode
- Pin2 - Anode


## Package Parameters

| Part Number | Marking   | Package  |
|-------------|-----------|----------|
| B1D15065K   | B1D15065K | TO-220-2 |

## Package: TO-220-2



## Electrical Connection



**Maximum Ratings ( $T_c=25^\circ\text{C}$  unless otherwise specified)**

| Symbol        | Parameter                            | Test conditions   | Value     | Unit             |
|---------------|--------------------------------------|---|-----------|------------------|
| $V_{RRM}$     | Repetitive peak reverse voltage      |   | 650       | V                |
| $V_{RSM}$     | Non-repetitive peak reverse voltage  |   | 650       | V                |
| $I_F$         | Continuous forward current           | $T_c=25^\circ\text{C}$<br>$T_c=150^\circ\text{C}$         | 49<br>15  | A                |
| $I_{FSM}$     | Non-repetitive forward surge current | $T_c=25^\circ\text{C}, t_p=10\text{ms}$<br>Half sine wave | 112       | A                |
| $\int i^2 dt$ | i <sup>2</sup> t value               | $T_c=25^\circ\text{C}, t_p=10\text{ms}$                   | 62.72     | A <sup>2</sup> S |
| $P_{tot}$     | Power dissipation                    | $T_c=25^\circ\text{C}$<br>$T_c=110^\circ\text{C}$         | 194<br>84 | W                |
| $T_j$         | Operating junction temperature       |   | -55~175   | °C               |
| $T_{stg}$     | Storage temperature                  |   | -55~175   | °C               |
|               | TO-220 mounting torque               | M3 Screw  | 0.7       | Nm               |

**Thermal Characteristics**





| Symbol       | Parameter                                | Value |      |      | Unit |
|--------------|--|-------|------|------|------|
|              |  | Min.  | Typ. | Max. |      |
| $R_{th(jc)}$ | Thermal resistance from junction to case |       | 0.77 |      | K/W  |


**Electrical Characteristics**
**Static Characteristics**

| Symbol   | Parameter             | Test conditions   | Value |              |      | Unit    |
|----------|-----------------------|---|-------|--------------|------|---------|
|          |                       |   | Min.  | Typ.         | Max. |         |
| $V_{DC}$ | DC blocking voltage   | $T_j=25^\circ C$  | 650   |              |      | V       |
| $V_F$    | Diode forward voltage | $I_F=15A T_j=25^\circ C$<br>$I_F=15A T_j=175^\circ C$   |       | 1.42<br>1.75 |      | V       |
| $I_R$    | Reverse current       | $V_R=650V T_j=25^\circ C$<br>$V_R=650V T_j=175^\circ C$ |       | 1<br>10      |      | $\mu A$ |


**AC Characteristics**

| Symbol | Parameter                 | Test conditions   | Value |                   |      | Unit    |
|--------|---------------------------|---|-------|-------------------|------|---------|
|        |                           |   | Min.  | Typ.              | Max. |         |
| $Q_C$  | Total capacitive charge   | $V_R=400V T_j=25^\circ C$<br>$Q_C=\int_0^{V_R} C(V)dV$    |       | 46                |      | nC      |
| C      | Total capacitance         | $V_R=1V f=1MHz$<br>$V_R=300V f=1MHz$<br>$V_R=600V f=1MHz$ |       | 713<br>79.7<br>79 |      | pF      |
| $E_C$  | Capacitance stored energy | $V_R=400V$  |       | 7.2               |      | $\mu J$ |


**Typical Performance**

**Figure 1** Typical forward characteristics

**Figure 2** Typical reverse current as function of reverse voltage

**Figure 3** Diode forward current as function of temperature, D=duty cycle

**Figure 4** Typical capacitance as function of reverse voltage,  $C=f(V_R)$ ;  $T_j=25^\circ\text{C}$ ;  $f=1 \text{ MHz}$

**Typical Performance**



**Figure 5**    **Typical reverse charge as function of reverse voltage**



**Figure 6**    **Power dissipation as function of case temperature**







**Figure 7**    **Capacitance stored energy**



**Figure 8**    **Max. transient thermal impedance,  $Z_{thjc} = f(t_p)$ , parameter:  $D = t_p / T$**



Package Dimensions



| SYMBOL | mm       |       |       |
|--------|----------|-------|-------|
|        | MIN      | NOM   | MAX   |
| A      | 4.37     | 4.57  | 4.77  |
| A1     | 1.22     | -     | 1.40  |
| A2     | 2.49     | 2.69  | 2.89  |
| b      | 0.75     | -     | 0.96  |
| b2     | 1.22     | -     | 1.47  |
| c      | 0.30     | -     | 0.48  |
| D      | 15.15    | 15.45 | 15.75 |
| D1     | 9.05     | 9.15  | 9.25  |
| D2     | 11.40    | -     | 12.88 |
| E      | 9.86     | 10.16 | 10.36 |
| E1     | 6.86     | -     | 8.89  |
| e      | 4.98     | 5.08  | 5.18  |
| H1     | 6.10     | 6.30  | 6.50  |
| L      | 12.70    | -     | 13.70 |
| L1     | -        | -     | 4.10  |
| L2     | 2.50 REF |       |       |
| Φ P    | 3.70     | 3.84  | 3.99  |
| Q      | 2.54     | -     | 2.94  |
| θ1     | 5°       | 7°    | 9°    |
| θ2     | 1°       | 3°    | 5°    |

## Revision History

| Document Version | Date of Release | Description of Changes                    |
|------------------|-----------------|---|
| Rev. 1.0         | 2020-07-06      | Release of the datasheet.                 |
| Rev. 1.1         | 2020-09-30      | Thermal resistance from junction to case. |
| Rev. 1.2         | 2021-12-06      | Updated.                                  |
|                  |                 |   |

**BASiC Semiconductor Ltd.**  
**Shenzhen, China**  
**© 2021 BASiC Semiconductor Ltd.**  
**All Rights Reserved.**

## Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest BASiC Semiconductor Office

## Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, BASiC semiconductor Ltd. hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.