



## CONNECTING YOUR MEDICAL DEVICES

Manage and secure your medical devices and data with Lantronix fault-tolerant EDS-MD® IoT gateway for medical devices. This device gateway is IEC-60601 certified and can securely managed your devices locally on site or remotely by authorized employees.



### Manage Visibility into Medical Assets

The medical industry utilizes many connected devices and assets. A majority of these devices are critical to the operation of the medical enterprise, for example, patient monitors. The [EDS-MD](#) can be integrated into the medical enterprise network and enable visibility into these devices from anywhere at anytime.



### Manage Mission-Critical Data Securely

The transport of sensitive information to and from remote device servers over the Internet demands the highest level of security. With Lantronix' proprietary Secure Com Port Redirector™ virtualization software, existing serial port applications can work with EDS-MD without any code modifications. Virtual COM ports can be mapped to EDS-MD and encrypted at both ends of communication.



### Manage Assets and Data Locally or Remotely

Management of any device and data requires fault-tolerance. EDS-MD empowers authorized IT staff to access and monitor devices and data anywhere at anytime. In addition, the EDS-MD goes beyond the IEC-60601 requirement, as it provides galvanic isolation on all ports to ensure the highest levels of safety and fault-tolerance. Should a grounding issue ever occurs, the operation of EDS-MD or other connected devices will not be affected.



### High-Performance Wired Connectivity

The EDS-MD offers 4, 8 or 16 individually isolated RS-232 serial ports with a Gigabit (10/100/1000Mbps) network interface. The configuration and setup of the EDS-MD is simple with industry-standard management tools including integrated Web and CLI interfaces along with XML support. Device management capabilities are supported by Lantronix Device Management SaaS offerings—monitor, manage and troubleshoot your IoT assets with ConsoleFlow™, our ready-to-use software platform.

### Perfect For:



Hospital

Clinics



EMS

ER

### Feature Rich Turnkey Design

- Configure and connect to the enterprise network, out-of-the-box with ease
- Make your device visible to authorized users with EDS-MD unique Device ID feature
- Develop and deploy custom applications with standards-based runtime services quickly and efficiently
- Benefit from Lantronix industrial design quality, reliability and connectivity
- For wireless healthcare IoT device gateway, refer to [SGX5150 MD](#)

## Features and Specifications

### Standards

- IEEE 802.3
- IEEE 802.3ab
- IEEE 802.3u
- USB 2.0

### Hardware

- 600MHz ARM 11 processor
- 256 MB SDRAM
- 8MB Flash
- Real Time Clock with Battery back-up
- 4 GB SD Card (internal only)
- Onboard Thermal Sensor

### Physical Interface 4/8/16 RJ 45 DTE Serial Connectors

- Serial Connectors
- EDS Protection - 15kV
- RS-232 Interface
- Circuit and port isolation - 1.5KVAC
- Data rates - up to 921 Kpbs

### LED Indicators

- Power/System
- Serial Ports (4,8,16)
- Ethernet - Activity/Link

### Protocols

- DHCP Client, DHCP Server, DHCPv6 Client
- IPv4, TCP, UDP, ICMP, ARP, Auto-IP, DNS, SNMP v2/v3, NTP
- uPnP (Discovery), LCAP (77FE), Telnet, FTP, HTTP(S)

### Physical Dimensions

- Size: 21 cm (8.25 in) x 19 cm (7.5 in) x 6 cm (2.4 in)
- 8-port = 0.82 Kg (1.8 lbs)
- 4-port = 0.8 Kg (1.75 lbs)
- 16 Port = 0.9 Kg (2.0 lbs)

### Software

- Network Time Protocol(NTP) support
- Gateway Features - port forwarding, static routers and DHCP servers
- AES 192 & 256 bit encryption support
- Supports copying port config settings

### Security

- SSL v3, SSH v2 Client & Server - up to 2048-bit certificates
- Encryption: AES 3DES, RC4
- Authentication: SHA-1, MD5, Base-64

### Management

- Web Browser (SSL option for secure login)
- XML Configuration Records via CLI or FTP
- CLI (over Serial Ports, Telnet or SSH)

### Environmental

- Operating Temp: 0C to +55C (32F to 131 F)
- Relative humidity, non-condensing
- Storage Temp: -30C to +80C
- IP Rating = 20

### Power

- Input: IEC60320 C14 receptacle without a power switch
- Power consumption: 23 Watts Max
- 100-240 VAC, 50/60 HZ, 0.4A
- Nominal Power: 12 Watts

### Mounting

- Wall mount
- Desktop

### Certifications

- UL, CE, FCC, VCCI, RCM and UL/ CSA/ IEC
- Please refer to EDS-MD [User Guide](#) for certification details.
- 60601-1 4th Edition for Medical Electrical Equipment.

### Warranty

- 5-year limited warranty

## Ordering Information

Part Number	Description
EDSMG04P (New)	IoT Gateway for Medical Devices 4-PORT Serial, IEC 60601 (Regional power cord sold separately)
EDSMG08P (New)	IoT Gateway for Medical Devices 8-PORT Serial, IEC 60601 (Regional power cord sold separately)
EDSMG16P (New)	IoT Gateway for Medical Devices 16-PORT Serial, IEC 60601 (Regional power cord sold separately)
EDSOR04P-01 *	4-PORT Device Server, RoHS, IEC 60601
EDSOR08P-01 *	8-PORT Device Server, RoHS, IEC 60601
EDSOR16P-01 *	16-PORT Device Server , RoHS, IEC 60601

\* The Device Server can be upgraded to Device Gateway with the latest [firmware](#).

### Accessories

Part #	Description
200.2066A	RJ45 TO DB25M CABLE ADAPTER (DTE DEVICE)
200.2067A	RJ45 TO DB25F CABLE ADAPTER (DTE DEVICE)
200.2069A	RJ45 TO DB9M CABLE ADAPTER (DTE DEVICE)
200.2070A	RJ45 TO DB9F CABLE ADAPTER (DTE DEVICE)
200.2071	RJ45 TO DB9M CABLE ADAPTER (DCE DEVICE)
200.2072	RJ45 TO DB9F CABLE ADAPTER (DCE DEVICE)
200.2073	RJ45 TO DB25M CABLE ADAPTER (DCE DEVICE)
200.2074	RJ45 TO DB25F CABLE ADAPTER (DCE DEVICE)
500-153	CABLE; RJ45 LOOPBACK ADAPTER
ADP010104-01	CABLE; ROLLED SERIAL ADAPTER, 0.1M (0.33 FT)
ADP010106-01	CABLE; ROLLED SERIAL ADAPTER, 0.1M (0.33 FT), 6 IN. CONNECTOR

## Contact Information

### Americas

800.422.7055  
 sales@lantronix.com  
 http://www.lantronix.com  
 NASDAQ: LTRX

### Asia-Pacific

+852 3428.2338  
 asiapacific\_sales@lantronix.com  
 China: +86.21.6237.8868  
 India: +91 994-551-2488

### Europe

+31 (0) 76.52.3.674 4  
 eu\_sales@lantronix.com



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lantronix:](#)

[EDSOR04P-01](#) [EDSOR08P-01](#) [EDSOR16P-01](#)