请务必在使用敝司产品之前阅读。

/ 注意

- ■本产品目录所记载的内容为2016年10月之内容。因改良等原因,可能会不经预告而变更记载内容,所以请务必在使用前先确认最新的产品信息。未按照本产品目录所记载的内容或交货规格说明书使用敝司产品的,即便其致使使用设备发生损害、瑕疵等时,敝司也不承担任何责任,敬请悉知。
- 就规格相关的详细内容,敝司备有交货规格说明书,详情请向敝司咨询。
- 使用敝司产品时、请务必事先安装到设备之后、在实际使用的环境下进行评估和确认。
- ■本产品目录所中记载的产品可使用于一般电子设备 [音像设备、办公自动化设备、家电产品、办公设备、信息/通讯设备 (手机、电脑等)]。因此,若考虑将本产品目录所记载的产品使用于可能会直接危及生命或身体的设备 [运输用设备 (汽车驱动控制设备、火车控制设备、船舶控制设备等)、交通信号设备、防灾设备、医疗用器械、高公共性信息通信设备 (电话交换机以及电话、无线、广播电视等基站)]等时,请务必事先向敝司咨询。

另外,请勿将敝司产品使用于对安全性和可靠性要求较高的设备(航天设备、航空设备、原子能控制设备、海底设备、军事设备等)。

且即便属于一般电子设备,使用于对安全性和可靠性要求较高的设备、电路上时,敝司建议进行充分的安全评估, 并根据需要,在设计时追加保护电路等。

未经敝司的事先书面同意,把本产品目录中记载的产品使用于前述需要向敝司咨询的设备或敝司禁止使用的设备,从而给客户或第三方造成的损害的,敝司不承担任何责任,敬请悉知。

- 因使用敝司产品,发生第三方的知识产权等权利相关问题的,敝司不承担责任。另外,并不代表授予这些权利的实施权,敬请悉知。
- ■除非书面合同中另有规定,敝司产品的保证范围仅限于交付的敝司产品单品,并且就敝司产品的故障或瑕疵所导致的损害,敝司不承担任何责任,敬请悉知。
- ■本产品目录所记载的内容适用于从敝司营业所、销售子公司、销售代理店(即"正规销售渠道")购买的敝司产品,并不适用于从上述以外的渠道购买的敝司产品,敬请悉知。

■出口相关注意事项

本产品目录所记载的部分产品在出口时须事先确认《外汇和对外贸易法》以及美国出口管理的相关法规,并办理相关手续。如有不明之处,请向敝司咨询。

绕线型片状电感器(LB 系列)






回流焊

■型号标示法

※使用温度范围: -40~+105℃ (包含产品本身发热)



①类型

代码	类型
LB	绕线型片状电感器

②特性

代码	特性
ΔΔ	标准品
ΔC	大电流
ΔR	低Rdc
MF	低损耗

③尺寸 (L×W)

代码	外型 (inch)	尺寸 (L×W) [mm]
1608	1608 (0603)	1.6 × 0.8
2012	2012 (0805)	2.0 × 1.25
2016	2016 (0806)	2.0 × 1.6
2518	2518(1007)	2.5 × 1.8
3218	3218(1207)	3.2 × 1.8
3225	3225(1210)	3.2 × 2.5

④包装

代码	包装
Т	卷盘带装

⑤标称电感值

代码 (例)	标称电感值 [µH]
1R0	1.0
100	10
101	100

※R=小数点

	h ===+: 1	= /\	*
(6)H	息感	重/バ	叐

代码	电感量公差
K	±10%
М	±20%

⑦个别规格

代码	个别规格
Δ	标准品
R	低Rdc 品


⑧本公司管理记号

■标准外型尺寸 / 标准数量

推荐焊盘图案

实装上的注意

- ·请确认实装状态后使用。
- ·本产品焊法限定为回流焊法。



Туре	Α	В	С
1608	0.55	0.7	0.9
MF1608	0.55	0.7	1.0
2012	0.60	1.0	1.45
2016	0.60	1.0	1.8
2518	0.60	1.5	2.0
3218	0.85	1.7	2.0
3225	0.85	1.7	2.7

单位: mm

Type		W	Т		标准数量[pcs]		
Туре	L	VV	•	е	纸带	压纹带	
LB 1608	1.6±0.1 (0.063±0.004)	0.8±0.1 (0.031±0.004)	0.8 ± 0.1 (0.031±0.004)	0.35±0.15 (0.014±0.006)	4000	_	
LBMF1608	1.6±0.2 (0.063±0.008)	0.8 ± 0.2 (0.031 ± 0.008)			3000		
LB 2012 LB C2012 LB R2012	2.0±0.2 (0.079±0.008)	1.25±0.2 (0.049±0.008)	1.25±0.2 (0.049±0.008)	0.5±0.2 (0.020±0.008)	_	3000	
LB 2016 LB C2016	2.0±0.2 (0.079±0.008)	1.6±0.2 (0.063±0.008)	1.6±0.2 (0.063±0.008)	0.5±0.2 (0.020±0.008)	_	2000	
LB 2518 LB C2518 LB R2518	2.5±0.2 (0.098±0.008)	1.8±0.2 (0.071±0.008)	1.8±0.2 (0.071±0.008)	0.5±0.2 (0.020±0.008)	_	2000	
LB 3218	3.2±0.2 (0.126±0.008)	1.8±0.2 (0.071±0.008)	1.8±0.2 (0.071±0.008)	0.6±0.2 (0.024±0.008)	_	2000	
LB C3225	3.2±0.2 (0.126±0.008)	2.5±0.2 (0.098±0.008)	2.5±0.2 (0.098±0.008)	0.6±0.3 (0.024±0.012)	_	1000	

单位: mm (inch)

[▶] 由于篇幅有限,本产品目录中只记载了有代表性的产品规格,若考虑使用弊司产品时,请确认交货规格说明书中的详细规格。 另外,有关各产品的详细信息(特性图、可靠性信息、使用时的注意事项等),请参阅弊司网站(http://www.ty-top.com/)。

●1608(0603)型

● 1000 (0000) ±	■ 1000 (0000) ±								
型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz](min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]		
LB 1608T1R0M	RoHS	1.0	±20%	100	0.17	160	7.96		
LB 1608T2R2M	RoHS	2.2	±20%	80	0.33	115	7.96		
LB 1608T4R7M	RoHS	4.7	±20%	45	0.55	70	7.96		
LB 1608T8R2M	RoHS	8.2	±20%	32	0.70	60	2.52		
LB 1608T100M	RoHS	10	±20%	32	0.70	60	2.52		

型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz](min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LBMF1608T1R0M	RoHS	1.0	±20%	100	0.09	230	7.96
LBMF1608T2R2M	RoHS	2.2	±20%	80	0.17	160	7.96
LBMF1608T3R3M	RoHS	3.3	±20%	60	0.22	130	7.96
LBMF1608T4R7M	RoHS	4.7	±20%	45	0.24	110	7.96
LBMF1608T100[]	RoHS	10	±10%, ±20%	32	0.36	80	2.52
LBMF1608T220[]	RoHS	22	±10%, ±20%	16	1.0	50	2.52
LBMF1608T470∏	RoHS	47	±10%, ±20%	11	2.5	35	2.52

●2012(0805)型

●2012(0805)型							
型号	EHS	标称电感值 [µH]	电感量公差	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB 2012T1R0M	RoHS	1.0	±20%	100	0.15	405	7.96
LB 2012T2R2M	RoHS	2.2	±20%	80	0.23	260	7.96
LB 2012T3R3M	RoHS	3.3	±20%	55	0.30	235	7.96
LB 2012T4R7M	RoHS	4.7	±20%	45	0.40	190	7.96
LB 2012T6R8M	RoHS	6.8	±20%	38	0.47	135	7.96
LB 2012T100[]	RoHS	10	±10%, ±20%	32	0.70	120	2.52
LB 2012T100[R	RoHS	10	±10%, ±20%	32	0.50	120	2.52
LB 2012T150[]	RoHS	15	±10%, ±20%	28	1.3	100	2.52
LB 2012T220[]	RoHS	22	±10%, ±20%	16	1.7	80	2.52
LB 2012T470[]	RoHS	47	±10%, ±20%	11	3.7	60	2.52
LB 2012T680[]	RoHS	68	±10%, ±20%	10	6.0	50	2.52
LB 2012T101[]	RoHS	100	±10%, ±20%	8	7.0	45	0.796
型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB C2012T1R0M	RoHS	1.0	±20%	100	0.19	620	7.96
LB C2012T2R2M	RoHS	2.2	±20%	70	0.33	430	7.96
LB C2012T4R7M	RoHS	4.7	±20%	45	0.50	295	7.96
LB C2012T100[]	RoHS	10	±10%, ±20%	40	1.2	200	2.52
LB C2012T220[]	RoHS	22	±10%, ±20%	16	3.7	130	2.52
LB C2012T470[]	RoHS	47	±10%, ±20%	11	5.8	90	2.52
		标称电感值		白共振频率	直流申阳	额定由流	测试频率

型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB C2012T1R0M	RoHS	1.0	±20%	100	0.19	620	7.96
LB C2012T2R2M	RoHS	2.2	±20%	70	0.33	430	7.96
LB C2012T4R7M	RoHS	4.7	±20%	45	0.50	295	7.96
LB C2012T100[]	RoHS	10	±10%, ±20%	40	1.2	200	2.52
LB C2012T220[]	RoHS	22	±10%, ±20%	16	3.7	130	2.52
LB C2012T470[]	RoHS	47	±10%, ±20%	11	5.8	90	2.52

型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz](min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB R2012T1R0M	RoHS	1.0	±20%	100	0.07	400	7.96
LB R2012T2R2M	RoHS	2.2	±20%	80	0.13	260	7.96
LB R2012T4R7M	RoHS	4.7	±20%	45	0.24	200	7.96
LB R2012T100[]	RoHS	10	±10%, ±20%	32	0.36	150	2.52
LB R2012T220[]	RoHS	22	±10%, ±20%	16	1.0	100	2.52
LB R2012T470[]	RoHS	47	±10%, ±20%	11	1.7	75	2.52
LB R2012T101[]	RoHS	100	±10%, ±20%	8	4.0	50	0.796

●2016(0806)型

型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz](min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB 2016T1R0M	RoHS	1.0	±20%	100	0.09	490	7.96
LB 2016T1R5M	RoHS	1.5	±20%	80	0.11	380	7.96
LB 2016T2R2M	RoHS	2.2	±20%	70	0.13	375	7.96
LB 2016T3R3M	RoHS	3.3	±20%	55	0.20	285	7.96
LB 2016T4R7M	RoHS	4.7	±20%	45	0.25	225	7.96
LB 2016T6R8M	RoHS	6.8	±20%	38	0.35	200	7.96
LB 2016T100□	RoHS	10	±10%, ±20%	32	0.50	155	2.52
LB 2016T150□	RoHS	15	±10%, ±20%	28	0.70	130	2.52
LB 2016T220□	RoHS	22	±10%, ±20%	16	1.0	105	2.52
LB 2016T330□	RoHS	33	±10%, ±20%	14	1.7	85	2.52
LB 2016T470□	RoHS	47	±10%, ±20%	11	2.4	70	2.52
LB 2016T680[]	RoHS	68	±10%, ±20%	10	3.0	55	2.52
LB 2016T101[]	RoHS	100	±10%, ±20%	8	4.5	40	0.796

⁽注) 型号中的[]中标有电感值代码 (M或K)。

LB/LBC系列

※)额定电流: 直流叠加导致的电感降低在10%以内、以及温度上升20℃以内都满足的最大直流电流值。

※)额定电流:直流叠加导致的电感降低在20%以内、以及温度上升20℃以内都满足的最大直流电流值。

[▶]由于篇幅有限,本产品目录中只记载了有代表性的产品规格,若考虑使用弊司产品时,请确认交货规格说明书中的详细规格。 另外,有关各产品的详细信息(特性图、可靠性信息、使用时的注意事项等),请参阅弊司网站(http://www.ty-top.com/)。

型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB C2016T1R0M	RoHS	1.0	±20%	100	0.10	690	7.96
LB C2016T1R5M	RoHS	1.5	±20%	80	0.15	600	7.96
LB C2016T2R2M	RoHS	2.2	±20%	70	0.20	520	7.96
LB C2016T3R3M	RoHS	3.3	±20%	55	0.27	410	7.96
LB C2016T4R7M	RoHS	4.7	±20%	45	0.37	355	7.96
LB C2016T6R8M	RoHS	6.8	±20%	38	0.59	290	7.96
LB C2016T100[]	RoHS	10	±10%, ±20%	32	0.82	245	2.52
LB C2016T150[]	RoHS	15	±10%, ±20%	28	1.2	200	2.52
LB C2016T220[]	RoHS	22	±10%, ±20%	16	1.8	165	2.52
LB C2016T330[]	RoHS	33	±10%, ±20%	14	2.8	135	2.52
LB C2016T470[]	RoHS	47	±10%, ±20%	11	4.3	110	2.52
LB C2016T680[]	RoHS	68	±10%, ±20%	10	7.0	95	2.52
LB C2016T101	RoHS	100	±10%, ±20%	8	8.0	75	0.796

●2518(1007)型

型믁	EHS	标称电感值 [µH]	电感量公差	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB 2518T1R0M	RoHS	1.0	±20%	100	0.06	665	7.96
LB 2518T1R5M	RoHS	1.5	±20%	80	0.07	405	7.96
LB 2518T2R2M	RoHS	2.2	±20%	68	0.09	340	7.96
LB 2518T3R3M	RoHS	3.3	±20%	54	0.11	280	7.96
LB 2518T4R7M	RoHS	4.7	±20%	46	0.13	240	7.96
LB 2518T4R7MR	RoHS	4.7	±20%	46	0.10	235	7.96
LB 2518T6R8M	RoHS	6.8	±20%	38	0.15	195	7.96
LB 2518T100□	RoHS	10	±10%, ±20%	30	0.25	165	2.52
LB 2518T150□	RoHS	15	±10%, ±20%	23	0.32	145	2.52
LB 2518T220□	RoHS	22	±10%, ±20%	19	0.50	115	2.52
LB 2518T330□	RoHS	33	±10%, ±20%	15	0.70	95	2.52
LB 2518T470□	RoHS	47	±10%, ±20%	12	0.95	85	2.52
LB 2518T680□	RoHS	68	±10%, ±20%	9.5	1.5	70	2.52
LB 2518T101[]	RoHS	100	±10%, ±20%	9.0	2.1	60	0.796
LB 2518T151[]	RoHS	150	±10%, ±20%	7.0	3.2	45	0.796
LB 2518T221□	RoHS	220	±10%, ±20%	5.5	4.5	40	0.796
LB 2518T331□	RoHS	330	±10%, ±20%	4.5	7.0	30	0.796
LB 2518T471[]	RoHS	470	±10%, ±20%	3.5	10	25	0.796
LB 2518T681	RoHS	680	±10%, ±20%	3.0	17	20	0.796
LB 2518T102[]	RoHS	1000	±10%, ±20%	2.4	24	15	0.252

型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB C2518T1R0M	RoHS	1.0	±20%	100	0.08	775	7.96
LB C2518T1R0MR	RoHS	1.0	±20%	100	0.07	890	7.96
LB C2518T1R5M	RoHS	1.5	±20%	80	0.11	730	7.96
LB C2518T2R2M	RoHS	2.2	±20%	68	0.13	630	7.96
LB C2518T3R3M	RoHS	3.3	±20%	54	0.16	560	7.96
LB C2518T4R7M	RoHS	4.7	±20%	41	0.20	510	7.96
LB C2518T6R8M	RoHS	6.8	±20%	38	0.30	420	7.96
LB C2518T100[]	RoHS	10	±10%, ±20%	30	0.36	375	2.52
LB C2518T150[]	RoHS	15	±10%, ±20%	23	0.65	285	2.52
LB C2518T220[]	RoHS	22	±10%, ±20%	19	0.77	250	2.52
LB C2518T330[]	RoHS	33	±10%, ±20%	15	1.5	185	2.52
LB C2518T470[]	RoHS	47	±10%, ±20%	12	1.9	165	2.52
LB C2518T680[]	RoHS	68	±10%, ±20%	9.5	2.8	140	2.52
LB C2518T101[]	RoHS	100	±10%, ±20%	9.0	3.7	125	0.796
LB C2518T151[]	RoHS	150	±10%, ±20%	7.0	6.1	95	0.796
LB C2518T221[]	RoHS	220	±10%, ±20%	5.5	8.4	80	0.796
LB C2518T331[]	RoHS	330	±10%, ±20%	4.5	12.3	65	0.796
LB C2518T471[]	RoHS	470	±10%, ±20%	3.5	22	50	0.796
LB C2518T681[]	RoHS	680	±10%, ±20%	3.0	28	45	0.796

型号	EHS	标称电感值 [µH]	电感量公差	自共振频率 [MHz](min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB R2518T1R0M	RoHS	1.0	±20%	100	0.045	960	7.96
LB R2518T2R2M	RoHS	2.2	±20%	68	0.07	480	7.96
LB R2518T4R7M	RoHS	4.7	±20%	45	0.10	345	7.96
LB R2518T100[]	RoHS	10	±10%, ±20%	30	0.19	235	2.52
LB R2518T220□	RoHS	22	±10%, ±20%	19	0.44	175	2.52
LB R2518T470□	RoHS	47	±10%, ±20%	11	0.84	120	2.52
LB R2518T101[]	RoHS	100	±10%, ±20%	9	1.89	80	0.796

⁽注)型号中的[]中标有电感值代码 (M或K)。

LB/LBC系列

※)额定电流:直流叠加导致的电感降低在10%以内、以及温度上升20℃以内都满足的最大直流电流值。

LBR系列

※)额定电流: 直流叠加导致的电感降低在20%以内、以及温度上升20°C以内都满足的最大直流电流值。

[▶] 由于篇幅有限,本产品目录中只记载了有代表性的产品规格,若考虑使用弊司产品时,请确认交货规格说明书中的详细规格。 另外,有关各产品的详细信息(特性图、可靠性信息、使用时的注意事项等),请参阅弊司网站(http://www.ty-top.com/)。

■3218(1207)型

●3218(1207)至							
型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz](min.)	直流电阻 [Ω] (±30%)	额定电流 [mA](max.)	测试频率 [MHz]
LB 3218T1R0M	RoHS	1.0	±20%	100	0.06	1,075	7.96
LB 3218T1R5M	RoHS	1.5	±20%	80	0.07	860	7.96
LB 3218T2R2M	RoHS	2.2	±20%	68	0.09	775	7.96
LB 3218T3R3M	RoHS	3.3	±20%	54	0.11	560	7.96
LB 3218T4R7M	RoHS	4.7	±20%	41	0.13	550	7.96
LB 3218T6R8M	RoHS	6.8	±20%	40	0.17	380	7.96
LB 3218T100[]	RoHS	10	±10%, ±20%	30	0.25	340	2.52
LB 3218T150[]	RoHS	15	±10%, ±20%	25	0.32	300	2.52
LB 3218T220[]	RoHS	22	±10%, ±20%	19	0.49	255	2.52
LB 3218T330[]	RoHS	33	±10%, ±20%	15	0.75	215	2.52
LB 3218T470[]	RoHS	47	±10%, ±20%	12	0.92	205	2.52
LB 3218T680[]	RoHS	68	±10%, ±20%	11	1.49	145	2.52
LB 3218T101[]	RoHS	100	±10%, ±20%	8.0	2.4	140	0.796
LB 3218T151[]	RoHS	150	±10%, ±20%	7.0	3.2	105	0.796
LB 3218T221[]	RoHS	220	±10%, ±20%	5.0	5.4	80	0.796
LB 3218T331[]	RoHS	330	±10%, ±20%	4.0	7.0	65	0.796
LB 3218T471[]	RoHS	470	±10%, ±20%	3.5	14	54	0.796
LB 3218T681[]	RoHS	680	±10%, ±20%	3.0	17	45	0.796
LB 3218T102[]	RoHS	1000	±10%, ±20%	2.4	27	39	0.252

●3225(1210)型

型号	EHS	标称电感值 [μH]	电感量公差	自共振频率 [MHz](min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LB C3225T1R0MR	RoHS	1.0	±20%	250	0.055	1,100	0.1
LB C3225T1R5MR	RoHS	1.5	±20%	220	0.060	1,000	0.1
LB C3225T2R2MR	RoHS	2.2	±20%	190	0.080	930	0.1
LB C3225T3R3MR	RoHS	3.3	±20%	160	0.095	820	0.1
LB C3225T4R7MR	RoHS	4.7	±20%	70	0.100	680	0.1
LB C3225T6R8MR	RoHS	6.8	±20%	50	0.120	620	0.1
LB C3225T100□R	RoHS	10	±10%, ±20%	23	0.133	540	0.1
LB C3225T150□R	RoHS	15	±10%, ±20%	20	0.195	420	0.1
LB C3225T220□R	RoHS	22	±10%, ±20%	17	0.27	330	0.1
LB C3225T330□R	RoHS	33	±10%, ±20%	13	0.41	300	0.1
LB C3225T470□R	RoHS	47	±10%, ±20%	10	0.67	220	0.1
LB C3225T680□R	RoHS	68	±10%, ±20%	8	1.0	190	0.1
LB C3225T101□R	RoHS	100	±10%, ±20%	6	1.4	150	0.1

(注)型号中的[]中标有电感值代码 (M或K)。

LB/LBC系列 ※)额定电流:直流叠加导致的电感降低在10%以内、以及温度上升20℃以内都满足的最大直流电流值。


信号用绕线型片状电感器(LB 系列 M 型)





■型号标示法

※使用温度范围: -40~+105℃ (包含产品本身发热)



2	0	1	6	Т	1	0	0	J	Δ
	(2	2)		<u>(3)</u>		(4)		(<u>5</u>)	<u>(6)</u>

△=空格

①类型

代码	类型
LBM	信号用绕线型片状电感器

②尺寸 (L×W)

代码	尺寸 (L×W) [mm]
2016	2.0 × 1.6

3/2表				
代码	包装			
Т	卷盘带装			

④标称电感值

O 13-13 DOOLE	
代码 (例)	标称电感值 [µH]
R12	0.12
1R0	1.0
100	10
101	100


※R=小数点

⑤电感量公差

<u> </u>	
代码	电感量公差
۲	±5%

⑥本公司管理记号

■标准外型尺寸 / 标准数量




推荐焊盘图案

实装上的注意

- ·请确认实装状态后使用。 ·本产品焊法限定为回流焊法。

Туре	А	В	С
LBM2016	0.6	1.0	1.8
			单位: mm



Type		w T	т		标准数	量[pcs]
Туре	L	VV	· '	e	纸带	压纹带
LBM2016	2.0±0.2 (0.08±0.008)	1.6±0.2 (0.063±0.008)	1.6±0.2 (0.063±0.008)	0.5±0.2 (0.02±0.008)	_	2000

单位: mm (inch)

LBM2016 型

●LBM2016型								
型号	EHS	标称电感值 [μH]	电感量公差	Q值 (min.)	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA] (max.)	测试频率 [MHz]
LBM 2016TR12J	RoHS	0.12	±5%	30	600	0.13	610	25.2
LBM 2016TR15J	RoHS	0.15	±5%	30	550	0.15	570	25.2
LBM 2016TR18J	RoHS	0.18	±5%	30	500	0.15	560	25.2
LBM 2016TR22J	RoHS	0.22	±5%	30	450	0.20	520	25.2
LBM 2016TR27J	RoHS	0.27	±5%	30	425	0.21	510	25.2
LBM 2016TR33J	RoHS	0.33	±5%	30	400	0.21	490	25.2
LBM 2016TR39J	RoHS	0.39	±5%	30	375	0.26	440	25.2
LBM 2016TR47J	RoHS	0.47	±5%	30	350	0.26	430	25.2
LBM 2016TR56J	RoHS	0.56	±5%	30	300	0.29	410	25.2
LBM 2016TR68J	RoHS	0.68	±5%	30	270	0.32	400	25.2
LBM 2016TR82J	RoHS	0.82	±5%	30	250	0.34	390	25.2
LBM 2016T1R0J	RoHS	1.0	±5%	30	220	0.38	385	7.96
LBM 2016T1R2J	RoHS	1.2	±5%	30	180	0.41	370	7.96
LBM 2016T1R5J	RoHS	1.5	±5%	30	135	0.47	350	7.96
LBM 2016T1R8J	RoHS	1.8	±5%	30	100	0.48	345	7.96
LBM 2016T2R2J	RoHS	2.2	±5%	30	75	0.54	340	7.96
LBM 2016T2R7J	RoHS	2.7	±5%	30	55	0.59	310	7.96
LBM 2016T3R3J	RoHS	3.3	±5%	30	48	0.68	290	7.96
LBM 2016T3R9J	RoHS	3.9	±5%	30	43	0.74	275	7.96
LBM 2016T4R7J	RoHS	4.7	±5%	30	40	0.78	270	7.96
LBM 2016T5R6J	RoHS	5.6	±5%	25	36	0.88	255	7.96
LBM 2016T6R8J	RoHS	6.8	±5%	25	33	0.97	240	7.96
LBM 2016T8R2J	RoHS	8.2	±5%	25	30	1.1	225	7.96
LBM 2016T100J	RoHS	10	±5%	25	27	1.2	215	2.52
LBM 2016T120J	RoHS	12	±5%	25	23	1.4	200	2.52
LBM 2016T150J	RoHS	15	±5%	25	20	1.5	190	2.52
LBM 2016T180J	RoHS	18	±5%	25	18	2.5	150	2.52
LBM 2016T220J	RoHS	22	±5%	25	17	2.8	140	2.52
LBM 2016T270J	RoHS	27	±5%	25	16	3.2	130	2.52
LBM 2016T330J	RoHS	33	±5%	25	15	3.6	125	2.52
LBM 2016T390J	RoHS	39	±5%	20	14	3.9	120	2.52
LBM 2016T470J	RoHS	47	±5%	20	13	4.1	115	2.52
LBM 2016T560J	RoHS	56	±5%	20	12	5.9	95	2.52
LBM 2016T680J	RoHS	68	±5%	20	11	7.0	90	2.52
LBM 2016T820J	RoHS	82	±5%	20	10	7.7	85	2.52
LBM 2016T101J	RoHS	100	±5%	15	9.0	8.0	80	0.796
LBM 2016T151J	RoHS	150	±5%	15	6.5	13.5	69	0.796
LBM 2016T181J	RoHS	180	±5%	15	6.0	15	67	0.796
LBM 2016T221J	RoHS	220	±5%	15	5.5	18	65	0.796


^{※)}额定电流:直流叠加导致的电感降低在10%以内、以及温度上升22℃以内都满足的最大直流电流值。


WIRE-WOUND CHIP INDUCTORS (LB SERIES), WIRE-WOUND CHIP POWER INDUCTORS (CB SERIES), WIRE-WOUND CHIP INDUCTORS FOR SIGNAL LINES (LB SERIES M TYPE)


PACKAGING


1 Minimum Quantity Standard Quantity [pcs] Туре Paper Tape Embossed Tape LB C3225 1000 CB C3225 LB 3218 2000 LB R2518 LB C2518 2000 LB 2518 CB 2518 CB C2518 LBM2016 LB C2016 LB 2016 2000 CB 2016 CB C2016 LB 2012 LB C2012 LB R2012 3000 CB 2012 CB C2012 CB L2012 4000 LB 1608 4000 LBMF1608 3000 CBMF1608

②Tape material










This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).


Embossed Tape (0.315 inches wide)



т.	Chip	cavity	Insertion pitch	Tape th	nickness
Type	Α	В	F	Т	K
LBM2016	LBM2016 1.75±0.1 2.1±0.1 (0.069±0.004) (0.083±0.004)		4.0±0.1 (0.157±0.004)	0.3±0.05 (0.012±0.002)	1.9max. (0.075max.)
LB C3225 CB C3225	2.8±0.1 (0.110±0.004)	3.5±0.1 (0.138±0.004)	4.0±0.1 (0.157±0.004)	0.3±0.05 (0.012±0.002)	4.0max. (0.157max.)
LB 3218	2.1±0.1 (0.083±0.004)	3.5±0.1 (0.138±0.004)	4.0±0.1 (0.157±0.004)	0.3±0.05 (0.012±0.002)	2.2max. (0.087max.)
LB 2518 CB 2518 LB C2518 CB C2518 LB R2518	2.15±0.1 (0.085±0.004)	2.7±0.1 (0.106±0.004)	4.0±0.1 (0.157±0.004)	0.3±0.05 (0.012±0.002)	2.2max. (0.087max.)
LB 2016 CB 2016 LB C2016 CB C2016	1.75±0.1 (0.069±0.004)	2.1±0.1 (0.083±0.004)	4.0±0.1 (0.157±0.004)	0.3±0.05 (0.012±0.002)	1.9max. (0.075max.)
LB 2012 CB 2012 LB C2012 CB C2012 LB R2012	1.45±0.1 (0.057±0.004)	2.25±0.1 (0.089±0.004)	4.0±0.1 (0.157±0.004)	0.25±0.05 (0.010±0.002)	1.45max. (0.057max.)
LBMF1608 CBMF1608	1.1±0.1 (0.043±0.004)	1.9±0.1 (0.075±0.004)	4.0±0.1 (0.157±0.004)	0.25±0.05 (0.010±0.002)	1.2max. (0.047max.)

Unit:mm(inch)

Card board carrier tape (0.315 inches wide)




_	Chip	cavity	Insertion pitch	Tape thickness
Туре	Α	В	F	Т
OD 1 0010	1.55±0.1	2.3±0.1	4.0±0.1	1.1max.
CB L2012	(0.061 ± 0.004)	(0.091 ± 0.004)	(0.157 ± 0.004)	(0.043max.)
LD 1000	1.0±0.1	1.8±0.1	4.0±0.1	1.1max.
LB 1608	(0.039 ± 0.004)	(0.071 ± 0.004)	(0.157 ± 0.004)	(0.043max.)


Unit:mm(inch)

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

4 Leader and Blank Portion




⑤Reel Size



©Top Tape Strength

The top tape requires a peel-off force 0.2 to 0.7N in the direction of the arrow as illustrated below.

Pull direction



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

WIRE-WOUND CHIP INDUCTORS (LB SERIES), WIRE-WOUND CHIP POWER INDUCTORS (CB SERIES), WIRE-WOUND CHIP INDUCTORS FOR SIGNAL LINES (LB SERIES M TYPE)

■RELIABILITY DATA

1.Operating tempera	ature Range				
1.Operating tempera	LB, LBC, LBR, LBMF Series				
0 :0 17/1		- 40 1405°O(1 1 1' 15 15 1 1 1 1)			
Specified Value	CB, CBC, CBL, CBMF Series	-40 ~ $+105$ °C (Including self-generated heat)			
	LBM Series				
2. Storage Tempera	ture Range (after soldering)				
3 1	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series	- −40~+85°C			
	LBM Series	1			
Test Methods and Remarks	LB, CB Series: Please refer the term of "7. storage conditions" in precaution	ns.			
3.Rated Current					
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance			
	LBM Series]			
4.Inductance					
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance			
	LBM Series				
Test Methods and Remarks	LB·LBC·LBR·CB·CBC·CBL·LBMF·CBMF·LBM Series Measuring equipment :LCR Mater(HP4285A or its e Measuring frequency : Specified frequency	equivalent)			
5.Q		1			
	LB, LBC, LBR, LBMF Series	-			
Specified Value	CB, CBC, CBL, CBMF Series				
	LBM Series	Within the specified tolerance			
Test Methods and Remarks	LBM Series Measuring equipment : LCR Mater(HP4285A or its ed) Measuring frequency : Specified frequency	quivalent)			
CDO D : ::					
6.DC Resisitance	LD LDG LDB LDME G	I			
0 :5 1)/1	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance			
Test Methods and	LBM Series				
Remarks	I Measuring equipment: DC Ohmmeter (HIOKI 3227 or its equivalent)				
7.Self-Resonant Fro	equency				
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series	Within the specified tolerance			
	LBM Series	1			
Test Methods and Remarks					

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

8.Temperature Cha	8.Temperature Characteristic					
	LBM2016				Inductance change : Within±5%	
	LB1608	LB2012	LBR2012	CB2012		
	CBL2012	LB2016	CB2016	LB2518	Inductance change : Within±20%	
Specified Value	LBR2518	CB2518	LBC3225	CBC3225		
	LBMF1608	CBMF1608	LBC2016	CBC2016	1 Walt 050/	
	LBC2518	CBC2518	LB3218		Inductance change : Within±25%	
	LBC2012	CBC2012			Inductance change : Within±35%	
Test Methods and Remarks	Based on the inductance at 20°C and Measured at the ambient of −40°C∼+85°C.					

9.Rasistance to Fle	9.Rasistance to Flexure of Substrate				
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series	No damage.			
	LBM Series				
	Warp : 2mm(LB·LBC·LBR·CB·CBC·CBL·LBM·L	BMF · CBMF Series)			
Test Methods and Remarks	Test substrate : Glass epoxy-resin substrate Thickness : 0.8mm (LB1608 · LBMF1608 · CBMF1608) : 1.0mm (Others) Pressing jig 10 20 R340 Board R5 45±2mm 45±2mm 45±2mm				

10.Body Strength	10.Body Strength				
	LB, LBC, LBR, LBMF Series	No damage.			
Specified Value	CB, CBC, CBL, CBMF Series				
	LBM Series	1			
Test Methods and Remarks	LB·LBC·LBR·CB·CBC·CBL·LBM Applied force : 10N Duration : 10sec. LB1608·LBMF1608·CBMF1608 Applied force : 5N Duration : 10sec.				

11.Adhesion of terminal electrode				
	LB, LBC, LBR, LBMF Series			
Specified Value	CB, CBC, CBL, CBMF Series	No abnormality.		
	LBM Series			
Test Methods and Remarks	LB·LBC·LBR·CB·CBC·CBL·LBM·LBMF·CBMF Applied force : 10N to X and Y directions Duration : 5 sec. Test substrate : Printed board LB1608·CBMF1608·LBMF1608 Applied force : 5N to X and Y directions Duration : 5 sec. Test substrate : Printed board			

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

12.Resistance to vil	pration				
	LB, LBC, LBR, LBMF Series		Inductance change : Within±10%		
Specified Value	CB, CBC, CBL, CBMF Series		No significant abnormality in appearance.		
Specified value	LBM Series		Inductance change : Within±5% No significant abnormality in appearance.		
	LB·LBR·LBC·CB·CBC·CBL·LBM·LBMF·CBMF:				
			sted depending on the conditions of the following table.		
	Vibration Frequency	10~55Hz	1 1 100 (0)		
Test Methods and Remarks	Total Amplitude Sweeping Method	1.5mm (May not exceed acc 10Hz to 55Hz to 10Hz for 1	· · · · · · · · · · · · · · · · · · ·		
Remarks	Sweeping Method	X X	111111.		
	Time	 	on each X, Y, and Z axis.		
	Recovery : At least 2 hrs of	f recovery under the standard	condition after the test, followed by the measurement within 48 hrs.		
13.Drop test					
·	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series				
opcomou value	LBM Series				
	LDIVI Series				
140 11 1					
14.Solderability					
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series		At least 90% of surface of terminal electrode is covered by new		
	LBM Series				
	LB.LBC.LBR.CB.CBC.CBL				
Test Methods and	•	5±5℃			
Remarks		:0.5sec	adambana.		
	Flux : Me	thanol solution with 25% of o	союрпопу		
455 1					
15.Resistance to so	-				
	LB, LBC, LBR, LBMF Series		Inductance change : Within±10%		
Specified Value	CB, CBC, CBL, CBMF Series				
	LBM Series		Inductance change : Within±5%		
Test Methods and	LB.LBC.LBR.CB.CBC.CBL				
Remarks			temperature at 260 °C for 5sec.		
	Recovery : At least 2 hrs of	f recovery under the standard	condition after the test, followed by the measurement within 48 hrs.		
16.Resisitance to so	plvent				
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series		_		
	LBM Series				
	Solvent temperature : Ro	om temperature			
Test Methods and Remarks	•	propyl alcohol			
Remarks	Cleaning conditions : 90s	s. Immersion and cleaning.			
17.Thermal shock					
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series		Inductance change: Within±10%		
•	LBM Series		No significant abnormality in appearance.		
Test Methods and	LB·LBC·LBR·CB·CBC·CBL·LBM·LBMF·CBMF:				
Remarks	The given sample is soldered		ctance is measured after 100cycles of the following conditions.		
	Step Temperature (°)		
	1 -40±3	30±3			
	2 Room temperat				
	3 +85±2	30±3			
	0 100±2	00_0			
	4 Room temperat	ure Within 3	standard condition after the test, followed by the measurement within 48 hrs.		

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

18.Damp heat life test					
	LB, LBC, LBR, LBMF Series	Inductance change : Within±10%			
Specified Value	CB, CBC, CBL, CBMF Series	No significant abnormality in appearance.			
	LBM Series				
T . M	Temperature : 60±2°C				
Test Methods and Remarks	Humidity : 90~95%RH Duration : 1000 hrs				
		tandard condition after the test, followed by the measurement within 48 hrs.			
19.Loading under da	amp heat life test				
	LB, LBC, LBR, LBMF Series				
	CB, CBC, CBL, CBMF Series	Inductance change : Within±10% No significant abnormality in appearance.			
Specified Value	LBM Series	The digrimount abnormality in appearance.			
Test Methods and	Temperature : 60±2°C				
Remarks	Humidity : 90~95%RH				
	Duration : 1000 hrs Applied current : Rated current				
		tandard condition after the test, followed by the measurement within 48 hrs.			
20.High temperature	e life test				
	LB, LBC, LBR, LBMF Series	_			
Specified Value	CB, CBC, CBL, CBMF Series	Inductance change : Within±10%			
	LBM Series	No significant abnormality in appearance.			
Test Methods and	Temperature : 85±2°C				
Remarks	Duration : 1000 hrs	40 has			
	Recovery : At least 2 hrs of recovery under the s	tandard condition after the test, followed by the measurement within 48 hrs.			
21 Loading at high t	emperature life test				
ZT.Loading at High t		Inductance change : Within±10%			
	LB, LBC, LBR, LBMF Series	(LBC3225 Series: Within±20%)			
Specified Value		No significant abnormality in appearance.			
	CB, CBC, CBL, CBMF Series				
	LBM Series				
	Temperature : 85±2°C				
Test Methods and Remarks					
Remarks	Applied current : Rated current : Recovery : At least 2 hrs of recovery under the standard condition after the test, followed by the measurement within 48 hr				
22.Low temperature	e life test				
	LB, LBC, LBR, LBMF Series				
Specified Value	CB, CBC, CBL, CBMF Series	☐ Inductance change : Within±10% ☐ No significant abnormality in appearance.			
	LBM Series	The significant abhormanty in appearance.			
Test Methods and	Temperature : $-40\pm2^{\circ}$ C				
Remarks	Duration : 1000 hrs				
	Recovery : At least 2 hrs of recovery under the standard condition after the test, followed by the measurement within 48 hrs.				
23.Standard condition	on I				
	LB, LBC, LBR, LBMF Series	Standard test conditions Unless specified, Ambient temperature is 20±15°C and the Relative			
		humidity is $65\pm20\%$. If there is any doubt about the test results, further measurement shall be had within the following limits:			
Specified Value	CB, CBC, CBL, CBMF Series				
		Ambient Temperature: 20±2°C Relative humidity: 65±5% Inductance value is based on our standard measurement systems.			
	LBM Series				
-	I.				

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

WIRE-WOUND CHIP INDUCTORS (LB SERIES), WIRE-WOUND CHIP POWER INDUCTORS (CB SERIES), WIRE-WOUND CHIP INDUCTORS FOR SIGNAL LINES (LB SERIES M TYPE)

PRECAUTIONS

1. Circuit Design

♦Operating environment

Precautions

1. The products described in this specification are intended for use in general electronic equipment, (office supply equipment, telecommunications systems, measuring equipment, and household equipment). They are not intended for use in mission-critical equipment or systems requiring special quality and high reliability (traffic systems, safety equipment, aerospace systems, nuclear control systems and medical equipment including life-support systems,) where product failure might result in loss of life, injury or damage. For such uses, contact TAIYO YUDEN Sales Department in advance.

2. PCB Design

Precautions

Technical

considerations

◆Land pattern design

1. Please contact any of our offices for a land pattern, and refer to a recommended land pattern of a right figure or specifications.

ľ

PRECAUTIONS

[Recommended Land Patterns]

Surface Mounting

- · Mounting and soldering conditions should be checked beforehand.
- · Applicable soldering process to those products is reflow soldering only.

3. Considerations for automatic placement

Precautions

◆Adjustment of mounting machine

- 1. Excessive impact load should not be imposed on the products when mounting onto the PC boards.
- 2. Mounting and soldering conditions should be checked beforehand.

Technical considerations

1. When installing products, care should be taken not to apply distortion stress as it may deform the products.

4. Soldering

◆Reflow soldering(LB and CB Types)

Precautions

1. For reflow soldering with either leaded or lead-free solder, the profile specified in "point for controlling" is recommended.


◆Recommended conditions for using a soldering iron

1. Put the soldering iron on the land-pattern. Soldering iron's temperature - Below 350°C Duration-3 seconds or less. The soldering iron should not come in contact with inductor directly.

◆Reflow soldering(LB and CB Types)

1. Reflow profile

Technical considerations



- ◆Recommended conditions for using a soldering iron
- 1. Components can be damaged by excessive heat where soldering conditions exceed the specified range

5. Cleaning

Precautions

◆Cleaning conditions

Washing by supersonic waves shall be avoided.

Technical considerations

♦Cleaning conditions

If washed by supersonic waves, the products might be broken.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

6. Handling	
Precautions	 ◆Handling 1. Keep the inductors away from all magnets and magnetic objects. ◆Breakaway PC boards(splitting along perforations) 1. When splitting the PC board after mounting inductors, care should be taken not to give any stresses of deflection or twisting to the board. 2. Board separation should not be done manually, but by using the appropriate devices. ◆Mechanical considerations 1. Please do not give the inductors any excessive mechanical shocks.
Technical considerations	 ◆Handling 1. There is a case that a characteristic varies with magnetic influence. ◆Breakaway PC boards(splitting along perforations) 1. Planning pattern configurations and the position of products should be carefully performed to minimize stress. ◆Mechanical considerations 1. There is a case to be damaged by a mechanical shock.

多层片状电感器(LK 系列)





※LK1005除外

■型号标示法

※使用温度范围: -40~+85℃

△=空格



①类型

· 大王				
代码	类型			
LK△	多层片状电感器			

②尺寸 (I×W)

⊕/₹3 (LVV/		
代码	外型 (inch)	尺寸 (L×W) [mm]
1005	1005(0402)	1.0 × 0.5
1608	1608 (0603)	1.6 × 0.8
2125	2125(0805)	2.0 × 1.25

3标称电感值

代码 (例)	标称电感值 [µH]
47N	0.047
R10	0.1
1R0	1.0
100	10
N1/- 1	•

※R=小数点 ※N=nH 的小数点 ④电感量公差

代码	电感量公差
K	±10%
М	±20%


⑤包装

代码	包装
-T	卷盘带装

⑥本公司管理记号

<u> </u>	
代码	本公司管理记号
Δ	标准品

■标准外型尺寸 / 标准数量



Туре	L	W	Т	е	标准数量[pcs]	
Type					纸带	压纹带
LK 1005	1.00±0.05	0.50 ± 0.05	0.50 ± 0.05	0.25±0.10	10000	_
(0402)	(0.039 ± 0.002)	(0.020 ± 0.002)	(0.020 ± 0.002)	(0.010 ± 0.004)		
LK 1608	1.6±0.15	0.8±0.15	0.8±0.15	0.3 ± 0.2	4000	_
(0603)	(0.063 ± 0.006)	(0.031 ± 0.006)	(0.031 ± 0.006)	(0.012 ± 0.008)		
	2.0+0.3/-0.1	1.25±0.2	0.85±0.2	0.5 ± 0.3	4000	
LK 2125	(0.079 + 0.012 / -0.004)	(0.049 ± 0.008)	(0.033 ± 0.008)	(0.020 ± 0.012)	4000	_
(0805)	2.0+0.3/-0.1	1.25±0.2	1.25±0.2	0.5 ± 0.3		2000
	(0.079 + 0.012 / -0.004)	(0.049 ± 0.008)	(0.049 ± 0.008)	(0.020 ± 0.012)	_	2000

单位: mm (inch)

[▶] 由于篇幅有限,本产品目录中只记载了有代表性的产品规格,若考虑使用弊司产品时,请确认交货规格说明书中的详细规格。 另外,有关各产品的详细信息(特性图、可靠性信息、使用时的注意事项等),请参阅弊司网站(http://www.ty-top.com/)。

LK1005

型号	EHS	标称电感值 [µH]	电感量公差	Q值 (min.)	自共振频率 [MHz](min.)	直流电阻 [Ω] (max.)	额定电流 [mA] (max.)	测试频率 [MHz]	厚度 [mm]
LK 1005 R12□-T	RoHS	0.12	±10%, ±20%	10	180	0.59	25	25	0.50 ±0.05
LK 1005 R15∏-T	RoHS	0.15	±10%, ±20%	10	165	0.63	25	25	0.50 ±0.05
LK 1005 R18∏-T	RoHS	0.18	±10%, ±20%	10	150	0.76	25	25	0.50 ±0.05
LK 1005 R22∏-T	RoHS	0.22	±10%, ±20%	10	135	0.79	25	25	0.50 ±0.05
LK 1005 R27 ☐-T	RoHS	0.27	±10%, ±20%	10	120	0.91	25	25	0.50 ±0.05
LK 1005 R33∏-T	RoHS	0.33	±10%, ±20%	10	105	1.05	25	25	0.50 ± 0.05
LK 1005 R39∏-T	RoHS	0.39	±10%, ±20%	20	85	0.41	20	10	0.50 ±0.05
LK 1005 R47□-T	RoHS	0.47	±10%, ±20%	20	80	0.42	20	10	0.50 ±0.05
LK 1005 R56 ☐-T	RoHS	0.56	±10%, ±20%	20	75	0.47	20	10	0.50 ± 0.05
LK 1005 R68□-T	RoHS	0.68	±10%, ±20%	20	70	0.55	20	10	0.50 ± 0.05
LK 1005 R82□-T	RoHS	0.82	±10%, ±20%	20	65	0.59	20	10	0.50 ±0.05
LK 1005 1R0□-T	RoHS	1.0	±10%, ±20%	20	60	0.64	20	10	0.50 ±0.05
LK 1005 1R2□-T	RoHS	1.2	±10%, ±20%	20	55	0.79	20	10	0.50 ±0.05
LK 1005 1R5∏-T	RoHS	1.5	±10%, ±20%	20	50	0.95	20	10	0.50 ±0.05
LK 1005 1R8□-T	R₀HS	1.8	±10%, ±20%	20	45	1.16	20	10	0.50 ±0.05
LK 1005 2R2□-T	R₀HS	2.2	±10%, ±20%	20	40	1.15	20	10	0.50 ±0.05

※型号中的[]中标有电感值公差。

LK1608

LK1608									
型号	EHS	标称电感值 [μH]	电感量公差	Q值 (min.)	自共振频率 [MHz] (min.)	直流电阻 [Ω] (max.)	额定电流 [mA] (max.)	测试频率 [MHz]	厚度 [mm]
LK 1608 47NM-T	RoHS	0.047	±20%	10	260	0.20	150	50	0.80 ±0.15
LK 1608 68NM-T	RoHS	0.068	±20%	10	250	0.30	150	50	0.80 ±0.15
LK 1608 82NM-T	RoHS	0.082	±20%	10	245	0.30	150	50	0.80 ±0.15
LK 1608 R10[]-T	RoHS	0.10	±10%, ±20%	15	240	0.35	150	25	0.80 ±0.15
LK 1608 R12[]-T	RoHS	0.12	±10%, ±20%	15	205	0.40	150	25	0.80 ±0.15
LK 1608 R15[]-T	RoHS	0.15	±10%, ±20%	15	180	0.45	150	25	0.80 ±0.15
LK 1608 R18[]-T	RoHS	0.18	±10%, ±20%	15	165	0.50	100	25	0.80 ±0.15
LK 1608 R22[]-T	RoHS	0.22	±10%, ±20%	15	150	0.55	100	25	0.80 ±0.15
LK 1608 R27∏-T	RoHS	0.27	±10%, ±20%	15	136	0.80	100	25	0.80 ±0.15
LK 1608 R33[]-T	RoHS	0.33	±10%, ±20%	15	125	0.75	80	25	0.80 ±0.15
LK 1608 R39∏-T	RoHS	0.39	±10%, ±20%	15	110	0.85	80	25	0.80 ±0.15
LK 1608 R47[]-T	RoHS	0.47	±10%, ±20%	15	105	0.95	80	25	0.80 ±0.15
LK 1608 R56∏-T	RoHS	0.56	±10%, ±20%	15	95	1.05	80	25	0.80 ±0.15
LK 1608 R68∏-T	RoHS	0.68	±10%, ±20%	15	80	1.25	40	25	0.80 ±0.15
LK 1608 R82∏-T	RoHS	0.82	±10%, ±20%	15	75	1.40	40	25	0.80 ±0.15
LK 1608 1R0[]-T	RoHS	1.0	±10%, ±20%	35	70	0.60	40	10	0.80 ±0.15
LK 1608 1R2∏-T	RoHS	1.2	±10%, ±20%	35	60	0.65	40	10	0.80 ±0.15
LK 1608 1R5[]-T	RoHS	1.5	±10%, ±20%	35	55	0.70	40	10	0.80 ±0.15
LK 1608 1R8[]-T	RoHS	1.8	±10%, ±20%	35	50	0.95	40	10	0.80 ±0.15
LK 1608 2R2[]-T	RoHS	2.2	±10%, ±20%	35	45	1.00	30	10	0.80 ±0.15
LK 1608 2R7[]-T	RoHS	2.7	±10%, ±20%	35	40	1.15	30	10	0.80 ±0.15
LK 1608 3R3[]-T	RoHS	3.3	±10%, ±20%	35	38	1.30	30	10	0.80 ±0.15
LK 1608 3R9∏-T	RoHS	3.9	±10%, ±20%	35	36	1.50	30	10	0.80 ±0.15
LK 1608 4R7[]-T	RoHS	4.7	±10%, ±20%	35	33	1.60	30	10	0.80 ±0.15
LK 1608 5R6∏-T	RoHS	5.6	±10%, ±20%	35	22	1.10	10	4	0.80 ±0.15
LK 1608 6R8∏-T	RoHS	6.8	±10%, ±20%	35	20	1.30	10	4	0.80 ±0.15
LK 1608 8R2[]-T	RoHS	8.2	±10%, ±20%	35	18	1.50	10	4	0.80 ±0.15
LK 1608 100∏-T	RoHS	10	±10%, ±20%	35	17	1.70	10	2	0.80 ±0.15
LK 1608 120∏-T	RoHS	12	±10%, ±20%	35	15	1.80	10	2	0.80 ±0.15
LK 1608 150M-T	RoHS	15	±20%	20	14	1.50	1	1	0.80 ±0.15
LK 1608 180M-T	RoHS	18	±20%	20	13	1.60	1	1	0.80 ±0.15
LK 1608 220M-T	RoHS	22	±20%	20	11	1.70	1	1	0.80 ±0.15
LK 1608 270M-T	RoHS	27	±20%	20	10	1.80	1	1	0.80 ±0.15
LK 1608 330M-T	RoHS	33	±20%	20	9	2.20	1	1	0.80 ±0.15
ショロナかロナニナカ	# はハギ								

※型号中的[]中标有电感值公差。

[▶] 由于篇幅有限,本产品目录中只记载了有代表性的产品规格,若考虑使用弊司产品时,请确认交货规格说明书中的详细规格。 另外,有关各产品的详细信息(特性图、可靠性信息、使用时的注意事项等),请参阅弊司网站(http://www.ty-top.com/)。

LK2125

LK2125									
型号	EHS	标称电感值 [µH]	电感量公差	Q值 (min.)	自共振频率 [MHz](min.)	直流电阻 [Ω] (max.)	额定电流 [mA] (max.)	测试频率 [MHz]	厚度 [mm]
LK 2125 47NM-T	RoHS	0.047	±20%	15	320	0.10	300	50	0.85 ± 0.2
LK 2125 68NM-T	RoHS	0.068	±20%	15	280	0.15	300	50	0.85 ± 0.2
LK 2125 82NM-T	RoHS	0.082	±20%	15	255	0.20	300	50	0.85 ±0.2
LK 2125 R10□-T	RoHS	0.10	±10%, ±20%	20	235	0.15	270	25	0.85 ±0.2
LK 2125 R12[]-T	RoHS	0.12	±10%, ±20%	20	220	0.20	270	25	0.85 ± 0.2
LK 2125 R15∏-T	RoHS	0.15	±10%, ±20%	20	200	0.20	270	25	0.85 ± 0.2
LK 2125 R18∏-T	RoHS	0.18	±10%, ±20%	20	185	0.25	270	25	0.85 ±0.2
LK 2125 R22[]-T	RoHS	0.22	±10%, ±20%	20	170	0.30	250	25	0.85 ± 0.2
LK 2125 R27[]-T	RoHS	0.27	±10%, ±20%	20	150	0.35	250	25	0.85 ±0.2
LK 2125 R33∏-T	RoHS	0.33	±10%, ±20%	20	145	0.40	250	25	0.85 ± 0.2
LK 2125 R39[]-T	RoHS	0.39	±10%, ±20%	25	135	0.45	200	25	0.85 ±0.2
LK 2125 R47∏-T	RoHS	0.47	±10%, ±20%	25	125	0.50	200	25	1.25 ±0.2
LK 2125 R56∏-T	RoHS	0.56	±10%, ±20%	25	115	0.55	150	25	1.25 ± 0.2
LK 2125 R68∏-T	RoHS	0.68	±10%, ±20%	25	105	0.60	150	25	1.25 ±0.2
LK 2125 R82∏-T	RoHS	0.82	±10%, ±20%	25	100	0.65	150	25	1.25 ±0.2
LK 2125 1R0[]-T	RoHS	1.0	±10%, ±20%	45	75	0.30	80	10	0.85 ± 0.2
LK 2125 1R2[]-T	RoHS	1.2	±10%, ±20%	45	65	0.35	80	10	0.85 ±0.2
LK 2125 1R5∏-T	RoHS	1.5	±10%, ±20%	45	60	0.40	80	10	0.85 ±0.2
LK 2125 1R8[]-T	RoHS	1.8	±10%, ±20%	45	55	0.45	80	10	0.85 ± 0.2
LK 2125 2R2[]-T	RoHS	2.2	±10%, ±20%	45	50	0.50	50	10	0.85 ± 0.2
LK 2125 2R7∏-T	RoHS	2.7	±10%, ±20%	45	45	0.55	50	10	1.25 ±0.2
LK 2125 3R3[]-T	RoHS	3.3	±10%, ±20%	45	41	0.60	50	10	1.25 ±0.2
LK 2125 3R9∏-T	RoHS	3.9	±10%, ±20%	45	38	0.70	30	10	1.25 ±0.2
LK 2125 4R7[]-T	RoHS	4.7	±10%, ±20%	45	35	0.70	30	10	1.25 ± 0.2
LK 2125 5R6∏-T	RoHS	5.6	±10%, ±20%	50	32	0.60	15	4	1.25 ±0.2
LK 2125 6R8∏-T	RoHS	6.8	±10%, ±20%	50	29	0.70	15	4	1.25 ±0.2
LK 2125 8R2[]-T	RoHS	8.2	±10%, ±20%	50	26	0.70	15	4	1.25 ±0.2
LK 2125 100 -T	RoHS	10	±10%, ±20%	50	24	0.80	15	2	1.25 ± 0.2
LK 2125 120∏-T	RoHS	12	±10%, ±20%	50	22	0.90	15	2	1.25 ±0.2
LK 2125 150M-T	RoHS	15	±20%	30	19	0.70	5	1	1.25 ±0.2
LK 2125 180M-T	RoHS	18	±20%	30	18	0.80	5	1	1.25 ±0.2
LK 2125 220M-T	RoHS	22	±20%	30	16	0.90	5	1	1.25 ±0.2
LK 2125 270M-T	RoHS	27	±20%	30	14	1.00	5	1	1.25 ±0.2
LK 2125 330M-T	RoHS	33	±20%	30	13	1.10	5	0.4	1.25 ±0.2

多层片状电感器(CK 系列/CK 系列 S 型)





波峰焊

峰焊 回流炸

■型号标示法

※使用温度范围: -40~+85℃

△=空格



①类型

代码	类型
CK△	多层片状电感器
CKS	多层户从电感 格

②尺寸 (L×W)

<u> </u>		
代码	外型 (inch)	尺寸 (L×W) [mm]
1608	1608 (0603)	1.6×0.8
2125	2125 (0805)	2.0 × 1.25

③标称电感值

代码 (例)	标称电感值 [µH]
1R0	1.0
100	10

※R=小数点

④电感量公差

0.0.1	
代码	电感量公差
М	±20%


⑤包装

代码	包装
_T	卷盘带装

⑥本公司管理记号

9个公司日廷的	っ
代码	本公司管理记号
Δ	标准品

■标准外型尺寸 / 标准数量



T		w	т.		标准数量 [pcs]		
Туре	L	VV	'	e	纸带	压纹带	
CK 1608	1.6±0.15	0.8±0.15	0.8±0.15	0.3±0.2	4000	_	
(0603)	(0.063 ± 0.006)	(0.031 ± 0.006)	(0.031 ± 0.006)	(0.012 ± 0.008)	4000		
01/ 0105	2.0+0.3/-0.1	1.25±0.2	0.85±0.2	0.5±0.3	4000		
CK 2125	(0.079+0.012/-0.004)	(0.049 ± 0.008)	(0.033 ± 0.008)	(0.020 ± 0.012)	4000	_	
CKS2125 (0805)	2.0+0.3/-0.1	1.25±0.2	1.25±0.2	0.5±0.3	_	2000	
(0000)	(0.079+0.012/-0.004)	$(0.079 + 0.012 / -0.004)$ (0.049 ± 0.008)		(0.020 ± 0.012)	_	2000	

单位: mm (inch)

■型号一览

CK1608

型号	EHS	标称电感值 [µH]	电感量公差	自共振频率 [MHz] (min.)	直流电阻 [Ω] (±30%)	额定电流 [mA](max.)	测试频率 [MHz]	厚度 [mm]
CK 1608 4R7M-T	RoHS	4.7	±20%	25	0.45	60	4	0.80 ± 0.15
CK 1608 100M-T	RoHS	10.0	±20%	17	0.85	50	2	0.80 ±0.15

CK2125

● O1(2120									
型号	EHS	标称电感值 [µH]	电感量公差	自共振频率 [MHz] (min.)	直流电源 (max.)	且 [Ω] (typ.)	额定电流 [mA](max.)	测试频率 [MHz]	厚度 [mm]
CK 2125 R10M-T	RoHS	0.10	±20%	235	0.16	0.08	500	25	0.85 ±0.2
CK 2125 R15M-T	RoHS	0.15	±20%	200	0.20	0.13	500	25	0.85 ±0.2
CK 2125 R22M-T	RoHS	0.22	±20%	170	0.23	0.16	400	25	0.85 ± 0.2
CK 2125 R33M-T	RoHS	0.33	±20%	145	0.28	0.21	400	25	0.85 ± 0.2
CK 2125 R47M-T	RoHS	0.47	±20%	125	0.32	0.25	400	25	1.25 ±0.2
CK 2125 R68M-T	RoHS	0.68	±20%	105	0.45	0.35	300	25	1.25 ±0.2
CK 2125 1R0M-T	RoHS	1.0	±20%	75	0.26	0.19	220	10	0.85 ±0.2
CK 2125 1R5M-T	RoHS	1.5	±20%	60	0.28	0.23	170	10	0.85 ±0.2
CK 2125 2R2M-T	RoHS	2.2	±20%	50	0.35	0.26	150	10	0.85 ±0.2
CK 2125 3R3M-T	RoHS	3.3	±20%	41	0.43	0.38	130	10	1.25 ±0.2
CK 2125 4R7M-T	RoHS	4.7	±20%	35	0.48	0.44	120	10	1.25 ±0.2
CK 2125 6R8M-T	RoHS	6.8	±20%	29	0.52	0.39	70	4	1.25 ±0.2
CK 2125 100M-T	RoHS	10.0	±20%	24	0.65	0.55	60	2	1.25 ±0.2

OKS2125

型号	EHS	标称电感值	电感量公差	自共振频率 「MHz] (min.)	直流电	阻 [Ω]	额定电流 [mA] (max.)	测试频率 [MHz]	厚度 [mm]
		[µH] [MHz]		[171112] (111111.)	(max.) (typ.)		[IIIA] (IIIax.)	[IVITIZ]	[IIIIII]
CKS2125 1R0M-T	RoHS	1.0	±20%	75	0.12	0.09	280	10	0.85 ± 0.2
CKS2125 2R2M-T	RoHS	2.2	±20%	50	0.19	0.15	170	10	0.85 ±0.2
CKS2125 4R7M-T	RoHS	4.7	±20%	35	0.30	0.25	130	10	1.25 ±0.2
CKS2125 100M-T	RoHS	10.0	±20%	24	0.52	0.40	110	2	1.25 ±0.2

[▶] 由于篇幅有限,本产品目录中只记载了有代表性的产品规格,若考虑使用弊司产品时,请确认交货规格说明书中的详细规格。 另外,有关各产品的详细信息(特性图、可靠性信息、使用时的注意事项等),请参阅弊司网站(http://www.ty-top.com/)。

Multilayer chip inductors Multilayer chip inductors for high frequency, Multilayer chip bead inductors Multilayer common mode choke coils (MC series F type) Metal Multilayer Chip Power Inductors (MCOILTM MC series)


PACKAGING

1 Minimum Quantity


Tape & Reel Packaging	S		
Tuna	Thickness	Standard Q	uantity [pcs]
Type	mm(inch)	Paper Tape	Embossed Tape
CK1608(0603)	0.8 (0.031)	4000	_
OK010E (000E)	0.85(0.033)	4000	_
CK2125 (0805)	1.25(0.049)	_	2000
OKC040E (000E)	0.85(0.033)	4000	_
CKS2125(0805)	1.25(0.049)	_	2000
CKP1608 (0603)	0.8 (0.031)	4000	_
CKP2012 (0805)	0.9 (0.035)	_	3000
CKP2016 (0806)	0.9 (0.035)	_	3000
	0.7 (0.028)	_	3000
CKP2520(1008)	0.9 (0.035)	_	3000
	1.1 (0.043)	_	2000
NM2012 (0805)	0.9 (0.035)	_	3000
-	0.9 (0.035)	_	3000
NM2520(1008)	1.1 (0.043)	_	2000
LK1005(0402)	0.5 (0.020)	10000	_
LK1608(0603)	0.8 (0.031)	4000	_
	0.85(0.033)	4000	_
LK2125(0805)	1.25(0.049)		2000
HK0603(0201)	0.3 (0.012)	15000	_
HK1005 (0402)	0.5 (0.020)	10000	_
HK1608 (0603)	0.8 (0.031)	4000	_
111(1000(0000)	0.85(0.033)	-	4000
HK2125(0805)	1.0 (0.039)	_	3000
HKQ0402(01005)	0.2 (0.008)	20000	40000
HKQ0603W(0201)	0.3 (0.012)	15000	-
HKQ0603C (0201)	0.3 (0.012)	15000	_
HKQ0603S (0201)	0.3 (0.012)	15000	_
HKQ0603U(0201)	0.3 (0.012)	15000	_
AQ105(0402)	0.5 (0.020)	10000	<u> </u>
BK0402 (01005)	0.3 (0.020)	20000	_
BK0603 (0201)	0.2 (0.008)	15000	<u> </u>
BK1005 (0402)			_
	0.5 (0.020)	10000	_
BKH0603(0201)	0.3 (0.012)	15000	_
BKH1005(0402)	0.5 (0.020)	10000	_
BK1608 (0603)	0.8 (0.031)	4000	_
BK2125(0805)	0.85(0.033)	4000	
DI(0010 (0004)	1.25(0.049)	4000	2000
BK2010(0804)	0.45(0.018)	4000	4000
BK3216(1206)	0.8 (0.031)	-	4000
BKP0402 (01005)	0.2 (0.008)	20000	_
BKP0603 (0201)	0.3 (0.012)	15000	_
BKP1005 (0402)	0.5 (0.020)	10000	_
BKP1608 (0603)	0.8 (0.031)	4000	_
BKP2125(0805)	0.85 (0.033)	4000	_
MCF0605 (0202)	0.3 (0.012)	15000	_
MCF0806 (0302)	0.4 (0.016)	_	10000
MCF1210 (0504)	0.55(0.022)	_	5000
MCF2010 (0804)	0.45(0.018)	_	4000
MCFK1608(0603)	0.6 (0.024)	4000	_
MCFE1608 (0603)	0.65 (0.026)	4000	_
MCHK2012(0806)	0.8 (0.031)	4000	_
MCKK2012 (0805)	1.0 (0.039)	-	3000


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Taping material




BK	0402
BK	0603
BK	1005
BK	1608
BK	2125
BK	2010
BKP	0402
BKP	0603
BKP	1005
BKP	1608
BKP	2125
BKH	0603
BKH	1005
MCF	0605
MC	1608
MC	2012






2125
3216
0806
1210
2010
2012



Taping Dimensions




This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

_	Thickness	Chip	cavity	Insertion Pitch	Tape Thickness
Туре	mm(inch)	А	В	F	Т
CK1608(0603)	0.8 (0.031)	1.0±0.2	1.8±0.2	4.0±0.1	1.1max
OK1000 (0000)	0.0 (0.001)	(0.039 ± 0.008)	(0.071 ± 0.008)	(0.157 ± 0.004)	(0.043max)
CK2125(0805)	0.85(0.033)	1.5±0.2	2.3±0.2	4.0±0.1	1.1max
		(0.059±0.008)	(0.091 ± 0.008)	(0.157±0.004)	(0.043max)
CKS2125 (0805)	0.85 (0.033)	1.5±0.2 (0.059±0.008)	2.3±0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	1.1max (0.043max)
		1.0±0.2	1.8±0.2	4.0±0.1	1.1max
CKP1608(0603)	0.8 (0.031)	(0.039 ± 0.008)	(0.071 ± 0.008)	(0.157 ± 0.004)	(0.043max)
	(2.222)	0.65±0.1	1.15±0.1	2.0±0.05	0.8max
LK1005(0402)	0.5 (0.020)	(0.026 ± 0.004)	(0.045 ± 0.004)	(0.079 ± 0.002)	(0.031max)
LK1608 (0603)	0.8 (0.031)	1.0±0.2	1.8±0.2	4.0±0.1	1.1max
LK1006(0003)	0.6 (0.031)	(0.039 ± 0.008)	(0.071 ± 0.008)	(0.157±0.004)	(0.043max)
LK2125(0805)	0.85(0.033)	1.5±0.2	2.3±0.2	4.0±0.1	1.1max
ERE120 (0000)	0.00 (0.000)	(0.059 ± 0.008)	(0.091 ± 0.008)	(0.157 ± 0.004)	(0.043max)
HK0603(0201)	0.3 (0.012)	0.40±0.06	0.70±0.06	2.0±0.05	0.45max
		(0.016±0.002)	(0.028±0.002)	(0.079±0.002)	(0.018max)
HK1005(0402)	0.5 (0.020)	0.65 ± 0.1	1.15±0.1	2.0±0.05	0.8max (0.031max)
		(0.026±0.004) 1.0±0.2	(0.045±0.004) 1.8±0.2	(0.079±0.002) 4.0±0.1	(0.031max) 1.1max
HK1608(0603)	0.8 (0.031)	(0.039 ± 0.008)	(0.071 ± 0.008)	(0.157 ± 0.004)	(0.043max)
		0.25±0.04	0.45±0.04	2.0±0.05	0.36max
HKQ0402(01005)	0.2 (0.008)	(0.010 ± 0.002)	(0.018 ± 0.002)	(0.079 ± 0.002)	(0.014max)
LU(0.0000::/(0.0)	0.0 (2.7.1.)	0.40±0.06	0.70±0.06	2.0±0.05	0.45max
HKQ0603W(0201)	0.3 (0.012)	(0.016 ± 0.002)	(0.028 ± 0.002)	(0.079 ± 0.002)	(0.018max)
LIKO06020 (0201)	0.2 (0.010)	0.40±0.06	0.70±0.06	2.0±0.05	0.45max
HKQ0603C(0201)	0.3 (0.012)	(0.016 ± 0.002)	(0.028 ± 0.002)	(0.079 ± 0.002)	(0.018max)
HKQ0603S(0201)	0.3 (0.012)	0.40 ± 0.06	0.70±0.06	2.0±0.05	0.45max
111(400000 (0201)	0.0 (0.012)	(0.016±0.002)	(0.028 ± 0.002)	(0.079 ± 0.002)	(0.018max)
HKQ0603U(0201)	0.3 (0.012)	0.40±0.06	0.70±0.06	2.0±0.05	0.45max
		(0.016±0.002)	(0.028±0.002)	(0.079±0.002)	(0.018max)
AQ105(0402)	0.5 (0.020)	0.75±0.1	1.15±0.1	2.0±0.05	0.8max
		(0.030 ± 0.004) 0.25 ± 0.04	(0.045±0.004) 0.45±0.04	(0.079±0.002) 2.0±0.05	(0.031max) 0.36max
BK0402(01005)	0.2 (0.008)	(0.010±0.002)	(0.018±0.002)	(0.079 ± 0.002)	(0.014max)
		0.40±0.06	0.70±0.06	2.0±0.05	0.45max
BK0603(0201)	0.3 (0.012)	(0.016±0.002)	(0.028 ± 0.002)	(0.079 ± 0.002)	(0.018max)
DI(1005(0400)	2.5 (2.222)	0.65±0.1	1.15±0.1	2.0±0.05	0.8max
BK1005(0402)	0.5 (0.020)	(0.026 ± 0.004)	(0.045 ± 0.004)	(0.079 ± 0.002)	(0.031max)
BK1608(0603)	0.8 (0.031)	1.0±0.2	1.8±0.2	4.0±0.1	1.1max
BK1008(0003)	0.6 (0.031)	(0.039 ± 0.008)	(0.071 ± 0.008)	(0.157±0.004)	(0.043max)
BK2125(0805)	0.85(0.033)	1.5±0.2	2.3±0.2	4.0±0.1	1.1max
2.12.120 (0000)		(0.059 ± 0.008)	(0.091 ± 0.008)	(0.157 ± 0.004)	(0.043max)
BK2010(0804)	0.45(0.018)	1.2±0.1	2.17±0.1	4.0±0.1	0.8max
		(0.047±0.004)	(0.085 ± 0.004)	(0.157±0.004)	(0.031max)
BKP0402 (01005)	0.2 (0.008)	0.25±0.04 (0.010±0.002)	0.45±0.04 (0.018±0.002)	2.0±0.05 (0.079±0.002)	0.36max (0.014max)
		0.40±0.06	0.70±0.06	2.0±0.05	0.45max
BKP0603 (0201)	0.3 (0.012)	(0.016±0.002)	(0.028 ± 0.002)	(0.079 ± 0.002)	(0.018max)
DIVD1005 (0100)	0.5 (0.000)	0.65±0.1	1.15±0.1	2.0±0.05	0.8max
BKP1005 (0402)	0.5 (0.020)	(0.026 ± 0.004)	(0.045 ± 0.004)	(0.079 ± 0.002)	(0.031max)
BKP1608 (0603)	0.8 (0.031)	1.0±0.2	1.8±0.2	4.0±0.1	1.1max
DIVE 1000 (0009)	0.0 (0.031)	(0.039 ± 0.008)	(0.071 ± 0.008)	(0.157±0.004)	(0.043max)
BKP2125 (0805)	0.85(0.033)	1.5±0.2	2.3±0.2	4.0±0.1	1.1max
		(0.059 ± 0.008)	(0.091 ± 0.008)	(0.157±0.004)	(0.043max)
BKH0603(0201)	0.3 (0.012)	0.40 ± 0.06	0.70 ± 0.06	2.0±0.05	0.45max
		(0.016±0.002)	(0.028±0.002)	(0.079±0.002)	(0.018max)
BKH1005(0402)	0.5 (0.020)	0.65±0.1 (0.026±0.004)	1.15±0.1 (0.045±0.004)	2.0±0.05 (0.079±0.002)	0.8max (0.031max)
		0.62±0.004)	0.77±0.03	2.0±0.05	0.45max
MCF0605 (0202)	0.3 (0.012)	(0.02±0.03 (0.024±0.001)	(0.030 ± 0.001)	(0.079 ± 0.002)	(0.018max)
		1.1±0.05	1.9±0.05	4.0±0.1	0.72max
	/ :				
MCFK1608 (0603)	0.6 (0.024)	(0.043 ± 0.002)	(0.075 ± 0.002)	(0.157 ± 0.004)	(0.028max)
	· · ·		(0.075±0.002) 1.9±0.05	(0.157±0.004) 4.0±0.1	(0.028max) 0.9max
MCFK1608 (0603) MCFE1608 (0603)	0.6 (0.024) 0.65 (0.026)	(0.043±0.002)			
	· · ·	(0.043±0.002) 1.1±0.05	1.9±0.05	4.0±0.1	0.9max

Unit : mm(inch)

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).




Turne	Thickness	Chip	cavity	Insertion Pitch	Tape Ti	nickness
Туре	mm(inch)	Α	В	F	K	Т
CK2125(0805)	1.25 (0.049)	1.5±0.2 (0.059±0.008)	2.3±0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	2.0 (0.079)	0.3 (0.012)
CKS2125(0805)	1.25(0.049)	1.5±0.2 (0.059±0.008)	2.3±0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	2.0 (0.079)	0.3 (0.012)
CKP2012 (0805)	0.9 (0.035)	1.55 ± 0.2 (0.061 \pm 0.008)	2.3 ± 0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	1.3 (0.051)	0.3 (0.012)
CKP2016 (0806)	0.9 (0.035)	1.8±0.1 (0.071±0.004)	2.2±0.1 (0.087±0.004)	4.0±0.1 (0.157±0.004)	1.3 (0.051)	0.25 (0.01)
	0.7 (0.028)				1.4 (0.055)	
CKP2520 (1008)	0.9 (0.035)	2.3±0.1 (0.091±0.004)	2.8±0.1 (0.110±0.004)	4.0±0.1 (0.157±0.004)	1.4 (0.055)	0.3 (0.012)
	1.1 (0.043)				1.7 (0.067)	
NM2012 (0805)	0.9 (0.035)	1.55±0.2 (0.061±0.008)	2.3±0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	1.3 (0.051)	0.3 (0.012)
NM2520(1008)	0.9 (0.035)	2.3±0.1	2.8±0.1	4.0±0.1	1.4 (0.055)	0.3
	1.1 (0.043)	(0.091 ± 0.004)	(0.110±0.004)	(0.157 ± 0.004)	1.7 (0.067)	(0.012)
LK2125(0805)	1.25(0.049)	1.5±0.2 (0.059±0.008)	2.3±0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	2.0 (0.079)	0.3 (0.012)
	0.85(0.033)	1.5±0.2	2.3±0.2	4.0±0.1	1.5 (0.059)	0.3
HK2125(0805)	1.0 (0.039)	(0.059 ± 0.008)	(0.091 ± 0.008)	(0.157±0.004)	2.0 (0.079)	(0.012)
BK2125(0805)	1.25(0.049)	1.5±0.2 (0.059±0.008)	2.3±0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	2.0 (0.079)	0.3 (0.012)
BK3216(1206)	0.8(0.031)	1.9±0.1 (0.075±0.004)	3.5 ± 0.1 (0.138 ± 0.004)	4.0±0.1 (0.157±0.004)	1.4 (0.055)	0.3 (0.012)
MCF0806(0302)	0.4 (0.016)	0.75±0.05 (0.030±0.002)	0.95 ± 0.05 (0.037 \pm 0.002)	2.0±0.05 (0.079±0.002)	0.55 (0.022)	0.3 (0.012)
MCF1210(0504)	0.55(0.022)	1.15±0.05 (0.045±0.002)	1.40 ± 0.05 (0.055 \pm 0.002)	4.0±0.1 (0.157±0.004)	0.65 (0.026)	0.3 (0.012)
MCF2010(0804)	0.45(0.018)	1.1±0.1 (0.043±0.004)	2.3±0.1 (0.091±0.004)	4.0±0.1 (0.157±0.004)	0.85	0.3 (0.012)
MCKK2012 (0805)	1.0 (0.039)	1.55±0.2 (0.061±0.008)	2.3±0.2 (0.091±0.008)	4.0±0.1 (0.157±0.004)	1.3 (0.051)	0.25 (0.010)

Unit: mm(inch)

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).


Embossed Tape (4mm wide)

Unit:mm(inch)




T	Thickness	Chip cavity		Insertion Pitch	Tape Th	nickness
Туре	mm(inch)	Α	В	F	K	Т
HKQ0402 (01005)	0.2 (0.008)	0.23	0.43	1.0±0.02	0.5max.	0.25max.
					Unit	: mm

4LEADER AND BLANK PORTION



5Reel Size




Α	В	С	D	E	R
ϕ 178 ± 2.0	ϕ 50 or more	ϕ 13.0 \pm 0.2	ϕ 21.0±0.8	2.0±0.5	1.0

	t	W
4mm width tape	1.5max.	5±1.0
8mm width tape	2.5max.	10±1.5

(Unit : mm)

6Top tape strength

The top tape requires a peel-off force of $0.1 \sim 0.7 N$ in the direction of the arrow as illustrated below.



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Multilayer chip inductors

Multilayer chip inductors for high frequency, Multilayer chip bead inductors

Multilayer common mode choke coils (MC series F type)

Metal Multilayer Chip Power Inductors (MCOIL™ MC series)

■RELIABILITY DATA

1. Operating Tempe					
	BK0402				
	BK0603				
	BK1005				
	BKH0603				
	BKH1005				
	BK1608				
	BK2125				
	ARRAY	BK2010			
		BK3216			
	BKP0402				
	BKP0603				
	BKP1005				
	BKP1608				
	BKP2125				
	MCF 0605				
	MCF 0806		-40∼+85°C		
	MCF 1210		TO - 100 O		
	MCF 2010				
	CK1608				
	CK2125				
Specified Value	CKS2125		<u>-</u> -		
opecined value	CKP1608				
	CKP2012				
	CKP2016		-40 s · + 95°C		
	CKP2520		-40~+85°C		
	NM2012				
	NM2520				
	LK1005				
	LK1608				
	LK2125				
	HKQ0402				
	HK0603				
	HK1005				
	HK1608		—————————————————————————————————————		
	HK2125		-40.4 ± 63 C		
	HKQ0603W/HK0	Q0603C/HKQ0603S/			
	HKQ0603U/		-55~+125°C		
	AQ105				
	MCFK1608				
	MCFE1608				
	MCHK2012		-40∼+125°C (Including self-generated heat)		
	MCKK2012				

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

2. Storage Tempera					
	BK0402				
	BK0603				
	BK1005				
	BKH0603				
	BKH1005				
	BK1608				
	BK2125				
	ARRAY	BK2010			
	70000	BK3216			
	BKP0402				
	BKP0603				
	BKP1005				
	BKP1608				
	BKP2125				
	MCF 0605				
	MCF 0806		-40∼+85°C		
	MCF 1210		40 * 1 03 C		
	MCF 2010				
	CK1608				
	CK2125				
Specified Value	CKS2125				
Specified value	CKP1608				
	CKP2012				
	CKP2016		-40∼+85°C		
	CKP2520		-40~+85 C		
	NM2012				
	NM2520				
	LK1005				
	LK1608				
	LK2125				
	HKQ0402				
	HK0603				
	HK1005				
	HK1608				
	HK2125		-40~+85 C		
	HKQ0603W/HK	(Q0603C/HKQ0603S/			
	HKQ0603U/				
	AQ105				
	MCFK1608				
	MCFE1608				
	MCHK2012		-40~+85°C		
	MCKK2012				

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

3. Rated Current			
	BK0402		150~750mA DC
	BK0603		100∼500mA DC
	BK1005		120~1000mA DC
	BKH0603		115~450mA DC
	BKH1005		200~300mA DC
	BK1608		150~1500mA DC
	BK2125		200~1200mA DC
	ADDAY	BK2010	100mA DC
	ARRAY	BK3216	100∼200mA DC
	BKP0402	•	0.55~1.1A DC
	BKP0603		0.8~1.8A DC
	BKP1005		0.8~2.4A DC
	BKP1608		1.0~3.0A DC
	BKP2125		1.5~4.0A DC
	MCF 0605		0.05A DC
	MCF 0806		0.1~0.13A DC
	MCF 1210		0.1~0.15A DC
	MCF 2010		0.1A DC
	CK1608		50∼60mA DC
	CK2125		60~500mA DC
	CKS2125		110~280mA DC
	CKP1608		0.35~0.9A DC
Specified Value	CKP2012		0.7∼1.7A DC
	CKP2016		0.9∼1.6A DC
	CKP2520		1.1~1.8A DC
	NM2012		1.0~1.2A DC
	NM2520		0.9~1.2A DC
	LK1005		20~25mA DC
	LK1608		1~150mA DC
	LK2125		5~300mA DC
	HK0603		60~470mA DC
	HK1005		110~300mA DC (-55~+125°C) 200~900mA DC (-55~+85°C)
	HK1608		150~300mA DC
	HK2125		300mA DC
	HKQ0402		100~500mA DC
	HKQ0603W		100∼850mA DC
	HKQ0603C		160~850mA DC
	HKQ0603S		130~600mA DC
	HKQ0603U		190~900mA DC
	AQ105		280~710mA DC
	MCFK1608		Idc1 : 1900~2300mA DC, Idc2 : 1600~2100mA DC

Definition of rated current:

MCFE1608

MCHK2012

MCKK2012

- •In the CK, CKS and BK Series, the rated current is the value of current at which the temperature of the element is increased within 20°C.
- In the BK Series P type, CK Series P type, NM Series, the rated current is the value of current at which the temperature of the element is increased within 40°C.

Idc1:

Idc1

•In the LK, HK, HKQ0603, and AQ Series, the rated current is either the DC value at which the initial L value is decreased within 5% with the application of DC bias, or the value of current at which the temperature of the element is increased within 20°C.

1400~2600mA DC,

3210~4320mA DC,

Idc2 : 800~1500mA DC

3240~3600mA DC

Idc2

Idc1: 4500~6200mA DC, Idc2: 3100~4000mA DC

- •In the HKQ0402(~9N1), the rated current is either the DC value at which the initial L value is decreased within 5% with the application of DC bias, or the value of current at which the temperature of the element is increased within 20°C.
- •In the HKQ0402(10N~), the rated current is either the DC value at which the initial L value is decreased within 5% with the application of DC bias, or the value of current at which the temperature of the element is increased within 25°C.
- •In the MC Series, Idc1 is the DC value at which the initial L value is decreased within 30% and Idc2 is the DC value at which the temperature of element is increased within 40°C by the application of DC bias. (at 20°C)

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

$ \begin{array}{c ccccccccccccccccccccccccccccccccccc$	
$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	
ARRAY BK3216 $60 \sim 1000 \Omega \pm 25\%$ BKP0402 $10 \sim 33 \Omega \pm 5 \Omega (10 \Omega), \pm 25\% (Other)$ BKP0603 $10 \sim 120 \Omega \pm 5 \Omega (10 \Omega), \pm 25\% (Other)$ BKP1005 $10 \sim 330 \Omega \pm 5 \Omega (EM100), \pm 25\% (Other)$ BKP1608 $33 \sim 470 \Omega \pm 25\%$	
BKP0402 $10 \sim 33 \Omega \pm 5 \Omega (10 \Omega, \pm 25\% (Other))$ BKP0603 $10 \sim 120 \Omega \pm 5 \Omega (10 \Omega, \pm 25\% (Other))$ BKP1005 $10 \sim 330 \Omega \pm 5 \Omega (EM100), \pm 25\% (Other)$ BKP1608 $33 \sim 470 \Omega \pm 25\%$	
BKP1005 $10 \sim 120 \Omega \pm 5 \Omega (10 \Omega)$, $\pm 25\% (Other)$ BKP1608 $10 \sim 330 \Omega \pm 5 \Omega (EM100)$, $\pm 25\% (Other)$ 33 ~ 470 Ω ± 25%	
BKP1005 $10\sim330\Omega\pm 5\Omega$ (EM100), ±25 %(Other) BKP1608 $33\sim470\Omega\pm25$ %	
BKP1608 $33\sim470\Omega\pm25\%$	
\mid BKP2125 \mid 33 \sim 330 Ω ±25%	
MCF 0605 $12 \sim 90 \Omega \pm 5 \Omega (12 \Omega), \pm 20\% (35 \Omega), \pm 25\% (Other)$	
MCF 0806 $12 \sim 90 \Omega \pm 5 \Omega (12 \Omega), \pm 20\% (Other)$	
MCF 1210 $40 \sim 90 \Omega \pm 20\% (2H900), \pm 25\% (Other)$	
MCF 2010 90Ω ±25%	
CK1608	
CK2125	
CKS2125	
Specified Value CKP1608	
CKP1000 CKP2012	
CKP2012 CKP2016	
CKP2520	
NM2012	
NM2520	
LK1005	
LK1608	
LK2125	
HKQ0402 HK0603	
HK1005	
HK1608	
HK2125	
HKQ0603W/HKQ0603C/HKQ0603S/	
HKQ0603U	
AQ105	
MCFK1608 MCFE1608	
MCHK2012	
MCKK2012 BK0402Series, BKP0402Series	
Measuring frequency : 100±1MHz	
Measuring equipment : E4991A(or its equivalent)	
Measuring jig : 16197A(or its equivalent)	
BK0603Series, BKP0603Series	
Measuring frequency : 100±1MHz	
Measuring equipment : 4291A (or its equivalent)	
Measuring jig : 16193A(or its equivalent)	
BK1005Series. BKP1005Series. BKH1005Series	
Test Methods and Measuring frequency : 100±1MHz	
Remarks Measuring equipment : 4291A(or its equivalent)	
Measuring jig : 16192A(or its equivalent), 16193A(or its equivalent)	
BK1608 • 2125Series, BKP1608 • 2125Series	
Measuring frequency : 100±1MHz	
Measuring frequency : 100±1MHz Measuring equipment : 4291A(or its equivalent), 4195A(or its equivalent)	
Measuring equipment : 4291A(or its equivalent), 4195A(or its equivalent)	
Measuring equipment : 4291A(or its equivalent), 4195A(or its equivalent) Measuring jig : 16092A(or its equivalent) or 16192A(or its equivalent)/HW	
Measuring equipment : 4291A(or its equivalent), 4195A(or its equivalent) Measuring jig : 16092A(or its equivalent) or 16192A(or its equivalent)/HW BK2010-3216Series, MCF Series	

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

5 Industria			
5. Inductance	DK0403		
	BK0402		-
	BK0603		4
	BK1005		-
	BKH0603		-
	BKH1005 BK1608		-
			-
	BK2125 BK2010		-
	ARRAY BK3216		-
	BKP0402		-
	BKP0603		-
	BKP1005		
	BKP1608		
	BKP2125		
	MCF 0605		-
	MCF 0806		1
	MCF 1210		1
	MCF 2010		
	CK1608		4.7~10.0 µH: ±20%
	CK2125		0.1~10.0 µH: ±20%
	CKS2125		1.0~10.0 µH: ±20%
	CKP1608		0.33~2.2 µH: ±20%
Specified Value	CKP2012		0.47~4.7 µH: ±20%
Specified Value	CKP2016		0.47~4.7 µH: ±20%
	CKP2520		0.47~4.7 μH: ±20%
	NM2012		0.82∼1.0 µH: ±20%
	NM2520		1.0~2.2 µH: ±20%
	LK1005		0.12~2.2 μH: ±10 or 20%
	LK1608		0.047~33.0 µH: ±20% 0.10~12.0 µH: ±10%
	LK2125		0.047~33.0 µH: ±20% 0.10~12.0 µH: ±10%
	HK0603		1.0~6.2nH: ±0.3nH 6.8~100nH: ±5%
	HK1005		1.0~6.2nH: ±0.3nH 6.8~270nH: ±5%
	HK1608		1.0~5.6nH: ±0.3nH 6.8~470nH: ±5%
	HK2125		1.5∼5.6nH: ±0.3nH 6.8∼470nH: ±5%
	HKQ0402		0.5 \sim 3.9nH: \pm 0.1 or 0.2 or 0.3nH 4.3 \sim 5.6nH: \pm 0.3nH or 3% or 5%
	111(40102		6.2~47nH: ±3 or 5%
	HKQ0603W		0.6~3.9nH: ±0.1 or 0.2 or 0.3nH 4.3~6.2nH: ±0.2 or 0.3nH or 3 or 5%
	1114000000		6.8~30nH: ±3 or 5% 33~100nH: ±5%
	HKQ0603C		0.6~3.9nH: ±0.1 or 0.2 or 0.3nH
	HKQ0603S		0.6~6.2nH: ±0.2 or 0.3nH 6.8~22nH: ±3 or 5%
	HKQ0603U		0.6~4.2nH: ±0.1 or 0.2 or 0.3nH 4.3~6.5nH: ±0.2 or 0.3nH 6.8~22nH: ±3 or 5% 1.0~6.2nH: ±0.3nH 6.8~15nH: ±5%
	AQ105		
	MCFK1608 MCFE1608		0.24~0.47H: ±20% 0.24~1.0 µH: ±20%
	MCHK2012		0.24~0.47H: ±20%
	MCKK2012		0.24~0.47H: ±20%
	CK, LK, CKP, NM, MC Series		V.E.1 V.1711. ±20//
	Measuring frequency	: 2~4MHz(CK16	608)
	Measuring frequency	: 2~25MHz(CK2	
	Measuring frequency	: 2~10MHz(CKS	
	Measuring frequency	: 10~25MHz(LK	(1005)
	Measuring frequency	: 1~50MHz(LK1	608)
	Measuring frequency	: 0.4~50MHz(Lh	
	Measuring frequency		8 • CKP2012 • CKP2016 • CKP2520 • NM2012 • NM2520 • MCFK1608 • MCFE1608 • MCHK2012 • MCKK2012)
	Measuring equipment /jig		B+16092A(or its equivalent) ·4195A+41951+16092A(or its equivalent)
			2A(or its equivalent) •4291A+16193A(or its equivalent)/LK1005
			H1A + 42842C + 42851 - 61100 (or its equivalent)/CKP1608 · CKP2012 · CKP2016 · CKP2520 · NM2012 · K1608 · MCEE1609 · MCHK2012 · MCKK2012
Test Methods and	Measuring ourrent	NM2520 • MCF :•1mA rms(0.047	K1608·MCFE1608·MCHK2012·MCKK2012
Remarks	Measuring current	•0.1mA rms(0.04)	
	HK, HKQ, AQ Series	0.1111A 11115 (J.C	υ ου μι,
	Measuring frequency	: 100MHz(HK060	03•HK1005•AQ105)
	Measuring frequency	: 50/100MHz(Hk	
	Measuring frequency		603C·HKQ0603S·HKQ0603U)
	Measuring frequency	: 300/500MHz(H	
	Measuring frequency	: 100/500MHz(H	
	Measuring equipment /jig	:•4291A+16197	A(or its equivalent)/HK0603•AQ105
			3A(or its equivalent)/HK1005
			97A(or its equivalent)/HKQ0603S•HKQ0603U•HKQ0603W•HKQ0603C
			2A + in-house made jig(or its equivalent)/HK1608•HK2125
		•E4991A+1619	96D(or its equivalent)/HKQ0402

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

6.0			
6. Q	BK0402		
	BK0603		1
	BK1005		1
	BKH0603		1
	BKH1005		
	BK1608		1
	BK2125		1
	BK2010		1
	ARRAY BK3216		1
	BKP0402		 -
	BKP0603		1
	BKP1005		1
	BKP1608		1
	BKP2125		1
	MCF 0605		
	MCF 0806		
	MCF 1210		
	MCF 2010		
	CK1608		
	CK2125		
	CKS2125		
Specified Value	CKP1608		
•	CKP2012		_
	CKP2016		-
	CKP2520		-
	NM2012 NM2520		1
	LK1005		10~20 min.
	LK1608		10~20 min.
	LK2125		15~50 min.
	HK0603		4~5 min.
	HK1005		8 min.
	HK1608		8~12 min.
	HK2125		10~18 min.
	HKQ0402		3∼8 min.
	HKQ0603W		6∼15 min.
	HKQ0603C		14~15 min.
	HKQ0603S		10~13 min.
	HKQ0603U AQ105		14 min.
	MCFK1608		8 min.
	MCFK1608 MCFE1608		1
	MCHK2012		
	MCKK2012		
	LK Series		I .
	Measuring frequency	: 10~25MHz(LK10	005)
	Measuring frequency	: 1~50MHz(LK160	
	Measuring frequency	: 0.4~50MHz(LK21	
	Measuring equipment /jig		+16092A(or its equivalent)
			-16092A(or its equivalent)
			(or its equivalent)
	Measuring current	•4291A + 16193A •1mA rms(0.047	(or its equivalent)/LK1005 ~4.7./H)
	Measuring current	•0.1mA rms(5.6~	
Test Methods and	HK、HKQ、AQ Series	2.1111/111113(0.0	y - y - y - y - y - y - y - y - y -
Remarks	Measuring frequency	: 100MHz(HK0603•	·HK1005·AQ105)
	Measuring frequency	: 50/100MHz(HK16	
	Measuring frequency		3C·HKQ0603S•HKQ0603U)
	Measuring frequency	: 300/500MHz(HKC	
	Measuring frequency	: 100/500MHz(HKC	
	Measuring equipment /jig		or its equivalent) /HK0603 · AQ105
			(or its equivalent) /HK1005 A (or its equivalent) /HKQ0603S∙HKQ0603U∙HKQ0603W∙HKQ0603C
			+ in-house made jig(or its equivalent)/HK1608, HK2125
			D(or its equivalent) HKQ0402
	ı		

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

7. DC Resistance							
	BK0402		0.07∼1.2Ωmax.				
	BK0603		0.065∼1.50 Ω max.				
	BK1005		0.03~0.90 Ω max.				
	BKH0603		0.26∼3.20 Ω max.				
	BKH1005		0.85~2.00 Ω max.				
	BK1608		0.05∼1.10Ω max.				
	BK2125		0.05~0.75Ω max.				
	4004)/	BK2010	0.10~0.90Ω max.				
	ARRAY	BK3216	0.15~0.80 Ω max.				
	BKP0402		0.05~0.15Ω max.				
	BKP0603		0.030~0.180Ω max.				
	BKP1005		0.0273~0.220Ω max.				
	BKP1608		0.025~0.18 Ω max.				
	BKP2125		0.020~0.075Ω max.				
	MCF 0605		2.5~6.5 Ω max				
	MCF 0806		2.5∼5.0 Ω max.				
	MCF 1210		2.5~4.5 Ω max.				
	MCF 2010		4.5Ω max.				
	CK1608		$0.45 \sim 0.85 \Omega(\pm 30\%)$				
	CK2125		0.16~0.65 Ω max.				
	CKS2125		0.12~0.52 Ω max.				
	CKP1608		0.15~0.35Ω max.				
Specified Value	CKP2012		0.08~0.28 Ω max.				
	CKP2016		0.075~0.20 Ω max				
	CKP2520		0.05~0.16 Ω max.				
	NM2012		0.10~0.15Ω max.				
	NM2520		0.11~0.22 Ω max.				
	LK1005		0.41~1.16Ω max.				
	LK1608		0.2~2.2Ω max.				
	LK2125		0.1~1.1Ω max.				
	HK0603		0.11~3.74Ω max.				
	HK1005		0.08~4.8 Ω max.				
	HK1608		0.05~2.6 Ω max.				
	HK2125		0.10~1.5Ω max.				
	HKQ0402		0.08~5.0Ω max.				
	HKQ0603W		0.07~4.1 Ω max.				
	HKQ0603W		0.07~1.6Ω max.				
	HKQ0603S		0.06~1.29 Ω max.				
	HKQ0603U		0.06~1.29 Ω max.				
	AQ105 MCFK1608		0.07~0.45 Ω max. 0.050~0.085 Ω max.				
	MCFE1608		0.100~0.340 Ω max.				
	MCHK2012		0.024~0.036 Ω max.				
		MCKK2012 0.025∼0.039 Ω max.					
Test Methods and Remarks	Measuring equipme	ent:VOAC-7412, VOA	AC-7512, VOAC-7521 (made by Iwasaki Tsushinki), HIOKI3227 (or its equivalent)				


This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

	, <u> </u>			
8. Self Resonance Free	· · ·			
	BK0402			
	BK0603			
	BK1005			
	BKH0603			
	BKH1005			
	BK1608			
	BK2125			
	ARRAY	BK2010		
		BK3216	_ _	_
	BKP0402			
	BKP0603			
	BKP1005			
	BKP1608			
	BKP2125		_ _	
	MCF 0605			
	MCF 0806			
	MCF 1210			
	MCF 2010			
	CK1608			17~25MHz min.
	CK2125			24~235MHz min.
	CKS2125			24~75MHz min.
Specified Value	CKP1608			
Specifica Value	CKP2012			
	CKP2016			_
	CKP2520			
	NM2012			1
	NM2520			
	LK1005			40~180MHz min.
	LK1608			9~260MHz min.
	LK2125			13~320MHz min.
	HK0603			900~10000MHz min.
	HK1005			400~10000MHz min.
	HK1608			300~10000MHz min.
	HK2125			200~4000MHz min.
	HKQ0402			1200~10000MHz min.
	HKQ0603W			800~10000MHz min.
	HKQ0603C			2500~10000MHz min.
	HKQ0603S			1900~10000MHz min.
	HKQ0603U			1900~10000MHz min.
	AQ105			2300~10000MHz min.
	MCFK1608			1
	MCFE1608			-
	MCHK2012			-
	MCKK2012			
	LK, CK Series :		41054/ "	
Test Methods and	Measuring equip	oment	: 4195A (or its equiv	
Remarks	Measuring jig : 41951+16092A(or		: 41951 + 16092A(o	or its equivalent)
	HK, HKQ, AQ Se		· 87190 (or its	valent) •8753D(or its equivalent)/HK2125
	Measuring equipment : 8719C (or its equiva			valent/ -0/000 (or its equivalent// TRZ120

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

9. Temperature Chara	emperature Characteristic			
	BK0402			
	BK0603			
	BK1005			
	BKH0603			
	BKH1005			
	BK1608			
	BK2125			
	ARRAY	BK2010		
		BK3216		
	BKP0402			
	BKP0603			
	BKP1005			
	BKP1608			
	BKP2125			
	MCF 0605			_
	MCF 0806			
	MCF 1210			
	MCF 2010			
	CK1608			
	CK2125			
	CKS2125			
Specified Value	CKP1608			
	CKP2012			
	CKP2016			
	CKP2520			
	NM2012			
	NM2520			
	LK1005			
	LK1608			
	LK2125			
	HK0603			
	HK1005			
	HK1608			
	HK2125			
	HKQ0402			
	HKQ0603W			
	HKQ0603C			Inductance change:Within ±10%
	HKQ0603S			inducance change. Maint = 1070
	HKQ0603U			
	AQ105			
	MCFK1608			
	MCFE1608			
	MCHK2012			
	MCKK2012			
	HK, HKQ, AQ Se			
	Temperature rar		: −30~+85°C	
Test Methods and	Reference temp	erature	: +20°C	
Remarks	MC Series:			
	Temperature rar	_	: −40~+85°C	
	Reference temp	erature	: +20°C	

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).



This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

11. Solderability			
	BK0402		
	BK0603		
	BK1005		
	BKH0603		
	BKH1005		
	BK1608		
	BK2125	1	
	ARRAY	BK2010	
		BK3216	
	BKP0402		
	BKP0603		
	BKP1005		
	BKP1608		
	BKP2125		
	MCF 0605		
	MCF 0806		
	MCF 1210		
	MCF 2010		
Specified Value	CK1608		
	CK2125		
	CKS2125		At least 75% of terminal electrode is covered by new solder.
	CKP1608		
	CKP2012		
	CKP2016		
	CKP2520		
	NM2012		
	NM2520		
	LK1005		
	LK1608		
	LK2125		
	HK0603		
	HK1005		
	HK1608		
	HK2125]
	HKQ0402		1
	HKQ0603W		1
	HKQ0603C		1
	HKQ0603S		1
	HKQ0603U		1
	AQ105		1
	MCFK1608		1
	MCFE1608		
	MCHK2012		
	MCKK2012		1
T . M .:	Solder temperatu	re :230±5°C (JIS Z 32	
Test Methods and	Solder temperatu		
Remarks	Duration	:4±1 sec.	

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

10 Decistant to 0.11	lavia e				
12. Resistance to Sold					
	BK0402				
	BK0603				
	BK1005				
	BKH0603				
	BKH1005				
	BK1608		1 N 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1		
	BK2125		Appearance: No significant abnormality		
	ARRAY BK201		Impedance change: Within ±30%		
	BK321	6			
	BKP0402				
	BKP0603				
	BKP1005				
	BKP1608				
	BKP2125				
	MCF 0605				
	MCF 0806		Appearance: No significant abnormality		
	MCF 1210		Impedance change: Within ±20%		
	MCF 2010				
	CK1608		No mechanical damage.		
	CK2125		Remaining terminal electrode: 70% min		
	CKS2125		1		
	CKP1608		Inductance change		
	CKP2012		R10~4R7: Within ±10% 6R8~100: Within ±15% CKS2125: Within ±20% CKP1608、CKP2012、CKP2016、CKP2520、NM2012、NM2520: Within ±30%		
Specified Value	CKP2016				
Specified value	CKP2520				
	NM2012				
	NM2520		No weekenied denotes		
	11/1005		No mechanical damage.		
	LK1005		Remaining terminal electrode: 70% min.		
	LK1608		Inductance change: Within ±15% No mechanical damage.		
	LK1000		Remaining terminal electrode: 70% min.		
			Inductance change		
	LK2125		47N~4R7: Within ±10%		
			5R6~330: Within ±15%		
	HK0603				
	HK1005				
	HK1608				
	HK2125		l		
	HKQ0402		No mechanical damage.		
	HKQ0603W		Remaining terminal electrode: 70% min.		
	HKQ0603C		Inductance change: Within ±5%		
	HKQ0603S				
	HKQ0603U				
	AQ105				
	MCFK1608		N		
	MCFE1608		No mechanical damage.		
	MCHK2012		Remaining terminal electrode: 70% min.		
	MCKK2012		Inductance change: Within ±10%		
	Solder temperature	:260±5°C			
	Duration	$:10\pm0.5\;{\rm sec.}$			
Test Methods and	Preheating temperature	:150 to 180°C			
Remarks	Preheating time	:3 min.			
	Flux		methanol solution with colophony for 3 to 5 sec.		
	Recovery		covery under the standard condition after the test.(See Note 1)		
(Note 1) When there a	hen there are questions concerning measurement result; measurement shall be made after 48±2 hrs of recovery under the standard condition.				

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

13. Thermal Shock						
13. Thermal Shock	BK0402		1			
	BK0603					
	BK1005					
	BKH0603		-			
			-			
	BKH1005		4			
	BK1608		┪, ,, ,	200 - 1 - 12		
	BK2125	L DIVOCALO.		gnificant abnormality		
	ARRAY	BK2010	Impedance change	: Within ±30%		
	DI/D0400	BK3216	_			
		BKP0402				
	BKP0603		-			
	BKP1005					
	BKP1608					
	BKP2125					
	MCF 0605					
	MCF 0806		- ' '	gnificant abnormality		
	MCF 1210		Impedance change	: Within ±20%		
	MCF 2010					
	CK1608			No mechanical damage.		
	CK2125			Inductance change:Within ±20% Q change:Within ±30%		
	CKS2125		Inductance change: Within ±20% (CKS2125)			
Specified Value	CKP1608					
opcomou valuo	CKP2012					
	CKP2016		No mechanical dan	No mechanical damage.		
	CKP2520			Inductance change: Within ±30%		
	NM2012					
	NM2520					
	LK1005		No mechanical damage. Inductance change: Within ±10% Q change: Within ±30%			
	LK1608					
	LK2125		Inductance change. Within ±1070 & change. Within ±3070			
	HK0603					
	HK1005					
	HK1608					
	HK2125					
	HKQ0402		No mechanical dan	No mechanical damage. Inductance change: Within ±10% Q change: Within ±20%		
	HKQ0603W		Inductance change			
	HKQ0603C					
	HKQ0603S					
	HKQ0603U					
	AQ105					
	MCFK1608					
	MCFE1608		Appearance: No sig	gnificant abnormality		
	MCHK2012		Inductance change: Within ±10%			
	MCKK2012					
	Conditions for	Conditions for 1 cycle				
	Step	temperature (°C)		time (min.)		
	1	Minimum operating temperature	re +0/-3	30±3		
Test Methods and	2	Room temperature		2~3		
Remarks	3	Maximum operating temperatu	re $+3/-0$	30±3		
	4	Room temperature		2~3		
	Number of cycl	les:5				
	Recovery: 2 to	3 hrs of recovery under the standar	rd condition after the	test (See Note 1)		

Recovery: 2 to 3 hrs of recovery under the standard condition after the test. (See Note 1)

(Note 1) When there are questions concerning measurement result; measurement shall be made after 48 ± 2 hrs of recovery under the standard condition.

[▶] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

14 Damm Hart C	du stata)			
14. Damp Heat (Stead	dy state) BK0402			
	BK0603			
	BK1005			
	BKH0603			
	BKH1005 BK1608			
	BK2125		Appearance: No significant abnormality	
	ARRAY	BK2010	Impedance change: Within ±30%	
	70000	BK3216		
	BKP0402			
	BKP0603			
	BKP1005			
	BKP1608			
	BKP2125			
	MCF 0605			
	MCF 0806		Appearance: No significant abnormality	
	MCF 1210		Impedance change: Within ±20%	
	MCF 2010		ampodunos shangs. Wallin =2575	
	CK1608		No mechanical damage.	
	CK1008		4	
			Inductance change: Within ±20% Q change: Within ±30%	
	CKS2125		Inductance change: Within ±20%	
	CKP1608			
Specified Value	CKP2012			
	CKP2016		No mechanical damage.	
	CKP2520		Inductance change: Within ±30%	
	NM2012			
	NM2520			
	LK1005		No mechanical damage.	
	LK1608		Inductance change: Within ±10% Q change: Within ±30%	
	11/0105		No mechanical damage.	
	LK2125		Inductance change: Within ±20% Q change: Within ±30%	
	HK0603			
	HK1005			
	HK1608			
	HK2125			
	HKQ0402		No mechanical damage.	
	HKQ0603W		Inductance change: Within ±10% Q change: Within ±20%	
	HKQ0603W		madetarioe charge. Walling 21070 & charge. Walling 22070	
	HKQ0603C			
	HKQ0603U			
	AQ105			
	MCFK1608			
	MCFE1608		Appearance: No significant abnormality	
	MCHK2012		Inductance change: Within ±10%	
	MCKK2012			
	BK, BKP, BKH S	eries, MCF Series:		
	Temperature	:40±2°C		
	Humidity	:90 to 95%RH		
	Duration	:500+24/-0 hrs		
	Recovery	:2 to 3 hrs of recovery under the	ne standard condition after the removal from test chamber.(See Note 1)	
Test Methods and				
Remarks	LK, CK, CKS, CH	KP、NM、HK、HKQ、AQ、MC Serie		
	Temperature	:40±2°C(LK, CK, CKS, CKP		
		:60±2°C(HK, HKQ, AQ, MC	Series)	
	Humidity	:90 to 95%RH		
	I D ::	. 500 ± 12 hun		
	Duration	:500±12 hrs		
	Recovery		ne standard condition after the removal from test chamber.(See Note 1)	

[►] This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

15. Loading under Dar	mn Heat			
To. Loading under Dar	BK0402			
	BK0603		1	
	BK1005			
	BKH0603			
	BKH1005			
	BK11003			
	BK2125		Appearance: No significant abnormality	
		K2010	Impedance change: Within ±30%	
	I ARRAY —	K3216	Impedance change. Within ±30%	
	BKP0402	K3210		
	BKP0603			
	BKP1005			
	BKP1608			
	BKP2125			
	CK1608		No mechanical damage.	
	CK2125		Inductance change: Within ±20% Q change: Within ±30%	
	OKETEO		No mechanical damage.	
	CKS2125		Inductance change: Within ±20%	
	CKP1608		The state of the light in the l	
	CKP2012		1	
	CKP2016		No mechanical damage.	
	CKP2520		Inductance change: Within ±30%	
Specified Value	NM2012			
•	NM2520			
			No mechanical damage.	
	LK1005		Inductance change: Within ±10% Q change: Within ±30%	
			No mechanical damage.	
	LK1608		Inductance change: $0.047 \sim 12.0 \mu\text{H}$: Within $\pm 10\%$ $15.0 \sim 33.0 \mu\text{H}$: Within $\pm 15\%$	
			Q change: Within ±30%	
	LK2125		No mechanical damage.	
	LIVETES		Inductance change: Within ±20% Q change: Within ±30%	
	HK0603			
	HK1005			
	HK1608			
	HK2125			
	HKQ0402		No mechanical damage.	
	HKQ0603W		Inductance change: Within ±10% Q change: Within ±20%	
	HKQ0603C			
	HKQ0603S			
	HKQ0603U			
	AQ105			
	MCFK1608※			
	MCFE1608※		Appearance: No significant abnormality	
	MCHK2012※		Inductance change: Within ±10%	
	MCKK2012※			
	BK, BKP, BKH Serie			
	Temperature	:40±2°C		
	Humidity Applied current	: 90 to 95%RH : Rated current		
	Duration	:500+24/-0 hrs		
	Recovery		der the standard condition after the removal from test chamber.(See Note 1)	
Test Methods and		NM, HK, HKQ, AQ, MC Serie		
Remarks	Temperature	:40±2°C(LK, CK, CKS,		
	· ·	:60±2°C(HK, HKQ, AQ,		
	Humidity	:90 to 95%RH		
	Applied current	:Rated current ※MC seri	ies ; Idc2max	
	Duration	$:500\pm12\; hrs$		
-	Recovery	:2 to 3 hrs of recovery und	der the standard condition after the removal from test chamber.(See Note 1)	

Note on standard condition: "standard condition" referred to herein is defined as follows:

5 to $35^{\circ}\!\text{C}\,$ of temperature, 45 to 85% relative humidity, and 86 to 106kPa of air pressure.

When there are questions concerning measurement results:

In order to provide correlation data, the test shall be conducted under condition of $20\pm2^{\circ}C$ of temperature, 60 to 70% relative humidity, and 86 to 106kPa of air pressure.

Unless otherwise specified, all the tests are conducted under the "standard condition."

(Note 1) Measurement shall be made after 48 ± 2 hrs of recovery under the standard condition.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

16 Looding at High T.	amparatura				
16. Loading at High Te	BK0402				
			4		
	BK0603				
	BK1005				
	BKH0603		4		
	BKH1005		4		
	BK1608		Annual No. 1 of the Street of the country of the		
	BK2125		Appearance: No significant abnormality		
	ARRAY	BK2010	Impedance change: Within ±30%		
		BK3216	-		
	BKP0402				
	BKP0603				
	BKP1005				
	BKP1608				
	BKP2125				
	MCF 0605				
	MCF 0806		Appearance: No significant abnormality		
	MCF 1210		Impedance change: Within ±20%		
	MCF 2010				
	CK1608		No mechanical damage.		
	CK2125		Inductance change: Within ±20% Q change: Within ±30%		
	CKS2125		No mechanical damage.		
			Inductance change: Within ±20%		
	CKP1608		-		
0 (0 1)/ 1	CKP2012				
Specified Value	CKP2016		No mechanical damage.		
	CKP2520		Inductance change: Within ±30%		
	NM2012				
	NM2520				
	LK1005		No mechanical damage.		
			Inductance change: Within ±10% Q change: Within ±30%		
			No mechanical damage.		
	LK1608		Inductance change: $0.047 \sim 12.0 \mu\text{H}$: Within $\pm 10\%$ $15.0 \sim 33.0 \mu\text{H}$: Within $\pm 15\%$		
			Q change: Within ±30%		
	LK2125		No mechanical damage.		
	HK0603		Inductance change: Within ±20% Q change: Within ±30%		
	HK1005		-		
	HK1608				
	HK2125				
	HKQ0402		Manusaharias I dan sara		
	HKQ0603W		No mechanical damage.		
	HKQ0603W HKQ0603C		Inductance change: Within ±10% Q change: Within ±20%		
			-		
	HKQ0603S		-		
	HKQ0603U		-		
	AQ105				
	MCFK1608%		Annual No. 1 of the Street of the country of the		
	MCFE1608※		Appearance: No significant abnormality		
	MCHK2012※ MCKK2012※		Inductance change: Within ±10%		
	+	Porios MCE Savias			
	Temperature	eries、MCF Series: : 125±3°C(BK、BKH Series)			
	remperature	: 85±3°C(BKP, MCF Series)			
	Applied current	: Rated current			
	Duration	:500+24/-0 hrs			
	Recovery		he standard condition after the removal from test chamber.		
T . M		(See Note 1)			
Test Methods and	LK, CK, CKS, CH	KP, NM, HKQ, AQ, MC Series:			
Remarks	Temperature	:85±2°C(LK,CK,CKS,CKP,	NM、MC Series)		
		: 85±2°C(HK1608, 2125)			
			rating temperature range $-55 \sim +85^{\circ}$ C)		
		: 125±2°C (HKQ0402, HK0603,	HK1005, HKQ0603S, HKQ0603U, HKQ0603W, HKQ0603C, AQ105		
		operating temperature	e range -55~+125°C)		
	Applied current	: Rated current ※MC series ;	Idc2max		
	Duration	:500±12 hrs			
	Recovery	:2 to 3 hrs of recovery under the	he standard condition after the test. (See Note 1)		
Note on standard con-	ndition: "standard condition" referred to herein is defined as follows:				

5 to $35^{\circ}\!C$ of temperature, 45 to 85% relative humidity, and 86 to 106kPa of air pressure.

When there are questions concerning measurement results:

In order to provide correlation data, the test shall be conducted under condition of $20\pm2^{\circ}C$ of temperature, 60 to 70% relative humidity, and 86 to 106kPa of air pressure. Unless otherwise specified, all the tests are conducted under the "standard condition."

(Note 1) Measurement shall be made after 48±2 hrs of recovery under the standard condition.

Finis catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/) .

Precautions on the use of Multilayer chip inductors

Multilayer chip inductors for high frequency, Multilayer chip bead inductors

Multilayer common mode choke coils (MC series F type)

Metal Multilayer Chip Power Inductors (MCOILTM MC series)

PRECAUTIONS

1. Circuit Design

- ◆Verification of operating environment, electrical rating and performance
 - 1. A malfunction in medical equipment, spacecraft, nuclear reactors, etc. may cause serious harm to human life or have severe social ramifications.

As such, any inductors to be used in such equipment may require higher safety and/or reliability considerations and should be clearly

Precautions differentiated from components used in general purpose applications.

- ◆Operating Current(Verification of Rated current)

 1. The operating current including inrush current for inductors must always be lower than their rated values.
- 2. Do not apply current in excess of the rated value because the inductance may be reduced due to the magnetic saturation effect.


2. PCB Design

Precautions

- ◆Pattern configurations (Design of Land-patterns)
- 1. When inductors are mounted on a PCB, the size of land patterns and the amount of solder used (size of fillet) can directly affect inductor performance.

Therefore, the following items must be carefully considered in the design of solder land patterns:

- (1) The amount of solder applied can affect the ability of chips to withstand mechanical stresses which may lead to breaking or cracking. Therefore, when designing land-patterns it is necessary to consider the appropriate size and configuration of the solder pads which in turn determines the amount of solder necessary to form the fillets.
- (2) When more than one part is jointly soldered onto the same land or pad, the pad must be designed so that each component's soldering point is separated by solder-resist.
- (3) The larger size of land patterns and amount of solder, the smaller Q value after mounting on PCB. It makes higher the Q value to design land patterns smaller than terminal electrode of chips.
- ◆Pattern configurations (Inductor layout on panelized[breakaway] PC boards)
 - 1. After inductors have been mounted on the boards, chips can be subjected to mechanical stresses in subsequent manufacturing processes (PCB cutting, board inspection, mounting of additional parts, assembly into the chassis, wave soldering the reflow soldered boards etc.) For this reason, planning pattern configurations and the position of SMD inductors should be carefully performed to minimize stress.
- ◆Pattern configurations(Design of Land-patterns)
 - The following diagrams and tables show some examples of recommended patterns to prevent excessive solder amounts (larger fillets which extend above the component end terminations). Examples of improper pattern designs are also shown.
 - (1) Recommended land dimensions for a typical chip inductor land patterns for PCBs



Recommended land dimensions for wave-soldering (Unit:mm)

Туре		1608	2012	2125	2016	2520	3216
Size	L	1.6	2.0	2.0	2.0	2.5	3.2
	W	0.8	1.25	1.25	1.6	2.0	1.6
Α		0.8~1.0	1.0~1.4	1.0~1.4	1.0~1.4	1.0~1.4	1.8~2.5
В		0.5~0.8	0.8~1.5	0.8~1.5	0.8~1.5	0.6~1.0	0.8~1.7
С		0.6~0.8	0.9~1.2	0.9~1.2	1.3~1.6	1.6~2.0	1.2~1.6


Technical considerations

Recommended land dimensions for reflow-soldering (Unit:mm)

Т	ype	0402	0603	1005	105	1608	2012	2125	2016	2520	3216
Size	L	0.4	0.6	1.0	1.0	1.6	2.0	2.0	2.0	2.5	3.2
Size	W	0.2	0.3	0.5	0.6	0.8	1.25	1.25	1.6	2.0	1.6
	Α	0.15~0.25	0.20~0.30	0.45~0.55	0.50~0.55	0.8~1.0	0.8~1.2	0.8~1.2	0.8~1.2	1.0~1.4	1.8~2.5
	В	0.10~0.20	0.20~0.30	0.40~0.50	0.30~0.40	0.6~0.8	0.8~1.2	0.8~1.2	0.8~1.2	0.6~1.0	0.6~1.5
	С	0.15~0.30	0.25~0.40	0.45~0.55	0.60~0.70	0.6~0.8	0.9~1.6	0.9~1.6	1.2~2.0	1.8~2.2	1.2~2.0

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Excess solder can affect the ability of chips to withstand mechanical stresses. Therefore, please take proper precautions when designing land-patterns.



Recommended land dimension for Reflow-soldering

Type		3216	2010	1210	0806	0605
	L	3.2	2.0	1.25	0.85	0.65
Size	W	1.6	1.0	1.0	0.65	0.50
а		0.7~0.9	0.5~0.6	0.45~0.55	0.25~0.35	0.27~0.33
b		0.8~1.0	0.5~0.6	0.7~0.8	0.25~0.35	0.17~0.23
С		0.4~0.5	0.2~0.3	0.25~0.35	0.25~0.35	0.20~0.26
d		0.8	0.5	0.55	0.5	0.4

(Unit:mm)

((2) Examples of good and bad solder application


	Examples of good and bad solder application						
	Item	Not recommended	Recommended				
Mix	ed mounting of SMD and leaded components	Lead wire of component	Solder-resist				
Com	ponent placement close to the chassis	Chassis Solder (for grounding) Electrode pattern	Solder-resist				
	and-soldering of leaded mponents near mounted components	Lead wire of component Soldering iron	Solder-resist				
	Horizontal component placement		Solder-resist				

- ◆Pattern configurations (Inductor layout on panelized[breakaway] PC boards)
 - 1-1. The following are examples of good and bad inductor layout; SMD inductors should be located to minimize any possible mechanical stresses from board warp or deflection.

Item	Not recommended	Recommended		
Deflection of the board		Position the component at a right angle to the direction of the mechanical stresses that are anticipated.	of	

1-2. To layout the inductors for the breakaway PC board, it should be noted that the amount of mechanical stresses given will vary depending on inductor layout.

An example below should be counted for better design.



1-3. When breaking PC boards along their perforations, the amount of mechanical stress on the inductors can vary according to the method used. The following methods are listed in order from least stressful to most stressful: push-back, slit, V-grooving, and perforation. Thus, any ideal SMD inductor layout must also consider the PCB splitting procedure.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

3. Considerations for automatic placement

- ◆Adjustment of mounting machine
 - 1. Excessive impact load should not be imposed on the inductors when mounting onto the PC boards.
 - 2. The maintenance and inspection of the mounter should be conducted periodically.

Precautions

◆ Selection of Adhesives

1. Mounting inductors with adhesives in preliminary assembly, before the soldering stage, may lead to degraded inductor characteristics unless the following factors are appropriately checked; the size of land patterns, type of adhesive, amount applied, hardening temperature and hardening period. Therefore, it is imperative to consult the manufacturer of the adhesives on proper usage and amounts of adhesive to use.

◆Adjustment of mounting machine

- 1. If the lower limit of the pick-up nozzle is low, too much force may be imposed on the inductors, causing damage. To avoid this, the following points should be considered before lowering the pick-up nozzle:
 - (1) The lower limit of the pick-up nozzle should be adjusted to the surface level of the PC board after correcting for deflection of the board.
 - (2) The pick-up pressure should be adjusted between 1 and 3N static loads.
 - (3) To reduce the amount of deflection of the board caused by impact of the pick-up nozzle, supporting pins or back-up pins should be used under the PC board. The following diagrams show some typical examples of good pick-up nozzle placement:

Item	Improper method	Proper method	
Single-sided mounting	chipping or cracking	supporting pins or back-up pins	
Double-sided mounting	chipping or cracking	supporting pins or back-up pins	

Technical considerations


2. As the alignment pin wears out, adjustment of the nozzle height can cause chipping or cracking of the inductors because of mechanical impact on the inductors. To avoid this, the monitoring of the width between the alignment pin in the stopped position, and maintenance, inspection and replacement of the pin should be conducted periodically.


◆Selection of Adhesives

- 1. Some adhesives may cause reduced insulation resistance. The difference between the shrinkage percentage of the adhesive and that of the inductors may result in stresses on the inductors and lead to cracking. Moreover, too little or too much adhesive applied to the board may adversely affect component placement, so the following precautions should be noted in the application of adhesives.
 - (1) Required adhesive characteristics
 - a. The adhesive should be strong enough to hold parts on the board during the mounting & solder process.
 - b. The adhesive should have sufficient strength at high temperatures.
 - c. The adhesive should have good coating and thickness consistency.
 - d. The adhesive should be used during its prescribed shelf life.
 - e. The adhesive should harden rapidly.
 - f. The adhesive must not be contaminated.
 - g. The adhesive should have excellent insulation characteristics.
 - h. The adhesive should not be toxic and have no emission of toxic gasses.
 - (2) When using adhesives to mount inductors on a PCB, inappropriate amounts of adhesive on the board may adversely affect component placement. Too little adhesive may cause the inductors to fall off the board during the solder process. Too much adhesive may cause defective soldering due excessive flow of adhesive on to the land or solder pad.

[Recommended conditions]

Figure	0805 case sizes as examples	
а	0.3mm min	
b	100∼120 μm	
С	Area with no adhesive	





4. Soldering

Precautions

◆Selection of Flux

- 1. Since flux may have a significant effect on the performance of inductors, it is necessary to verify the following conditions prior to use;
 - (1) Flux used should be with less than or equal to 0.1 wt% (Chlorine conversion method) of halogenated content. Flux having a strong acidity content should not be applied.
 - (2) When soldering inductors on the board, the amount of flux applied should be controlled at the optimum level.
 - (3) When using water-soluble flux, special care should be taken to properly clean the boards.

◆Soldering

1. Temperature, time, amount of solder, etc. are specified in accordance with the following recommended conditions, and please contact us about peak temperature when you use lead-free paste.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

◆Selection of Flux

- 1-1. When too much halogenated substance (Chlorine, etc.) content is used to activate the flux, or highly acidic flux is used, an excessive amount of residue after soldering may lead to corrosion of the terminal electrodes or degradation of insulation resistance on the surface of the Inductor.
- 1-2. Flux is used to increase solderability in flow soldering, but if too much is applied, a large amount of flux gas may be emitted and may detrimentally affect solderability. To minimize the amount of flux applied, it is recommended to use a flux-bubbling system.
- 1-3. Since the residue of water-soluble flux is easily dissolved by water content in the air, the residue on the surface of Inductor in high humidity conditions may cause a degradation of insulation resistance and therefore affect the reliability of the components. The cleaning methods and the capability of the machines used should also be considered carefully when selecting water-soluble flux.

Soldering


1-1. Preheating when soldering

Heating: Chip inductor components should be preheated to within $100 \text{ to } 130^{\circ}\text{C}$ of the soldering. Cooling: The temperature difference between the components and cleaning process should not be greater than 100°C .


Chip inductors are susceptible to thermal shock when exposed to rapid or concentrated heating or rapid cooling. Therefore, the soldering process must be conducted with a great care so as to prevent malfunction of the components due to excessive thermal shock.

[Reflow soldering]

[Recommended conditions for eutectic soldering]



[Recommended condition for Pb-free soldering]




- m %Ceramic chip components should be preheated to within 100 to 130°C of the soldering.
- *Assured to be reflow soldering for 2 times.
- *MC series; Peak 230°C(eutectic soldering), 260°C(Pb-free soldering)max within 5sec.

Caution

Technical

considerations


1. The ideal condition is to have solder mass (fillet) controlled to 1/2 to 1/3 of the thickness of the inductor, as shown below:




2. Because excessive dwell times can detrimentally affect solderability, soldering duration should be kept as close to recommended times as possible.

[Wave soldering]

[Recommended conditions for eutectic soldering]



[Recommended condition for Pb-free soldering]




- $\rm \% Ceramic \ chip \ components \ should \ be \ preheated \ to \ within \ 100 \ to \ 130 \ C$ of the soldering.
- XAssured to be wave soldering for 1 time.
- Except for reflow soldering type

Caution


- 1. Make sure the inductors are preheated sufficiently.
- 2. The temperature difference between the inductor and melted solder should not be greater than 100 to 130° C.
- 3. Cooling after soldering should be as gradual as possible.
- 4. Wave soldering must not be applied to the inductors designated as for reflow soldering only.

[Hand soldering]

[Recommended conditions for eutectic soldering



[Recommended condition for Pb-free soldering]



- (**※**⊿T≦190°C(3216Type max), ⊿T≦130°C(3225 Type min)
- lphaIt is recommended to use 20W soldering iron and the tip is 1 ϕ or less.
- XThe soldering iron should not directly touch the components.
- *Assured to be soldering iron for 1 time

Note: The above profiles are the maximum allowable soldering condition, therefore these profiles are not always recommended.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).

Caution 1. Use a 20W soldering iron with a maximum tip diameter of 1.0 mm. 2. The soldering iron should not directly touch the inductor.

5. Cleaning Cleaning conditions 1. When cleaning the PC board after the Inductors are all mounted, select the appropriate cleaning solution according to the type of flux used and purpose of the cleaning(e.g. to remove soldering flux or other materials from the production process.) 2. Cleaning conditions should be determined after verifying, through a test run, that the cleaning process does not affect the inductor's characteristics. Cleaning conditions 1. The use of inappropriate solutions can cause foreign substances such as flux residue to adhere to the inductor, resulting in a degradation of the inductor's electrical properties(especially insulation resistance). 2. Inappropriate cleaning conditions (insufficient or excessive cleaning) may detrimentally affect the performance of the inductors. (1) Excessive cleaning

Technical considerations

a. In the case of ultrasonic cleaning, too much power output can cause excessive vibration of the PC board which may lead to the cracking of the inductor or the soldered portion, or decrease the terminal electrodes' strength. Thus the following conditions should be carefully checked;

Ultrasonic output Below 20W/2
Ultrasonic frequency Below 40kHz
Ultrasonic washing period 5 min. or less

6. Post cleaning processes

◆Application of resin coatings, moldings, etc. to the PCB and components.

Precautions

- 1. With some type of resins a decomposition gas or chemical reaction vapor may remain inside the resin during the hardening period or while left under normal storage conditions resulting in the deterioration of the inductor's performance.
- 2. When a resin's hardening temperature is higher than the inductor's operating temperature, the stresses generated by the excess heat may lead to inductor damage or destruction.
- 3. Stress caused by a resin's temperature generated expansion and contraction may damage inductors.

The use of such resins, molding materials etc. is not recommended.

7. Handling

- ◆Breakaway PC boards (splitting along perforations)
 - 1. When splitting the PC board after mounting inductors and other components, care is required so as not to give any stresses of deflection or twisting to the board.
 - 2. Board separation should not be done manually, but by using the appropriate devices.
- ♦ General handling precautions
 - 1. Always wear static control bands to protect against ESD.
 - $\ensuremath{\mathbf{2}}.$ Keep the inductors away from all magnets and magnetic objects.
- Precautions
- 3. Use non-magnetic tweezers when handling inductors.4. Any devices used with the inductors (soldering irons, measuring instruments) should be properly grounded.
- 5. Keep bare hands and metal products (i.e., metal desk) away from chip electrodes or conductive areas that lead to chip electrodes.
- 6. Keep inductors away from items that generate magnetic fields such as speakers or coils.
- ◆Mechanical considerations
 - 1. Be careful not to subject the inductors to excessive mechanical shocks.
 - (1) If inductors are dropped on the floor or a hard surface they should not be used.
 - (2) When handling the mounted boards, be careful that the mounted components do not come in contact with or bump against other boards or components.

8. Storage conditions

♦Storage

1. To maintain the solderability of terminal electrodes and to keep the packaging material in good condition, care must be taken to control temperature and humidity in the storage area. Humidity should especially be kept as low as possible.

Recommended conditions

Ambient temperature Below 30°C

Humidity Below 70% RH

The ambient temperature must be kept below 40°C. Even under ideal storage conditions inductor electrode solderability decreases as time passes, so inductors should be used within 6 months from the time of delivery.

*The packaging material should be kept where no chlorine or sulfur exists in the air.

◆Storage

Technical considerations

Precautions

1. If the parts are stocked in a high temperature and humidity environment, problems such as reduced solderability caused by oxidation of terminal electrodes and deterioration of taping/packaging materials may take place. For this reason, components should be used within 6 months from the time of delivery. If exceeding the above period, please check solderability before using the inductors.

This catalog contains the typical specification only due to the limitation of space. When you consider the purchase of our products, please check our specification. For details of each product (characteristics graph, reliability information, precautions for use, and so on), see our Web site (http://www.ty-top.com/).