

## TELEDATA ELECTRONIC SERVICE CASE

The case with a basic equipment of special tools for the installation and maintenance of complex telecommunication systems and data networks.

6700 **BERNSTEIN** TELEDATA with tool set

6715 **BERNSTEIN** TELEDATA without tool set

### Description:

Case made from deep-drawn, impact-resistant, grained black plastic, with sturdy aluminium frame, dustproof and rainproof, acid- and scratch-resistant. 80 tools are clearly arranged on two removable tool trays, one of it on both sides, and in the plastic tray with adjustable partitions in the bottom of the case. The basic equipment for special operations at telecommunication systems and data networks may efficiently be completed by special tools additionally recommended.

The case has 2 locks.

**Outside dimensions: 470 x 340 x 170 mm**

**Weight without tools: approx. 4.600 kg**

**Weight with tools: approx. 8.700 kg**

### Tool set

No.	Description of individual tools	No.	Description of individual tools
2-265	<b>2 test prods</b> , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire	5-107	<b>Engineer's tweezers</b> , with bent tips, 150 mm, made from steel, nickel-plated
2-601	<b>IC-tweezers</b> , nickel-plated, 125 mm, for gripping, inserting and removing IC's	5-117	<b>Engineer's tweezers</b> , straight-flat-wide, 145 mm, made from steel, nickel-plated
2-620	<b>PLCC-extractor</b>	5-240	<b>Warding files</b> , 6-piece set, with wooden handles, in plastic wallet
2-701	<b>Insertion tool with sensor</b> , for connecting the wires and simultaneously cutting off the residual wire	5-505	<b>Insulation stripping tool</b> , with hook blade, for cable diameter of 4 up to 28 mm
3-112-2	<b>Side cutters</b> , 120 mm, for soft wire up to 1.0 mm, with rounded head, double leaf spring, chrome-plated, with transparent insulation	6-103	<b>Socket wrench</b> , 4.5 mm, chrome vanadium, chrome-plated, with square handle
3-134 VDE	<b>Side cutters</b> , 160 mm, for steel wire up to 1.6 mm Ø, chrome-plated, with VDE safety insulation	6-104	<b>Socket wrench</b> , 5.0 mm, chrome vanadium, chrome-plated, with square handle
3-235-1	<b>Telephone pliers</b> , 160 mm, chrome-plated, with BERNSTEINIT-insulation	6-105	<b>Socket wrench</b> , 5.5 mm, chrome-vanadium, chrome-plated, with square handle
3-532-1	<b>Flat nose pliers</b> , 160 mm, with long jaws, chrome-plated, with BERNSTEINIT-insulation	6-500-12	<b>Double open-ended wrench</b> , 12 x 13 mm, chrome vanadium, chrome-plated
3-574-1	<b>Water pump pliers</b> , 175 mm, made from chrome vanadium, chrome-plated, with BERNSTEINIT-insulation	6-500-18	<b>Double open-ended wrench</b> , 18 x 19 mm, chrome vanadium, chrome-plated
3-732-1	<b>Combination pliers</b> , 165 mm, chrome-plated, with BERNSTEINIT-insulation	6-600	<b>Combination ring- and open-ended wrench</b> , 7-piece set, chrome vanadium, chrome-plated, 6.0, 7.0, 8.0, 9.0, 10.0, 11.0, 13.0 mm
3-0605	<b>Combination crimping pliers</b> , 200 mm, for connector types 6P/6C, 6P/4C, 6P/2C, 8P/8C	6-600-12	<b>Combination ring- and open-ended wrench</b> , 12 mm, chrome vanadium, chrome-plated
4-222	<b>Screwdriver</b> , with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 260 x 3.0 mm, with black tip	6-600-17	<b>Combination ring- and open-ended wrench</b> , 17 mm, chrome vanadium, chrome-plated
4-227	<b>Crosspoint-screwdriver</b> , size 1, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 300 mm, with black tip	6-600-19	<b>Combination ring- and open-ended wrench</b> , 19 mm, chrome vanadium, chrome-plated
4-228	<b>Crosspoint-screwdriver</b> , size 2, with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 300 mm, with black tip	6-880	<b>Hexagon wrench keys</b> , 8-piece set in a wallet, 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 7/32", 1/4"
4-431	<b>Retaining screwdrivers</b> , for inserting and tightening slotted screws, blade made from chrome vanadium, nickel-plated, insulated, blade 100 x 3.0 mm,	6-950	<b>Ballpoint wrench keys</b> , hexagon, 8-piece set in a wallet, 1.5, 2.0, 2.5, 3.0, 4.0, 5.0, 6.0, 8.0 mm
4-437	<b>Retaining screwdriver</b> , for inserting and tightening cross-recess screws size 1, blade made from chrome vanadium, nickel-plated, insulated	6-995	<b>Torx screwdrivers with bore-hole in the tip</b> , 8-piece set in a box, T 9, T 10, T 15, T 20, T 25, T 27, T 30, T 40
14-651 VDE	<b>Screwdriver</b> , blade 75 x 2.5 mm, with VDE-insulation	7-425	<b>Duster</b>
14-652 VDE	<b>Screwdriver</b> , blade 100 x 3.5 mm, with VDE-insulation	7-506	<b>Roller tape measure</b> , 2 m
14-653 VDE	<b>Screwdriver</b> , blade 100 x 4.0 mm, with VDE-insulation	7-616	<b>Pocket saw</b> , with adjustable wooden handle, in a wallet
14-681 VDE	<b>Cross-recess screwdriver</b> , size 0, with VDE-insulation, blade length 60 mm	9-316/5	<b>5 Chip-Container</b> , conductive box with lid, black, internal dimensions: 118 x 32 x 14 mm
14-682 VDE	<b>Cross-recess screwdriver</b> , size 1, with VDE-insulation, blade length 80 mm		
14-683 VDE	<b>Cross-recess screwdriver</b> , size 2, with VDE-insulation, blade length 100 mm		
14-684 VDE	<b>Cross-recess screwdriver</b> , size 3, with VDE-insulation, blade length 150 mm		

### To complete the set we recommend:

2-751	<b>Test headphones</b> , 1 x 600 ohm, switchable from 600 to 10.000 ohm, with fine control including test prods, maximum load 2 W
2-702	<b>Insertion tool for systems HVT 71</b> , for connecting the cable conductors and jumper wires
8-110	<b>ERSA fine soldering iron</b> , Tip 260 BN/230 V/16 W
8-385	<b>ERSA OVAC X desoldering pump</b>

# TELEDATA 6700 ELECTRONIC SERVICE CASE

The service case for the ambitious Telecommunication engineer

