

This document is the property of Amphenol Aorora Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Aorora Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.

REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A	/	New Version	May 2016-04-14	Rain 2016-04-14	Hongkui.liu 2016-04-14
B	/	Increase the control	May 2016-12-05	Rain 2016-12-05	Hongkui.liu 2016-12-05

NO.	COMPONENTS	MATERIALS	FINISH/COLOR SPECIFICATION	QUANTITY
1	Housing	GLASS FILLED LCP,UL94V-0	NATURAL	1
2	Contact	PHOSPHOR BRONZE, T=0.20±0.01mm	80u" MIN. TIN PLATING ALL	N

NOTE:

1.MATERIAL:
HOUSING:LCP.NATURAL.UL94V-0.
CONTACT:PHOSPHOR BRONZE;T=0.20mm.

2.PLATING:

CONTACT:80~160u" Matter Tin plating over all,
40~120u" Ni underplating over all

3.▽ NOTATION FOR CPK AND X-R TEST SIZE

4.COMPLIANT TO RoHS DIRECTIVE

2002/95/EC AND SONY SS-00259.

5.PART NO. LEGEND:






F52L-*A7A1-110**-*B*00

1:With Mylar
2:Without Mylar



1A:LCP NATURAL
FA:LCP NATURAL(水口)
7A:Matter Tin plating

DIMENSION LIST:

NO.OF POS	NO.OF POS			NO. OF POSITIONS			
	A	B	C	A	B	C	
3	2.00	4.10	6.00	17	16.00	18.10	20.00
4	3.00	5.10	7.00	18	17.00	19.10	21.00
5	4.00	6.10	8.00	19	18.00	20.10	22.00
6	5.00	7.10	9.00	20	19.00	21.10	23.00
7	6.00	8.10	10.00	21	20.00	22.10	24.00
8	7.00	9.10	11.00	22	21.00	23.10	25.00
9	8.00	10.10	12.00	23	22.00	24.10	26.00
10	9.00	11.10	13.00	24	23.00	25.10	27.00
11	10.00	12.10	14.00	25	24.00	26.10	28.00
12	11.00	13.10	15.00	26	25.00	27.10	29.00
13	12.00	14.10	16.00	27	26.00	28.10	30.00
14	13.00	15.10	17.00	28	27.00	29.10	31.00
15	14.00	16.10	18.00	29	28.00	30.10	32.00
16	15.00	17.10	19.00	30	29.00	31.10	33.00




SUPPORTING TAPE





APPLICABLE FPC/FFC

KIND	TOLERANCE		
	P	W	M
FPC	±0.02	+0.10 -0.05	±0.05
FFC	±0.05	±0.03	±0.10



3D VIEW.



MOUNTING LAYOUT (CONN.MOUNTING SIDE)

UNLESS OTHERWISE SPECIFIED TOLERANCES		ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd	
X.	±0.50	X.	± 1'		
X.X	±0.30	X.X	± 0.5'	TITLE:	
X.XX	±0.20	X.XX	± 0.5'	FPC PITCH1.0mm NON-ZIF. SMT A TYPE	
X.XXX	±0.10	X.XXX	± 1'	DRAWN DATE: May 2016-12-05	
LINEAR DIMS	ANGLES DIMS	DOC TYPE: Customer Drw		DESIGN DATE: May 2016-12-05	
P/N: F52L-*A7A1-110**-*B*00				CHECKED DATE: Rain 2016-12-05	
MATERIAL	SEE NOTES	APPROVED DATE: Hongkui.liu 2016-12-05		SIZE: A4	DWG NO. A-S0289
FINISHED	SEE NOTES	SCALE: 1:1		UNIT: mm	SHEET 1 OF 1