

EFD Cores (8995151521)



Part Number: 8995151521

95 EFD CORE SET

EFD (Economical Flat Design) cores have been designed to maximize volume in a low profile geometry. EFD cores allow maximum throughput power density with reasonably low mass for board level installation.

EFD cores can be supplied with the center post gapped to a mechanical dimension or an A_L value.

[Catalog Drawing](#)
[3D Model](#)

Weight indicated is per pair or set.

Weight: 2.8 (g)

Dim	mm	mm tol	nominal inch	inch misc.
A	15	± 0.40	0.591	—
B	7.5	± 0.15	0.295	—
C	4.65	± 0.20	0.183	—
D	5.5	± 0.15	0.217	—
E	11	± 0.40	0.433	—
F	5.3	± 0.20	0.209	—
K	2.4	± 0.10	0.094	—



Chart Legend

$\Sigma l / A$: Core Constant, l_e : Effective Path Length, A_e : Effective Cross- Sectional Area, V_e :
Effective Core Volume
 A_L : Inductance Factor 

Explanation of Part Numbers: Digits 1 & 2 = product class and 3 & 4 = material grade.

Electrical Properties	
A_L (nH)	1050 ±25%
A_e (cm ²)	0.154
$\Sigma l / A$ (cm ⁻¹)	22.3
l_e (cm)	3.44
V_e (cm ³)	0.531
A_{min} (cm ²)	0.127

A_L value is measured at 1 kHz, B < 10 gauss.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Fair-Rite:](#)

[8995151521](#)