


Type Designation	4103
Designation IEC	LR03
System	Zn-MnO ₂ (Alkaline)
Shelf Life (Coding)*	5 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	1200 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	11
Volume [ccm]	3.5



Dimensions [mm]	min:	max:
Ø	9.5	10.5
A	-	44.5
B	43.3	-
C	4.3	-
E	-	0.5
F	-	3.8
G	0.8	-

Typical Capacities (at 20°C):



Discharge Type	Load	End Voltage[V]	0.9
15S/M, 8H/D, 7D/W	24 Ω	Time [h]	20,8
Remote control		Capacity [mAh]	1098
		Energy [mWh]	1399
Discharge Type	Load	End Voltage[V]	0.9
4M/H, 8H/D, 7D/W	5.1 Ω	Time [m]	259
Portable Lighting		Capacity [mAh]	989
		Energy [mWh]	1169
Discharge Type	Load	End Voltage[V]	0.9
1H/D, 7D/W	3,9 Ω	Time [min]	270
Toy		Capacity [mAh]	976
		Energy [mWh]	1096
Discharge Type	Load	End Voltage[V]	0.9
4H/D, 7D/W	75 Ω	Time [h]	73,3
Transistor Radios		Capacity [Ah]	1.20
		Energy [Wh]	1,51

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

* In consideration of typical loss of capacity at storage and application.