




Scotchlok™ Terminals

MNHU18-250DMI thru MNHU10-250DMI
Male Disconnect, Nylon Fully Insulated,
Heatshrink Insulated, Butted Seam



Data Sheet

Product Number	Wire Range (AWG)	Male Tab Width (W') x Thickness	L	W	D	Barrel Length	Barrel I.D.
MNHU18-250DMI	22-18	0.250 x 0.032	1.2	0.44	0.30	0.25	0.065
MNHU14-250DMI	16-14	0.250 x 0.032	1.2	0.44	0.30	0.25	0.085
MNHU10-250DMI	12-10	0.250 x 0.032	1.2	0.47	0.39	0.25	0.150

Specifications


Wire Size:	See Table Above
Barrel Seam:	Butted
Maximum Voltage Rating:	600 V Building Wire 1000 V Signs or Fixtures (Luminaires)
Maximum Temperature Rating:	221°F (105°C)
Maximum Current:	Same as Wire
Insulator Material:	Nylon/Adhesive lined Polyolefin, TMW
Terminal Material:	ETP Copper
Plating:	Tin

Installation Information

⚠ WARNING

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

For use on stranded copper (AWG) wire only.
Strip away the end 3/8 inch of wire insulation.
Make the crimp in the proper station of a recommended 3M™ crimp tool: TH-440, TH-450 (scissor style) hand tools.



Barrel Crimp (Required)

Shrink tubing using a heat gun. Heat until tubing is completely shrunk and adhesive protrudes slightly from the tubing.

Engineering Specification

Crimp-Type Male Quick Disconnect Terminals shall, electrically and mechanically connect permanently to a prestripped end of a stranded copper wire and, have a flat tongue portion for mating to a Female Quick Disconnect in a separable, reusable manner, forming a Quick Connect Wiring Connection.

The connector line shall offer a tongue variations (size 0.250 x 0.032 or 0.187 x 0.020 per ANSI/NEMA DC-2) and barrel variations in wire size 22-18 AWG, 16-14 AWG, 12-10 AWG and construction of nylon fully insulated plus polyolefin heatshrink material.

The tongue shall be marked with the wire range and the manufacturer's symbol.(↑)

The Nylon Fully Insulated Male Quick Disconnect with adhesive lined polyolefin shall be tin plated .032" thick copper, with a 0.250" wide blade conforming to ANSI/NEMA DC-2 dimensions and a 0.25" long barrel. The terminal shall be covered by a molded nylon funnel entry sleeve which extends to cover the tongue, and preapplied heat shrink tubing color coded, and sized for a specified (AWG) wire range (22-18, 16-14, 12-10).

3M and Scotchlok are trademarks of 3M

IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**

3M

Electrical Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
<http://www.3M.com/elpd>

Litho in USA.
© 3M 2002 78-8125-9868-4-B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

3M:

[MNHU10-250DMIK](#) [MNHU14-250DMIK](#) [MNHU18-250DMIK](#)