



Connectors > Automotive Connectors > Automotive Housings > TIMER, CONNECTOR HOUSING



Connector & Housing Type: **Housing for Female Terminals**

Mating Tab Width: **3 mm [.118 in]**

Connector System: **Wire-to-Wire**

Number of Positions: **2**

Centerline (Pitch): **5 mm [.196 in]**

[All TIMER, CONNECTOR HOUSING \(540\)](#)

Features

Product Type Features

Connector Shape	Rectangular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Hybrid Connector	No
Primary Locking Feature	On the Terminal
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
Number of Rows	1

Electrical Characteristics

Operating Voltage	24 VDC
Nominal Voltage Architecture	12 V, 24 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black
Connector & Keying Code	Neutral



Contact Features

Contact Size	2.8mm
Contact Type	Receptacle
Mating Tab Width	3 mm[.118 in]
Contact Current Rating (Max)	20 A

Mechanical Attachment

Terminal Position Assurance	Yes
Strain Relief	Without
Mating Alignment Type	Polarization Slot
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	PA
Centerline (Pitch)	5 mm[.196 in]

Dimensions

Connector Height	37.5 mm[1.476 in]
Product Width	22 mm[.866 in]
Product Length	23.8 mm[.937 in]

Usage Conditions

Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C[158 °F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F]
Operating Temperature Range	-30 – 125 °C[-22 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Method	Bag
------------------	-----

Other

Serviceable	No
Connector Position Assurance Capable	No



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 828905-1
SINGLE-WIRE-SEAL(5MM HOLE)




TE Part # 828904-1
SINGLE WIRE SEAL FOR J.P.T.CON




TE Part # 828906-2
BLINDSTOPFEN 1,5SYS



TE Part # CAT-T4827-T273
TIMER, RECEPTACLE AND TAB



TE Part # 106462-1
2P.FASTIN-ON HSG.



TE Part # 282536-1
S.WAY SEAL F.JPT CONTACT 2.5MM




TE Part # 1-929937-1
JPT REC 2.8 Contact SWS Au




TE Part # 828906-1
CAVITY PLUG (5MM HOLE)


Also in the Series | Timer Connector System




Automotive Connector Caps & Covers (11)




Automotive Connector Locks & Position Assurance (16)




Automotive Housings (218)




Automotive Seals & Cavity Plugs (31)




Automotive Terminals (131)



Crimp Terminal Housings (13)




Insertion & Extraction Tools (20)



Other Automotive Connector Accessories (1)



PCB Headers & Receptacles (78)



Quick Disconnects (4)

Customers Also Bought



TE Part #1-2066502-4
COVER 2 POS MINI FUSE BOX, MAT-2



TE Part #1554461-2
33POS, 1.0 SERIES, REC HSG ASSY, SLD




TE Part #1719668-1
2.LOCK REC HSG




TE Part #2338360-1
2P ECONOSEAL RECEPTACLE ASSY







TE Part #2822352-2
070 TYPE RUBBER PLUG




TE Part #0021036033
RBK-ILS-125-NR3-0-25MM




TE Part #6776556004
RPPM-NR510-X-50MM



TE Part #925014
2 P FF 110(2.8 MM) HOUSING RECEPTACLE



TE Part #2338363-1
2P ECONOSEAL RECEPTACLE DBL



TE Part #9-2363287-9
48 POS MIXED REC HSG BN

Documents

Product Drawings

SPLASH PROOF CONN. W.S.L.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_282189-1_M_c-282189-1-m.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_282189-1_M_c-282189-1-m.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_282189-1_M_c-282189-1-m.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Timer Interconnection System

English

Product Specifications

Product Specification

English

Instruction Sheets

2-7 positions junior power timer splash proof connectors



English

[Instruction Sheet \(non U.S.\)](#)

English

[2-7 positions Junior Power Timer splash proof connectors \(english version\)](#)

English

[Instruction Sheet \(non U.S.\)](#)

English