

accessories

pneumatic sleeve valve


The pneumatic sleeve valve has been introduced to complement the LF 3000 push-in fitting range. Sleeve valves may be used to effect an immediate isolation of

the air line by venting the system to atmosphere. The design is :
 - **compact**
 - **neat**

- **aesthetically pleasing** and can be directly installed in the circuit.

How it works



By moving the sleeve in one direction, the air is free to pass through the sleeve valve to the system. By moving it in the opposite direction, the supply is shut off and the air that had previously passed through to the system is allowed to escape to the atmosphere.



Technical characteristics



- direction of medium 1 way
- medium compressed air
- body nickel plated brass
- sleeve anodised aluminium
- seals nitrile rubber
- minimum working temp. -10°C
- maximum working temp. +80°C
- maximum working pressure 16 bar

0669 double female sleeve valve



C	DN	F	G	L	kg
1/8	4	14	25	48	0,051
1/4	7	19	30	58	0,084
3/8	10	22	35	68	0,153
1/2	14	27	40	80	0,227

Clip clip strips for tubes



ØD	H	K	N	Number of clips per strip	Ø LF 3000 to be clipped	kg
4	9	13,5	10,5	8		0,008
6	10,5	13	10,5	8		0,009
8	12,5	10,5	12	7	4	0,009
10	14	12	15	6	6	0,010
12	16,5	14	16,5	5		0,011
14	18	16	20,5	4	8	0,012

Delivered in boxes of 5 strips of the same diameter (complete with self-tapping screws of 9.5 mm length).