

## HDC 32B KLU 1M32G

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

### General ordering data

|            |  |
|------------|--|
| Version    | HDC enclosures, Size: 10, Protection degree: IP65 (in plugged condition), Coupling housing, End-locking clamp, lower side, Standard, Size of cable entries: M 32 |
| Order No.  | <a href="#">1788500000</a>   |
| Type       | HDC 32B KLU 1M32G  |
| GTIN (EAN) | 4032248206032  |
| Qty.       | 1 pc(s).   |

## HDC 32B KLU 1M32G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Depth      | 107 mm   | Depth (inches)  | 4.213 inch |
| Height     | 83 mm    | Height (inches) | 3.268 inch |
| Width      | 115.9 mm | Width (inches)  | 4.563 inch |
| Net weight | 454 g    |                 |            |

## Temperatures

|                   |                   |
|-------------------|-------------------|
| Limit temperature | -40 °C ... 125 °C |
|-------------------|-------------------|

## Dimensions

|                      |           |                     |         |
|----------------------|-----------|---------------------|---------|
| Cable entry          | w. thread | Height of housing B | 83 mm   |
| Total length housing | 94 mm     | Width housing C     | 82.5 mm |

## General data

|                             |                             |                       |                             |
|-----------------------------|-----------------------------|-----------------------|-----------------------------|
| EMC housings                | No                          | Housing main material | diecast aluminium           |
| Material of locking element | Stainless steel, rust-proof | Protection degree     | IP65 (in plugged condition) |
| Surface finish              | Powder coating              | Tightening torque     | 2 Nm                        |

## Version

|                              |                               |                                |                  |
|------------------------------|-------------------------------|--------------------------------|------------------|
| BG                           | 10                            | Cable entry                    | w. thread        |
| Clamp version                | End-locking clamp             | Colour (RAL)                   | RAL 7035         |
| Design                       | Standard                      | Design of housing              | Coupling housing |
| Design of locking system     | End-locking clamp, lower side | Internal thread                | M 32             |
| Number of cable entry on top | 1                             | Number of cable entry sideways | 0                |
| Sealing                      | NBR                           | Size                           | 10               |
| Size of cable entries        | M 32                          | Suitable for ModuPlug®         | Yes              |
| Tightening torque            | 2 Nm                          | Top part/bottom part/lid       | lower part       |
| Type                         | coupling extension            |                                |                  |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000437    | ETIM 7.0    | EC000437    |
| ETIM 8.0    | EC000437    | ECLASS 9.0  | 27-44-02-02 |
| ECLASS 9.1  | 27-44-02-02 | ECLASS 10.0 | 27-44-02-02 |
| ECLASS 11.0 | 27-44-02-02 | ECLASS 12.0 | 27-44-02-02 |

|                     |                         |
|---------------------|-------------------------|
| Substance           | Acetone                 |
| Chemical resistance | Conditionally resistant |
| Substance           | Drilling oil            |
| Chemical resistance | Resistant               |
| Substance           | Diesel                  |
| Chemical resistance | Resistant               |
| Substance           | Ethyl alcohol           |
| Chemical resistance | Resistant               |
| Substance           | Transmission oil        |
| Chemical resistance | Resistant               |

Creation date January 28, 2023 7:20:50 AM CET

## HDC 32B KLU 1M32G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

|                     |                         |
|---------------------|-------------------------|
| Substance           | Hydraulic oil           |
| Chemical resistance | Resistant               |
| Substance           | Coolant                 |
| Chemical resistance | Resistant               |
| Substance           | Petroleum benzine       |
| Chemical resistance | Resistant               |
| Substance           | Sweat                   |
| Chemical resistance | Resistant               |
| Substance           | Premium gasoline        |
| Chemical resistance | Conditionally resistant |
| Substance           | Water                   |
| Chemical resistance | Resistant               |
| Substance           | UV                      |
| Chemical resistance | Unstable                |
| Substance           | Ozone                   |
| Chemical resistance | Unstable                |

## Environmental Product Compliance

|                     |  |
|---------------------|--|
| REACH SVHC          | Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3  |
| SCIP                | e98b2b24-ba23-41bf-8d19-0dda3647412f   |
| Chemical resistance | de.myview.objectmodel.impl.BlockImpl@2f172fc8 de.myview.objectmodel.impl.BlockImpl@514ecb89<br>de.myview.objectmodel.impl.BlockImpl@38d429ce de.myview.objectmodel.impl.BlockImpl@21174128<br>de.myview.objectmodel.impl.BlockImpl@37e843ad de.myview.objectmodel.impl.BlockImpl@10ddc45a<br>de.myview.objectmodel.impl.BlockImpl@9de15d6 de.myview.objectmodel.impl.BlockImpl@125b0bc4<br>de.myview.objectmodel.impl.BlockImpl@675bc709 de.myview.objectmodel.impl.BlockImpl@19da20ac<br>de.myview.objectmodel.impl.BlockImpl@6053f6e4 de.myview.objectmodel.impl.BlockImpl@2a1cc401<br>de.myview.objectmodel.impl.BlockImpl@13c63dc4 |

## Approvals

Approvals



|                         |            |
|-------------------------|------------|
| ROHS                    | Conform    |
| UL File Number Search   | UL Website |
| Certificate No. (cURus) | E92202     |

## Downloads

|                             |  |
|-----------------------------|--|
| Engineering Data            | <a href="#">CAD data – STEP</a>  |
| Engineering Data            | <a href="#">WSCAD</a>  |
| Product Change Notification | <a href="#">20220214 Technical change to HDC housings</a><br><a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a> |
| Technical Documentation     | <a href="#">1788500000_HDC_32B_KLU_1M32G_STP_Blatt__1.pdf</a>  |
| Catalogues                  | <a href="#">Catalogues in PDF-format</a>   |
| Brochures                   | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a>   |

Creation date January 28, 2023 7:20:50 AM CET

Catalogue status 24.01.2023 / We reserve the right to make technical changes.

3

**Data sheet**

**HDC 32B KLU 1M32G**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

