

# Intelligent Infrared Carbon Dioxide Module (Model: MH-Z14A)

User's Manual V1.4

Issue Date. Mar. 31st,2021

Zhengzhou Winsen Electronics Technology CO., LTD.

Email: <a href="mailto:sales@winsentech.com">sales@winsentech.com</a>

**Statement** 

The copyright of this manual belongs to Zhengzhou Winsen Electronics Technology Co., LTD.

Without the written permission, any part of this manual shall not be copied, translated, stored in

database or retrieval system, also can't spread through electronic, copying, record ways.

Thanks for purchasing our product. In order to enable customers to better use the product and

reduce the faults caused by misuse, please read the manual carefully and operate it correctly in

accordance with the instructions. If users disobey the terms or remove, disassemble, change the

components inside of the sensor, we shall not be responsible for the loss.

The specific such as color, appearance, sizes ...etc., please in kind prevail.

We are devoting ourselves to products development and technical innovation, so we reserve the

right to improve the products without notice. Please confirm it is the valid version before using this

manual. At the same time, users' comments on optimized using way are welcome.

Please keep the manual properly, in order to get help if you have questions during the usage in the


future.

Zhengzhou Winsen Electronics Technology CO., LTD

# MH-Z14A NDIR CO2 Module

## 1. Profile

MH-Z14A NDIR Infrared gas module is a common type, small size sensor, using non-dispersive infrared (NDIR) principle to detect the existence of CO<sub>2</sub> in the air, with good selectivity, non-oxygen dependent and long life. Built-in temperature sensor can do temperature compensation; and it has digital output and PWM output. This common type infrared gas sensor is developed by the tight integration of mature infrared absorbing gas detection technology, Precision optical circuit design and superior circuit design.



#### 3. Main Features

Chamber is gold plated, water-proof and anti-corrosion High sensitivity, low power consumption Good stability

Temperature compensation, excellent linear output Multiple output modes: UART, PWM

Long lifespan

Anti-water vapor interference, anti-poisoning

# 2. Applications

\*HVAC refrigeration \*Air cleaner device \*Indoor air quality monitoring \*Smart home


\*Ventilation system

# 4. Main technical parameters


Model No.	MH-Z14A				
Detection Gas	CO2 gas				
Working voltage	DC (5.0±0.1V)				
Average current	< 40 mA (@5V supply)				
Peak current	125mA (@5V supply)				
Interface level	3.3 V (5V compatible)				
Measuring range	400~10000ppm optional				
Output signal	Serial port(UART) (TTL)				
Output signal	PWM				
Preheat time	1min				
Response Time	T90 < 120s				
Working temperature	10°C × 50°C				
Working humidity	0~95%RH(no condensation)				
Storage temperature	30°C ~ 60°C				
Weight	14 g				
Lifespan	>10 years				

Target Gas	Measuring Range	Resolution	Accuracy	
	400~2000ppm			
Carbon Dioxide (CO2)	400~5000ppm	1ppm	±(50ppm	
(CO2)	400~10000ppm		+5%reading value)	

# 5. Structure



# 6. Definition for pins



PIN No	Description
1,15,23	Power positive (Vin)
2,3,12, 22	Power negative (GND)
4,5,21	Analog output
6,26	PWM
8, 20	HD(for zero-point calibration, low level lasting for
	over 7 sec is effective)
7,9	NC
11, 14, 24	UART(RXD) TTL data input
10,13, 25	UART(TXD)TTL data output

# 7. Two Output ways

# ● PWM output

Take 400~2000ppm for example	
CO2 output range	400~2000ppm
Cycle	1004ms±5%
Cycle start high level output	2ms(theoretical value)
The middle cycle	1000ms±5%
cycle end low level output	2ms(theoretical value)
CO2 concentration: Cppm=2000×(TH-2m	ns)/(TH+TL-4ms)
C <sub>ppm</sub> : CO2 concentration could be calculated	ed by PWM output
TH high level output time during cycle	
TL low level output time during cycle	
202 m s 400 ppm 502 m s 1000 ppm 752 m s 1500 ppm 1002 m s 2000 ppm	∬

# Serial port output (UART)

## **Hardware connection**

Connect module's Vin-GND-RXD-TXD to users' 5V-GND-TXD-RXD. (Users must use TTL level. If RS232 level, it must be converted.)

# **Software setting**

Set serial port baud rate be 9600, data bit 8 bytes, stop bit 1byte, parity bit null.

## **Command List:**

0x86	Gas concentration
0x87	Calibrate zero point (ZERO)
0x88	Calibrate span point (SPAN)
0x79	ON/OFF Self-calibration function for zero point
0x99	Detection range setting

Email: <a href="mailto:sales@winsentech.com">sales@winsentech.com</a>

<b>0x86-</b> Rea	ad CO2 conce	ntration						
Sending c	ommand							
Byte0	Byte1	Byte2	Byte3	Byte4	Byte5	Byte6	Byte7	Byte8
Start Byte	Reserved	Command	-	-	-	-	-	Checksum
0xFF	0x01	0x86	0x00	0x00	0x00	0x00	0x00	0x79
Return val	ue							
Byte0	Byte1	Byte2	Byte3	Byte4	Byte5	Byte6	Byte7	Byte8
Start Byte	Command	Concentration	Concentration	-	-	-	-	Checksum
		(High 8 Byte)	(Low 8 Byte)					
0xFF	0x86	HIGH	LOW	-	-	-	-	Checksum

CO2 concentration = HIGH \* 256 + LOW

For example:

Send command FF 01 86 00 00 00 00 00 79, Return value FF 86 02 20 00 00 00 00 58

How to calculate concentration: convert hexadecimal 02 into decimal 2, hexadecimal 20 into decimal 32, then 2\*256+32=544ppm

0x79- On/0	0x79- On/Off Self-calibration for Zero Point										
Send command-No return value											
Byte0	Byte1	Byte2	Byte3	Byte4	Byte5	Byte6	Byte7	Byte8			
Start Byte	Reserved	Command	-	-	-	-	-	Checksum			
0xFF	0x01	0x79	0xA0/0x00	0x00	0x00	0x00	0x00	Checksum			

For example:

ON this function, send command: FF 01 79 A0 00 00 00 00 E6 OFF this function, send command: FF 01 79 00 00 00 00 00 86  $\,$ 

NOTE: This function is on when Byte3 is 0xA0 while this function is off when Byte3 is 0x00.

Default status is "this function is on".

0x99- Det	ection range set	tting						
Send comr	mand-No return	value						
Byte0	Byte1	Byte2	Byte3	Byte4	Byte5	Byte6	Byte7	Byte8
Start	Reserved	Com	Reserved	Detection	Detection	Detection	Detection	Check
Byte		mand		range 24~32	range 16~23	range 8~15	range 0~7	sum
				bit	bit	bit	bit	
0xFF	0x01	0x99	0x00	Data 1	Data 2	Data 3	Data 4	Check
								sum

Note: Detection range should be 0~2000, 0~5000, or 0~10000ppm.

For example: set  $0\sim2000$ ppm detection range, send command: FF 01 99 00 00 00 07 D0 8F

set 0~10000ppm detection range, send command: FF 01 99 00 00 00 27 10 2F

#### 1. Checksum calculation method

Checksum = (Negative (Byte1+Byte2+Byte3+Byte4+Byte5+Byte6+Byte7))+1

#### For example:

Byte0	Byte1	Byte2	Byte3	Byte4	Byte5	Byte6	Byte7	Byte8
Start Byte	Reserved	Comman	-	-	-	-	-	Check
		d						sum
0xFF	0x01	0x86	0x00	0x00	0x00	0x00	0x00	Check
								sum

#### Calculating Checksum:

- 1. Add Byte 1 to Byte 7: 0x01 + 0x86 + 0x00 + 0x00 + 0x00 + 0x00 + 0x00 = 0x87
- $2 \cdot \text{Negative: } 0xFF 0x87 = 0x78$
- 3, Then+1: 0x78 + 0x01 = 0x79

#### C language

```
char getCheckSum(char *packet)
{
    char i, checksum;
    for( i = 1; i < 8; i++)
    {
        checksum += packet[i];
    }
    checksum = 0xff - checksum;
    checksum += 1;
    return checksum;
}
```

#### 8. Zero Point Calibration

#### About zero point calibration:

This module has three methods for zero point calibration: hand-operated method, sending command method and self-calibration. All the zero point is at 400ppm CO2.

**Hand-operated method**: Connect module's HD pin to low level(0V), lasting for 7 seconds at least. Before calibrating the zero point, please ensure that the sensor is stable for more than 20 minutes at 400ppm ambient environment.

#### Sending command method:

Zero and Span point calibration can be achieved by sending a calibration command to the sensor via the serial port (URAT). Zero and SPAN point calibration commands are as follows:

0x87-ZERO	0x87-ZERO POINT CALIBRATION									
Send comm	and-no returr	n value								
Byte0	Byte1	Byte2	Byte3	Byte4	Byte5	Byte6	Byte7	Byte8		
Start Byte	Reserved	Command	5	95.7	15.1	(5)	150	Checksum		
0xFF	0x01	0x87	0x00	0x00	0x00	0x00	0x00	0x78		

#### For example:

Put the module in 400ppm standard CO2 gas or clean outdoor environment for at least 20 min;

Send command FF 01 87 00 00 00 00 00 78 for zero point calibration.

Caution: Forbid sending this command in other environment except above.

0x88- SPAN POINT CALIBRATION										
Send comm	and-no returr	n value								
Byte0	Byte1	Byte2	Byte3	Byte4	Byte5	Byte6	Byte7	Byte8		
Start Byte	Reserved	Command	Span(High 8 Byte)	Span(low 8 Byte)	-	1=0		Checksum		
0xFF	0x01	0x88	HIGH	LOW	0x00	0x00	0x00	Checksum		

#### For example:

Put the module in 2000ppm CO2 gas, stability for 20 min at least.

If span value is 2000ppm, then HIGH=2000/256, LOW = 2000 % 256

Send command FF 01 88 07 D0 00 00 00 A0 for span calibration

Caution: Zero calibration should be done before span calibration.

It is recommended to use 2000ppm as the SPAN calibration value.

If lower value as the span value is needed, choose a value above 1000ppm.

#### Self-calibration:

After the module works for some time, it can judge the zero point intelligently and do the zero calibration automatically. The calibration cycle is every 24 hours since the module is power on. The zero point is 400ppm. This method is suitable for office and home environment, not suitable for agriculture greenhouse, farm, refrigerator, etc.. If the module is used in latter environment, please turn off this function.

### 9. Notes

9.1 Please avoid the pressure of its gilded plastic chamber from any direction, during welding, installation, and use.

- 9.2 When placed in small space, the space should be well ventilated, especially for diffusion window.
- 9.3 The module should be away from heat, and avoid direct sunlight or other heat radiation.
- 9.4 The module should be calibrated termly, the suggested period is not longer than 6 months.
- 9.5 Do not use the sensor in the high dusty environment for long time.
- 9.6 To ensure the normal work, the power supply must be among 4.5V~5.5V DC rang, the power current must be not less than 150mA. Out of this range, it will result in the failure of the sensor. (The concentration output is low, or the sensor can not work normally.)
- 9.7 During the zero point calibration procedure by manual, the sensor must work in stable gas environment (400ppm) for over 20 minutes. Connect the HD pin to low level (0V) for over 7 seconds.

Zhengzhou Winsen Electronics Technology Co.,

Ltd

Add: No.299, Jinsuo Road, National Hi-Tech Zone,

Zhengzhou 450001 China **E-mail:** sales@winsentech.com **Website:** www.winsentech.com