



BE-T-B_T1-SW-013

Тесты демонстрации производительности для микропроцессора Baikal-T1

Список изменений

Revision	Date	Description
1.0	15.03.2017	Initial version
1.1	08.08.2017	Added SPEC CPU2006 Int results
2.0	15.07.2018	Migration to gcc8.1 compiler. Added SPEC CPU2006 FP results.
2.1	18.07.2018	Iperf results for XGbE added.
2.2	20.07.2018	FIO results for PCIE, SATA, USB added.



Содержание

Список изменений.....	1
1. Список тестов демонстрации производительности.....	3
2. Оборудование для демонстрации производительности.....	5
3. Результаты тестов демонстрации производительности.....	5
4. Лог запуска тестов.....	7
Coremark.....	7
Whetstone.....	9
Dhrystone.....	10
STREAM.....	11
5. Результаты SPEC CPU2006.....	12
6. Производительность Gigabit Ethernet.....	15
7. Производительность 10 Gigabit Ethernet.....	16
Предварительные настройки.....	16
Запуск.....	17
Результаты.....	17
8. Производительность PCIe.....	19
9. Производительность SATA.....	20
10. Производительность USB.....	21

1. Список тестов демонстрации производительности

Test name	Description	Comments
Coremark	List processing (find and sort), Matrix_(mathematics) manipulation (common matrix operations), <u>state machine</u> (determine if an input stream contains valid numbers), and CRC.	OpenSource Multi-threading Integer Performance Results http://www.coremark.org/benchmark
Dhrystone	Developed in 1984 by R.P. Wecker, Dhrystone is a benchmark program written in C that tests a system's integer performance. The program is CPU bound, performing no I/O functions or operating system calls. Dhrystones per second is the metric used to measure the number of times the program can run in a second. Original versions of the benchmark gave performance ratings in terms of Dhrystones per second. This was later changed to VAX MIPS by dividing Dhrystones per second by 1757, the DEC VAX 11/780 result.	Integer Performance OpenSource Results http://www.roylongbottom.org.uk/dhrystone%20results.htm
Whetstone	The Whetstone benchmark measure computing power in units of Millions of Whetstone Instructions Per Second (MWIPS). Test Loop In Tables 1. floating point MFLOP 1 2. floating point MFLOP 2 3. if then else IF MOPS 4. fixed point FIXPT MOPS 5. sin,cos etc. COS MOPS 6. floating point MFLOP 3 7. assignments EQUAL MOPS 8. exp,sqrt etc. EXP MOPS	OpenSource Multi-threading Floating-Point Performance (Double and Single precision) Results http://freespace.virgin.net/roy.longbottom/whetstone%20results.htm#anchorandroidC
Stream	This program measure memory transfer rates in MB/s for simple operations (copy, scale, add, and triad) http://www.cs.virginia.edu/stream/	Multi-threading OpenSource Results

		http://ssvb.github.io/2011/09/13/origenboard-memory-performance.html
SPEC CPU 2006 INT	List of Benchmarks 400.perlbench (C) Programming Language 401.bzip2 (C) Compression 403.gcc (C) C Compiler 429.mcf (C) Combinatorial Optimization 445.gobmk (C) Artificial Intelligence: Go 456.hmmmer (C) Search Gene Sequence 458.sjeng (C) Artificial Intelligence: chess 462.libquantum (C) Physics / Quantum Computing 464.h264ref (C) Video Compression 471.omnetpp (C++) Discrete Event Simulation 473.astar (C++) Path-finding Algorithms 483.xalancbmk (C++) XML Processing	Results http://spec.org/cpu2006/results/
Iperf	Iperf is a test for network performance measurement. Iperf has “client” and “server” functionality, and can create data streams to measure the throughput between the two ends.	OpenSource
fio	Flexible I/O Tester. fio is a tool that will spawn a number of threads or processes doing a particular type of I/O action as specified by the user. The typical use of fio is to write a job file matching the I/O load one wants to simulate.	OpenSource https://github.com/axboe/fio
hdparm	hdparm is a command line program for Linux to set and view ATA hard disk drive hardware parameters and test performance. It can set parameters such as drive caches, sleep mode, power management, acoustic management, and DMA settings. GParted and Parted Magic both include hdparm. Perform timings of device (-t) and cache (-T) reads for benchmark and comparison purposes.	OpenSource

2. Оборудование для демонстрации производительности

Процессор	CPU: MIPS32 P5600 @ 1200 MHz (Rev 1.0) FPU: Present Cores: 2 Timer: 600 MHz ECC: L1 L2 (80800ff0) PLLs: CPU: 1200MHz SATA: 600MHz ETH:1250MHz PCIE:1200MHz DDR3: 400MHz AXI: 600MHz
Плата	Baikal-T1 BFK3.1
Память	Kingston KVR16S11/8. 1.5V 1G x 64-bit (8GB) DDR3-1600 CL11 SDRAM
OS	Linux 4.4.135
SDK	Baikal-T1 SDK 4.14 (https://www.baikalelectronics.ru/products/T1/?type=razrabotka)
Disks	SSD Intel DC S3510 Series 120 GB SSDSC2BB120G601 ORICO 2.5 inch USB2.0 Hard Drive Enclosure (2588US) Plextor M8Pe 128GB PCIe Gen 3 x4

3. Результаты тестов демонстрации производительности

OS: Linux 4.4.135

При сборке бенчмарков используются следующие компиляторы с опциями.

Compilers:

- GCC 8.1 -Ofast -funroll-all-loops -mmsa -EL -mtune=p5600 -static
- Для получения максимальной производительности на coremark

в качестве компилятора использовался Mentor тулчейн 4.9.1(2014.1-22)

<https://sourcery.mentor.com/GNUToolchain/subscription3537?lite=MIPS>

с плагином (tree_switch_shortcut_elf-2014.11-21.so)

<http://community.imgtec.com/developers/mips/tools/benchmarks/> в качестве компоновщика

<https://sourcery.mentor.com/GNUToolchain/release2935>

GCC4.9.1 -static -O3 -funroll-all-loops -fgcse-sm -fgcse-las -finline-functions -finline-limit=1000 -msoft-float -EL -march=74kc -falign-functions=16 -mno-dsp -fplugin=./tree_switch_shortcut_elf-2014.11-21.so



Benchmark	Baikal-T1 MIPS P5600 1200 MHz		Compiler / Software
Coremark	GCC 8.1 Coremarks 10653 (2 threads) Coremarks/MHz 8.88 Coremarks/Mhz/core 4.44	Mentor GCC 4.9.1 with plugin Coremarks 13142 (2 threads) Coremarks/MHz 10.95 Coremarks/Mhz/core 5.47	GCC 8.1 MentorGCC 4.9
Dhrystone	4432 VAX MIPS (1 thread) 3.69 DMIPS/Mhz		GCC 8.1
Whetstone	1679 MWIPS (2 threads) 0.69 MWIPS/Mhz/core		GCC 8.1
STREAM	Copy: 3307 MB/s Scale: 3300 MB/s Add: 2479 MB/s Triad: 2482 MB/s		GCC 8.1
SPEC CPU2006	INT(geomean) 5.6 FP(geomean) 3.8 FP(geomean without milc, gamess) 4.8		GCC 8.1
iperf	1 Gb Ethernet Bandwidth: 940 Mbits/sec (TCP) 10 Gb Ethernet Bandwidth: 3050 Mbits/sec (TCP)		iperf2.0.8 iperf3.2 GCC 8.1
FIO	PCEe (SSD Plextor) WRITE: bw=454MiB/s ; READ: bw=654MiB/s SATA (Intel SSD 120 GB) WRITE: bw=139MiB/s; READ: bw=366MiB/s USB2.0 (Intel SSD 120 GB over ORICO USB2.0 Hard Drive Adapter) WRITE: bw=39.1MiB/s ; READ: bw=37.9MiB/s		fio3.7

4. Лог запуска тестов

Coremark

```
developer@baikal:~ $ ./coremark_49.exe
2K performance run parameters for coremark.
CoreMark Size      : 666
Total ticks        : 16740
Total time (secs) : 16.740000
Iterations/Sec     : 13142.174432
Iterations         : 220000
Compiler version  : GCC4.9.1
Compiler flags    : -O3 -funroll-all-loops -fgcse-sm -fgcse-las -finline-
functions -finline-limit=1000 -msoft-float -EL -G4
-fplugin=./tree_switch_shortcut_elf-2014.11-21.so -march=74kc -falign-
functions=16 -mno-dsp -DMULTITHREAD=2 -DUSE_FORK -DPERFORMANCE_RUN=1 -lrt
Parallel Fork : 2
Memory location   : Please put data memory location here
                   (e.g. code in flash, data on heap etc)
seedcrc          : 0xe9f5
[0]crclist       : 0xe714
[1]crclist       : 0xe714
[0]crcmatrix     : 0x1fd7
[1]crcmatrix     : 0x1fd7
[0]crcstate      : 0x8e3a
[1]crcstate      : 0x8e3a
[0]crcfinal      : 0x33ff
[1]crcfinal      : 0x33ff
Correct operation validated. See readme.txt for run and reporting rules.
CoreMark 1.0 : 13142.174432 / GCC4.9.1 -O3 -funroll-all-loops -fgcse-sm -fgcse-
las -finline-functions -finline-limit=1000 -msoft-float -EL -G4
-fplugin=./tree_switch_shortcut_elf-2014.11-21.so -march=74kc -falign-
functions=16 -mno-dsp -DMULTITHREAD=2 -DUSE_FORK -DPERFORMANCE_RUN=1 -lrt /
Heap / 2:Fork

developer@baikal:~ $ ./coremark_81.exe
2K performance run parameters for coremark.
CoreMark Size      : 666
Total ticks        : 20650
Total time (secs) : 20.650000
Iterations/Sec     : 10653.753027
Iterations         : 220000
Compiler version  : GCC8.1.0
Compiler flags    : -static -lrt -Ofast -funroll-all-loops -fgcse-sm -fgcse-las
-finline-functions -finline-limit=1000 --fast-math -EL -march=p5600 -mtune=p5600
-falign-functions=16
Parallel Fork : 2
```



Memory location : Please put data memory location here
(e.g. code in flash, data on heap etc)

seedcrc : 0xe9f5
[0]crclist : 0xe714
[1]crclist : 0xe714
[0]crcmatrix : 0x1fd7
[1]crcmatrix : 0x1fd7
[0]crcstate : 0x8e3a
[1]crcstate : 0x8e3a
[0]crcfinal : 0x33ff
[1]crcfinal : 0x33ff

Correct operation validated. See readme.txt for run and reporting rules.

CoreMark 1.0 : 10653.753027 / GCC8.1.0 -static -lrt -Ofast -funroll-all-loops
-fgcse-sm -fgcse-las -finline-functions -finline-limit=1000 --fast-math -EL
-march=p5600 -mtune=p5600 -falign-functions=16 / Heap / 2:Fork



Whetstone

```

developer@baikal: $ # ./whetsmp.exe
#####
get_nprocs() - CPUs 2, Configured CPUs 2
get_phys_pages() and size - RAM Size 3.61 GB, Page Size 16384 Bytes
uname() - Linux, localhost.localdomain, 4.4.135-bfk3-06728-gc5040bf
#51 SMP Thu Jun 21 19:55:09 MSK 2018, mips

```

Multithreading Single Precision Whetstones 32-Bit Version 1.0

Using 2 threads - Wed Jul 18 08:55:31 2018

```

Calibrate
  0.01336 Seconds      1   Passes (x 100)
  0.06249 Seconds      5   Passes (x 100)
  0.30946 Seconds     25   Passes (x 100)

```

Use 807 passes (x 100)

```

MFLOPS 1      411      408
MFLOPS 2      474      471
IFMOPS       8110     7160
FIXPMOPS 22352471363444
COSMOPS        14       14
MFLOPS 3      265      265
EQUMOPS       9616     9091
EXPMOPS        11       11
millisec     9608     9595
MWIPS         840      841

```

Thread	MWIPS	MFLOPS 1	MFLOPS 2	MFLOPS 3	Cos MOPS	Exp MOPS	Fixpt MOPS	If MOPS	Equal MOPS
Total	1681	819	945	530	27	223598691	15270	18707	

MWIPS 1679 Based on time for last thread to finish

Results Of Calculations Thread 1

```

MFLOPS 1      -1.12356138229370117      MFLOPS 2      -1.13133072853088379
IFMOPS        1.0000000000000000000      FIXPMOPS      12.0000000000000000000
COSMOPS       0.49911013245582581         MFLOPS 3      0.99999982118606567
EQUMOPS       3.0000000000000000000         EXPMOPS       0.93536460399627686

```



Dhrystone

```
developer@baikal:~$ ./dhry.exe
```

```
#####  
get_nprocs() - CPUs 2, Configured CPUs 2  
get_phys_pages() and size - RAM Size 3.61 GB, Page Size 16384 Bytes  
uname() - Linux, localhost.localdomain, 4.4.135-bfk3-06728-gc5040bf  
#51 SMP Thu Jun 21 19:55:09 MSK 2018, mips
```

Dhrystone Benchmark, Version 2.1 (Language: C or C++)

Optimisation Opt 2 32 Bit
Register option not selected

```
10000 runs 0.00 seconds  
100000 runs 0.01 seconds  
1000000 runs 0.13 seconds  
2000000 runs 0.26 seconds  
4000000 runs 0.51 seconds  
8000000 runs 1.03 seconds  
16000000 runs 2.05 seconds
```

Final values (* implementation-dependent):

```
Int_Glob: O.K. 5 Bool_Glob: O.K. 1  
Ch_1_Glob: O.K. A Ch_2_Glob: O.K. B  
Arr_1_Glob[8]: O.K. 7 Arr_2_Glob8/7: O.K. 16000010  
Ptr_Glob-> Ptr_Comp: * 4854664  
Discr: O.K. 0 Enum_Comp: O.K. 2  
Int_Comp: O.K. 17 Str_Comp: O.K. DHRYSTONE PROGRAM, SOME STRING  
Next_Ptr_Glob-> Ptr_Comp: * 4854664 same as above  
Discr: O.K. 0 Enum_Comp: O.K. 1  
Int_Comp: O.K. 18 Str_Comp: O.K. DHRYSTONE PROGRAM, SOME STRING  
Int_1_Loc: O.K. 5 Int_2_Loc: O.K. 13  
Int_3_Loc: O.K. 7 Enum_Loc: O.K. 1  
Str_1_Loc: O.K. DHRYSTONE PROGRAM, 1'ST STRING  
Str_2_Loc: O.K. DHRYSTONE PROGRAM, 2'ND STRING
```

```
Microseconds for one run through Dhrystone: 0.13  
Dhrystones per Second: 7787511  
VAX MIPS rating = 4432.28
```



STREAM

```
developer@baikal:$ ./stream.exe
```

```
-----  
STREAM version $Revision: 5.10 $  
-----
```

```
This system uses 8 bytes per array element.  
-----
```

```
Array size = 48000000 (elements), Offset = 0 (elements)
```

```
Memory per array = 366.2 MiB (= 0.4 GiB).
```

```
Total memory required = 1098.6 MiB (= 1.1 GiB).
```

```
Each kernel will be executed 10 times.
```

```
The *best* time for each kernel (excluding the first iteration)  
will be used to compute the reported bandwidth.  
-----
```

```
Number of Threads requested = 1
```

```
Number of Threads counted = 1  
-----
```

```
Your clock granularity/precision appears to be 1 microseconds.
```

```
Each test below will take on the order of 242435 microseconds.
```

```
(= 242435 clock ticks)
```

```
Increase the size of the arrays if this shows that  
you are not getting at least 20 clock ticks per test.  
-----
```

```
WARNING -- The above is only a rough guideline.
```

```
For best results, please be sure you know the  
precision of your system timer.  
-----
```

Function	Best Rate MB/s	Avg time	Min time	Max time
Copy:	3307.8	0.232516	0.232175	0.233148
Scale:	3300.8	0.233006	0.232674	0.233518
Add:	2479.9	0.464971	0.464536	0.465537
Triad:	2482.6	0.464478	0.464036	0.465782

```
-----
```

```
Solution Validates: avg error less than 1.000000e-13 on all three arrays  
-----
```

5. Результаты SPEC CPU2006

Результаты производительности микропроцессора БАЙКАЛ-Т1 на бенчмарках из пакета SPEC CPU2006 представлены на диаграммах (см. ниже рисунок 1, 2).

SPEC CPU2006 INT	Ref results
400. perlbench	5.8
401. bzip2	3.7
403. gcc	5.0
429. mcf	4.9
445. gobmk	5.6
456. hmmer	8.8
458. sjeng	5.5
462. libquantum	12.1
464. h264ref	5.7
471. omnetpp	4.1
473. astar	4.2
483. xalancbmk	5.6
SPEC CPU2006 INT (geomean)	5.6




Рисунок 1. Результаты на бенчмарках из пакета SPEC CPU2006 INT (ref workload).

SPECCPU 2006 FP	Ref results
410. bwaves	5.5
416. gamess	1.5
433. milc	0.2
434. zeusmp	6.0
435. gromacs	4.3
436. cactusADM	4.0
437. leslie3d	5.2
444. namd	5.2
447. dealII	8.2
450. soplex	4.4
453. povray	5.8
454. calculix	4.1
459. GemsFDTD	4.4
465. tonto	3.1
470. lbm	4.1
481. wrf	4.9
482. sphinx3	5.6
SPECfp (geomean)	3.8
SPECfp (geomean without milc, gamess)	4.8




Рисунок 2. Результаты на бенчмарках из пакета SPECCPU2006 FP (ref workload).



SPECPU2006 options

```
# Optimization
OPTIMIZE = -Ofast -static -funroll-all-loops -mmsa -ffast-math
-falign-functions=16 -falign-loops=32 -march=p5600 -mtune=p5600
-EL
COPTIMIZE = $(OPTIMIZE)
CXXOPTIMIZE = $(OPTIMIZE) -std=c++03 -fpermissive
FOPTIMIZE = $(OPTIMIZE) -DSPEC_CPU_LINUX -ffixed-form
##### #
32/64 bit Portability Flags - all

# Portability Flags
400.perlbench=default=default=default:
CPORTABILITY = -fno-strict-aliasing -fno-store-merging -fsigned-
char -DSPEC_CPU_LINUX -mno-mips16 -mno-interlink-mips16 -std=gnu89
462.libquantum=default=default=default:
CPORTABILITY = -DSPEC_CPU_LINUX
483.xalancbmk=default=default=default:
CXXPORTABILITY = -DSPEC_CPU_LINUX
481.wrf=default=default=default:
CPORTABILITY = -DSPEC_CPU_CASE_FLAG -DSPEC_CPU_LINUX
436.cactusADM=default=default=default:
CPORTABILITY = -DSPEC_CPU_LINUX
416.gamess=default=default=default:
FPORTABILITY = -DSPEC_CPU_LP64 -fno-strict-aliasing -mno-mips16
-mno-interlink-mips16 -std=legacy
```

6. Производительность Gigabit Ethernet

Результаты получены на бенчмарке `iperf` (ver. 2.0.8b, <https://iperf.fr>), предназначенном для тестирования пропускной способности интернет канала (GbE интерфейс, протокол TCP).

Байкал-Т1 в качестве «клиента»:

```
root@baikal:~# iperf -c 192.168.68.10
connect failed: Connection refused
root@baikal:~# iperf -c 192.168.68.10
```

```
-----
Client connecting to 192.168.68.10, TCP port 5001
TCP window size: 43.8 KByte (default)
-----
```

```
[ 3] local 192.168.68.27 port 51434 connected with 192.168.68.10 port 5001
[ ID] Interval      Transfer    Bandwidth
[ 3] 0.0-10.0 sec  1.10 GBytes  942 Mbits/sec
root@baikal:~# iperf -c 192.168.68.10 -t 100
```

```
-----
Client connecting to 192.168.68.10, TCP port 5001
TCP window size: 43.8 KByte (default)
-----
```

```
[ 3] local 192.168.68.27 port 51436 connected with 192.168.68.10 port 5001
[ ID] Interval      Transfer    Bandwidth
[ 3] 0.0-100.0 sec 11.0 GBytes  941 Mbits/sec
root@baikal:~# iperf -c 192.168.68.10 -t 300
```

```
-----
Client connecting to 192.168.68.10, TCP port 5001
TCP window size: 48.1 KByte (default)
-----
```

```
[ 3] local 192.168.68.27 port 51438 connected with 192.168.68.10 port 5001
[ ID] Interval      Transfer    Bandwidth
[ 3] 0.0-300.0 sec 32.9 GBytes  941 Mbits/sec
```

Байкал-Т1 в качестве «сервера»:

```
root@baikal:~# iperf -s
```

```
-----
Server listening on TCP port 5001
TCP window size: 85.3 KByte (default)
-----
```

```
[ 4] local 192.168.68.27 port 5001 connected with 192.168.68.10 port 51069
[ ID] Interval      Transfer    Bandwidth
[ 4] 0.0-10.0 sec  1.10 GBytes  940 Mbits/sec
[ 5] local 192.168.68.27 port 5001 connected with 192.168.68.10 port 51070
[ 5] 0.0-300.0 sec 32.8 GBytes  940 Mbits/sec
```

7. Производительность 10 Gigabit Ethernet

Используются две платы ВФК 3.1, соединённые непосредственно друг с другом без использования какого-либо промежуточного сетевого оборудования (топология «точка-точка»). Соединение осуществляется при помощи оптического либо медного кабеля с XGbE-трансиверами на концах.

XGbE PHY	Marvell Alaska X 88X2222
Трансивер XGbE для оптического кабеля	Intel FTLX8571D3BCV-IT
Трансивер XGbE для медного кабеля	Juniper Networks 740-030429 Rev 01

Нижеприведённые результаты получены на стандартном тесте `iperf3` (<https://iperf.fr>) версии 3.2+. Тест `iperf3` реализует клиент-серверную модель. Таким образом, одной плате ВФК 3.1 назначается условная роль сервера, а второй — роль клиента. Роль определяется ключами, передаваемыми исполняемому файлу `iperf3` при запуске (см. ниже).

Предварительные настройки

На стороне клиента и сервера:

```
sysctl -w net.ipv4.tcp_timestamps=0
sysctl -w net.ipv4.tcp_sack=0
sysctl -w net.ipv4.tcp_rmem="10000000 10000000 10000000"
sysctl -w net.ipv4.tcp_wmem="10000000 10000000 10000000"
sysctl -w net.ipv4.tcp_mem="10000000 10000000 10000000"
sysctl -w net.core.rmem_max=4194303
sysctl -w net.core.wmem_max=4194303
sysctl -w net.core.rmem_default=4194303
sysctl -w net.core.wmem_default=4194303
sysctl -w net.core.optmem_max=4194303
sysctl -w net.core.netdev_max_backlog=300000
echo 2 > /proc/irq/82/smp_affinity
echo 2 > /proc/irq/83/smp_affinity
echo 2 > /proc/irq/84/smp_affinity
echo 2 > /proc/irq/85/smp_affinity
```

Только на стороне сервера:

```
ifconfig eth0 10.0.4.1 netmask 255.255.255.0 mtu 9000 txqueuelen 8000 up
```




Только на стороне клиента:

```
ifconfig eth0 10.0.4.2 netmask 255.255.255.0 mtu 9000 txqueuelen 8000 up
```

Запуск

На стороне сервера:

```
/mnt/disk1/opt/iperf/iperf3 -A 1 -V -s
```

На стороне клиента:

```
/mnt/disk1/opt/iperf/iperf3x -A 1 -V -l 1M -c 10.0.4.1 -O 1
```

Результаты

В результате серии тестов установлено, что скорость обмена данными составляет ~3,05 Гбит/с при использовании как медного, так и оптического кабеля. Ниже приводятся примеры журналов сервера и клиента.

Сервер

```
iperf 3.2
```

```
Linux baikal-BFK3-0 4.4.135-bfk3 #4 SMP Mon Jul 2 19:43:46 MSK 2018 mips
```

```
-----  
Server listening on 5201  
-----
```

```
Time: Fri, 06 Jul 2018 13:06:18 GMT
```

```
Accepted connection from 10.0.4.2, port 52280
```

```
Cookie: wv64rl7yk32wjyjdjip5kc2g7uuvdmqhduku7
```

```
TCP MSS: 0 (default)
```

```
[ 5] local 10.0.4.1 port 5201 connected to 10.0.4.2 port 52282
```

```
Starting Test: protocol: TCP, 1 streams, 1048576 byte blocks, omitting 1 seconds, 10 second test,  
tos 0
```

[ID]	Interval	Transfer	Bitrate	
[5]	0.00-1.00	sec 346 MBytes	2.89 Gbits/sec	(omitted)
[5]	0.00-1.00	sec 366 MBytes	3.06 Gbits/sec	
[5]	1.00-2.00	sec 367 MBytes	3.07 Gbits/sec	
[5]	2.00-3.00	sec 367 MBytes	3.08 Gbits/sec	
[5]	3.00-4.00	sec 364 MBytes	3.05 Gbits/sec	
[5]	4.00-5.01	sec 365 MBytes	3.06 Gbits/sec	
[5]	5.01-6.00	sec 360 MBytes	3.02 Gbits/sec	
[5]	6.00-7.00	sec 365 MBytes	3.06 Gbits/sec	



```
[ 5] 7.00-8.01 sec 367 MBytes 3.08 Gbits/sec
[ 5] 8.01-9.01 sec 367 MBytes 3.07 Gbits/sec
[ 5] 9.01-10.00 sec 362 MBytes 3.06 Gbits/sec
```

Test Complete. Summary Results:

```
[ ID] Interval          Transfer      Bitrate
[ 5] (sender statistics not available)
[ 5] 0.00-10.00 sec 3.56 GBytes 3.06 Gbits/sec receiver
```

CPU Utilization: local/receiver 37.2% (0.0%/37.1%), remote/sender 51.5% (0.6%/50.9%)

snd_tcp_congestion cubic

rcv_tcp_congestion cubic

Клиент

iperf 3.2

Linux baikal-BFK3-0 4.4.135-bfk3 #4 SMP Mon Jul 2 19:43:46 MSK 2018 mips

Control connection MSS 8960

Time: Fri, 06 Jul 2018 13:06:19 GMT

Connecting to host 10.0.4.1, port 5201

Cookie: wv64rl7yk32wjy djip5kc2g7uuvdmqhduku7

TCP MSS: 8960 (default)

```
[ 5] local 10.0.4.2 port 52282 connected to 10.0.4.1 port 5201
```

Starting Test: protocol: TCP, 1 streams, 1048576 byte blocks, omitting 1 seconds, 10 second test, tos 0

```
[ ID] Interval          Transfer      Bitrate      Retr  Cwnd
[ 5] 0.00-1.00 sec 356 MBytes 2.99 Gbits/sec 0 3.32 MBytes (omitted)
[ 5] 0.00-1.00 sec 365 MBytes 3.06 Gbits/sec 0 3.67 MBytes
[ 5] 1.00-2.00 sec 367 MBytes 3.08 Gbits/sec 0 3.67 MBytes
[ 5] 2.00-3.00 sec 367 MBytes 3.08 Gbits/sec 0 3.67 MBytes
[ 5] 3.00-4.00 sec 363 MBytes 3.05 Gbits/sec 0 3.67 MBytes
[ 5] 4.00-5.00 sec 365 MBytes 3.06 Gbits/sec 0 3.67 MBytes
[ 5] 5.00-6.00 sec 361 MBytes 3.03 Gbits/sec 0 4.45 MBytes
[ 5] 6.00-7.01 sec 369 MBytes 3.07 Gbits/sec 0 4.45 MBytes
[ 5] 7.01-8.00 sec 364 MBytes 3.08 Gbits/sec 0 4.45 MBytes
[ 5] 8.00-9.00 sec 365 MBytes 3.06 Gbits/sec 0 4.45 MBytes
[ 5] 9.00-10.00 sec 368 MBytes 3.08 Gbits/sec 0 4.67 MBytes
```

Test Complete. Summary Results:

```
[ ID] Interval          Transfer      Bitrate      Retr
```



```
[ 5]  0.00-10.00  sec  3.57 GBytes  3.06 Gbits/sec    0          sender
[ 5]  0.00-10.00  sec  3.56 GBytes  3.06 Gbits/sec          receiver
CPU Utilization: local/sender 54.7% (0.2%u/54.5%u), remote/receiver 37.2% (0.0%u/37.1%u)
snd_tcp_congestion cubic
rcv_tcp_congestion cubic
```

8. Производительность PCIe

Подсистема PCIe тестировалась на карте PCIe NVMe SSD Plextor M8PeGN. Карта инициализировалась на скорости GEN3. Для замеров скорости записи и чтения применялась утилита fio v3.7 (лог. запуска см. ниже). Для использования драйвера в конфигурацию ядра Linux нужно добавить опции:

```
CONFIG_BLK_DEV_NVME=y
CONFIG_NVMEM=y
```

Выдержка из dmesg:

```
pci 0000:01:00.0: Link Capability is GEN3, x4
pci 0000:01:00.0: Link Status is GEN1, x4
pci 0000:01:00.0: retrain link to GEN3
pci 0000:01:00.0: Link Status is GEN3, x4
bus: 'pci': driver_probe_device: matched device 0000:01:00.0 with
driver nvme
bus: 'pci': really_probe: probing driver nvme with device
0000:01:00.0
devices_kset: Moving 0000:01:00.0 to end of list
device: 'nvme0': device_add
PM: Adding info for No Bus:nvme0
driver: 'nvme': driver_bound: bound to device '0000:01:00.0'
bus: 'pci': really_probe: bound device 0000:01:00.0 to driver nvme
```

Запуск утилиты fio:

```
# fio --filename=/dev/nvme0n1 --direct=1 --rw=read
--ioengine=vsync --bs=1M --iodepth=1 --numjobs=2 --size=10G
--group_reporting --name pcie
pcie: (g=0): rw=read, bs=(R) 1024KiB-1024KiB, (W) 1024KiB-1024KiB,
(T) 1024KiB-1024KiB, ioengine=vsync, iodepth=1
```

...

Run status group 0 (all jobs):

```
READ: bw=654MiB/s (685MB/s), 654MiB/s-654MiB/s (685MB/s-
```



685MB/s), io=20.0GiB (21.5GB), run=31330-31330msec

Disk stats (read/write):

nvme0n1: ios=162911/0, merge=0/0, ticks=177360/0,
in_queue=177330, util=94.57%

```
# fio --filename=/dev/nvme0n1 --direct=1 --rw=write  
--ioengine=vsync --bs=1M --iodepth=1 --numjobs=2 --size=10G  
--group_reporting --name pcie
```

pcie: (g=0): rw=write, bs=(R) 1024KiB-1024KiB, (W) 1024KiB-
1024KiB, (T) 1024KiB-1024KiB, ioengine=vsync, iodepth=1

...

Run status group 0 (all jobs):

WRITE: bw=454MiB/s (477MB/s), 454MiB/s-454MiB/s (477MB/s-
477MB/s), io=20.0GiB (21.5GB), run=45062-45062msec

Disk stats (read/write):

nvme0n1: ios=0/163068, merge=0/0, ticks=0/395670,
in_queue=396500, util=95.14%

```
# hdparm -tT /dev/nvme0n1p1
```

Timing buffer-cache reads: 1254 MB in 0.50 seconds = 2518422 kB/s

Timing buffered disk reads: 1505 MB in 3.00 seconds = 513684 kB/s

9. Производительность SATA

Для замеров скорости записи и чтения на SATA интерфейсе применялась утилита fio v3.7 (лог. запуска ниже). В качестве оборудования использовался SSD-накопитель Intel 120 GB подключенный SATA-кабелем к БФКЗ.1.

```
# hdparm -tT /dev/sdb
```

Timing buffer-cache reads: 1148 MB in 0.50 seconds = 2305930 kB/s

Timing buffered disk reads: 791 MB in 3.00 seconds = 269785 kB/s

```
# fio --filename=/dev/sdb --direct=1 --rw=read --ioengine=vsync  
--bs=1M --iodepth=1 --numjobs=2 --size=4G --group_reporting --name
```



sata_ssd

```
sata_ssd: (g=0): rw=read, bs=(R) 1024KiB-1024KiB, (W) 1024KiB-1024KiB, (T) 1024KiB-1024KiB, ioengine=vsync, iodepth=1
```

...

Run status group 0 (all jobs):

```
READ: bw=366MiB/s (384MB/s), 366MiB/s-366MiB/s (384MB/s-384MB/s), io=8192MiB (8590MB), run=22377-22377msec
```

Disk stats (read/write):

```
sdb: ios=8108/0, merge=0/0, ticks=43710/0, in_queue=43700, util=99.63%
```

```
# fio --filename=/dev/sdb --direct=1 --rw=write --ioengine=vsync --bs=1M --iodepth=1 --numjobs=2 --size=4G --group_reporting --name sata_ssd
```

```
sata_ssd: (g=0): rw=write, bs=(R) 1024KiB-1024KiB, (W) 1024KiB-1024KiB, (T) 1024KiB-1024KiB, ioengine=vsync, iodepth=1
```

...

Run status group 0 (all jobs):

```
WRITE: bw=139MiB/s (146MB/s), 139MiB/s-139MiB/s (146MB/s-146MB/s), io=8192MiB (8590MB), run=58894-58894msec
```

Disk stats (read/write):

```
sdb: ios=0/8191, merge=0/0, ticks=0/116230, in_queue=116240, util=99.89%
```

10. Производительность USB

Для замеров скорости записи и чтения на USB2.0 интерфейсе применялась утилита fio v3.7 (лог. запуски ниже). В качестве оборудования использовался SSD-накопитель Intel 120 GB вставленный в USB2.0-адаптер ORICO подключенный USB-кабелем к БФК3.1.

```
# fio --filename=/dev/sdb --direct=1 --rw=write --ioengine=vsync --bs=1M --iodepth=1 --numjobs=2 --size=2G --group_reporting --name usb
```

```
usb: (g=0): rw=write, bs=(R) 1024KiB-1024KiB, (W) 1024KiB-1024KiB,
```



```
(T) 1024KiB-1024KiB, ioengine=vsync, iodepth=1
```

```
...
```

```
Run status group 0 (all jobs):
```

```
WRITE: bw=39.1MiB/s (40.0MB/s), 39.1MiB/s-39.1MiB/s (40.0MB/s-40.0MB/s), io=4096MiB (4295MB), run=104853-104853msec
```

```
--
```

```
Disk stats (read/write):
```

```
sdb: ios=0/36790, merge=0/0, ticks=0/1458840, in_queue=1459200, util=99.96%
```

```
# fio --filename=/dev/sdb --direct=1 --rw=read --ioengine=vsync --bs=1M --iodepth=1 --numjobs=2 --size=2G --group_reporting --name usb
```

```
usb: (g=0): rw=read, bs=(R) 1024KiB-1024KiB, (W) 1024KiB-1024KiB, (T) 1024KiB-1024KiB, ioengine=vsync, iodepth=1
```

```
...
```

```
Run status group 0 (all jobs):
```

```
READ: bw=37.9MiB/s (39.7MB/s), 37.9MiB/s-37.9MiB/s (39.7MB/s-39.7MB/s), io=4096MiB (4295MB), run=108165-108165msec
```

```
Disk stats (read/write):
```

```
sdb: ios=36857/0, merge=0/0, ticks=1514290/0, in_queue=1514310, util=99.97%
```

```
hdparm -tT /dev/sdb
```

```
Timing buffer-cache reads: 1314 MB in 0.50 seconds = 2640402 kB/s
```

```
Timing buffered disk reads: 113 MB in 3.01 seconds = 38333 kB/s
```