

Product Overview

MBR1545CT: Schottky Barrier Rectifier, 15 A, 45 V

For complete documentation, see the data sheet.

This Schottky Rectifier uses the Schottky Barrier principle with a platinum barrier metal.

Features

- Center-Tap Configuration
- Guardring for Stress Protection
- Low Forward Voltage
- 150 C Operating Junction Temperature
- Guaranteed Reverse Avalanche
- Epoxy Meets UL94, VO at 1/8"

Mechanical Characteristics:

- Case: Epoxy, Molded
- Weight: 1.9 grams (approximately)
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260 °C Max. for 10 Seconds

For more features, see the data sheet

Part Electrical Specifications

Product	Compliance	Status	Configuration	V_{RRM} Min (V)	V_F Max (V)	I_{RM} Max (μ A)	$I_{O(Rec)}$ Max (A)	I_{FSM} Max (A)	t_r Max (ns)	C_j Max (pF)	Package Type
MBR1545CTG	Pb-free	Active	Common Cathode	45	0.84	100	15	150	-	-	TO-220-3

For more information please contact your local sales support at www.onsemi.com.

Created on: 6/18/2019