

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C
	VOLTAGE	300 V AC	OPERATING HUMIDITY RANGE	85 % MAX
	CURRENT	2 A	APPLICABLE CABLE	(NON-CONDENSING)
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE	100 mA (DC OR 1000 Hz).	20 mΩ MAX.	X	-
INSULATION RESISTANCE	100 V DC.	10 ⁶ MΩ MIN.	X	-
VOLTAGE PROOF	1000 V AC FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	-
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	500 TIMES INSERTIONS AND EXTRACTIONS.	1) CONTACT RESISTANCE: 20 mΩ MAX. 2) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
VIBRATION	FREQUENCY 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, - m/s ² FOR 2 h, IN 3 DIRECTIONS.	1) NO ELECTRICAL DISCONTINUITY OF 1 μs. 2) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
SHOCK	490 m/s ² DIRECTIONS OF PULSE 11 ms FOR 3 TIME IN 3 DIRECTION.		X	-
ENVIRONMENTAL CHARACTERISTICS				
DAMP HEAT (STEADY STATE)	EXPOSED AT 40±2 °C, 90 TO 95 %, 96 h.	1) CONTACT RESISTANCE: 20 mΩ MAX. 2) INSULATION RESISTANCE:	X	-
RAPID CHANGE OF TEMPERATURE	TEMPERATURE -65→15 TO 35→+125→15 TO 35°C TIME 30→ MAX5 → 30 →MAX5min. UNDER 5 CYCLES.	10 ⁶ MΩ MIN. 3) NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	-
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	1) CONTACT RESISTANCE: 20 mΩ MAX. 2) NO HEAVY CORROSION.	X	-
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△				
REMARK		APPROVED	KI. AKIYAMA	05.08.30
		CHECKED	SI. TOMIOKA	05.08.30
		DESIGNED	HT. SUGIMURA	05.08.29
		DRAWN	HM. SAITO	05.08.29
Unless otherwise specified, refer to MIL-STD-1344.				
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test	DRAWING NO.	ELC4-154145-01	
HRS	SPECIFICATION SHEET	PART NO.	PCN10-*P-2. 54DSA (72)	
	HIROSE ELECTRIC CO., LTD.	CODE NO.		△ 1/1