





FILE: _____




Straight Type

Long Dip



P. C. B Layout



Long Lever

Short Lever

Dimension

position	A	B	C	D
06	26.52	5.08	16.76	13.22
08	29.06	7.62	19.30	15.76
10	31.60	10.16	21.84	18.30
14	36.68	15.24	26.92	23.38
16	39.22	17.78	29.46	25.92
20	44.30	22.86	34.54	31.00
26	51.92	30.48	42.16	38.62
30	57.00	35.56	47.24	43.70
34	62.08	40.64	52.32	48.78
40	69.70	48.26	59.94	56.40
50	82.40	60.96	72.64	69.10
60	95.10	73.66	85.34	81.80
64	100.18	78.74	90.42	86.88

Electrical Characteristics:

- Current Rating: 1AMP
- Insulator Resistance: 5000MΩmin. at DC 500V
- Contact Resistance: 20mΩmax. at DC 100mA
- Operating Temperature: -45°C~+105°C

Material:

- Housing: 30% Glass filled PBT UL94V-0
- Contacts: Brass
- Plating: Gold plated: 2u". over 50u" nickel

Features:

- * Fully shrouded provides ultimate reliability.
- * Black or gray insulator available.
- * Choices of Eject lever.

Total Pitch Tolerances in mm								Nominal dimension range in mm										⊥	≡	—	//		
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5

ITEM	NAME OF PART	NO. OF PART	Q"TY	MATERIAL			NOTE	
DWG.		DATE	SIZE	A4	UNITS	mm	SHEET/OF	1 / 1
CHK.		DATE	SCALE					
APP.		DATE		SCM-XX				
			DWGNO.					





Autodesk


Autodesk

FILE:

REV	CONTENT	CHK	DATE
-----	---------	-----	------



Right Angle Type





Long Dip


Electrical Characteristics:
Current Rating: 1AMP
Insulator Resistance: 5000MΩmin. at DC 500V
Contact Resistance: 20mΩmax. at DC 100mA
Operating Temperature: -45°C~+105°C

Material:
Housing: 30% Glass filled PBT UL94V-0
Contacts: Brass
Plating: Gold plated: 2u" over 50u" nickel


Features:
 * Fully shrouded provides ultimate reliability,
 * Black or gray insulator available.
 * Choices of Eject lever.



P. C. B Layout



Long Lever



Short Lever

Dimension				
position	A	B	C	D
06	26.52	5.08	16.76	13.22
08	29.06	7.62	19.30	15.76
10	31.60	10.16	21.84	18.30
14	36.68	15.24	26.92	23.38
16	39.22	17.78	29.46	25.92
20	44.30	22.86	34.54	31.00
26	51.92	30.48	42.16	38.62
30	57.00	35.56	47.24	43.70
34	62.08	40.64	52.32	48.78
40	69.70	48.26	59.94	56.40
50	82.40	60.96	72.64	69.10
60	95.10	73.66	85.34	81.80
64	100.18	78.74	90.42	86.88

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	—	//		
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.3	0.2	0.3	0.5	

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL			NOTE	
DWG.		DATE	SIZE	A4	UNITS	mm	SHEET/OF	1 / 1
CHK.		DATE	SCALE					
APP.		DATE		NAME				
				SCM-XXR				
				DWGNO.				

Autodesk

Autodesk