

6		5		4		3		2		1																																																																											
REV								CONTENT		CHK		DATE																																																																									
<table border="1"> <tr> <td>Product model</td> <td>PCT-213</td> </tr> <tr> <td>Product name</td> <td>Terminal block</td> </tr> <tr> <td>Rated voltage</td> <td>400V</td> </tr> <tr> <td>Rated current</td> <td>32A</td> </tr> <tr> <td rowspan="2">Wiring range</td> <td>Hard wire 0,08mm²-4,0mm²</td> </tr> <tr> <td>Flexible wire 0,08mm²-2,5mm²</td> </tr> <tr> <td>Stripping length</td> <td>9-10mm/0,39in</td> </tr> <tr> <td>Operating temperature</td> <td>-20C° -- 105C°</td> </tr> <tr> <td>Product hole</td> <td>3</td> </tr> <tr> <td>Plastic material</td> <td>Flame Retardant Nylon</td> </tr> <tr> <td>Contact material</td> <td>Copper</td> </tr> <tr> <td>Shrapnel material</td> <td>Stainless steel</td> </tr> </table>												Product model	PCT-213	Product name	Terminal block	Rated voltage	400V	Rated current	32A	Wiring range	Hard wire 0,08mm ² -4,0mm ²	Flexible wire 0,08mm ² -2,5mm ²	Stripping length	9-10mm/0,39in	Operating temperature	-20C° -- 105C°	Product hole	3	Plastic material	Flame Retardant Nylon	Contact material	Copper	Shrapnel material	Stainless steel																																																			
Product model	PCT-213																																																																																				
Product name	Terminal block																																																																																				
Rated voltage	400V																																																																																				
Rated current	32A																																																																																				
Wiring range	Hard wire 0,08mm ² -4,0mm ²																																																																																				
	Flexible wire 0,08mm ² -2,5mm ²																																																																																				
Stripping length	9-10mm/0,39in																																																																																				
Operating temperature	-20C° -- 105C°																																																																																				
Product hole	3																																																																																				
Plastic material	Flame Retardant Nylon																																																																																				
Contact material	Copper																																																																																				
Shrapnel material	Stainless steel																																																																																				
<table border="1"> <thead> <tr> <th>ITEM</th> <th colspan="2">NAME OF PART</th> <th>NO. OF PART</th> <th>Q'TY</th> <th colspan="2">MATERIAL</th> <th colspan="2">NOTE</th> </tr> <tr> <td>DWG.</td> <td>ZX</td> <td>DATE</td> <td></td> <td>SIZE</td> <td>A4</td> <td>UNITS</td> <td>mm</td> <td>SHEET/OF 1 / 1</td> </tr> </thead> <tbody> <tr> <td>CHK.</td> <td></td> <td>DATE</td> <td></td> <td>SCALE</td> <td colspan="2">3:1</td> <td colspan="2"></td> </tr> <tr> <td>APP.</td> <td></td> <td>DATE</td> <td></td> <td rowspan="2"> </td> <td colspan="4">NAME KSE-222-413</td> </tr> <tr> <td colspan="5">KEEN SIDE ELECTRONICS</td> <td colspan="4">DWGNO.</td> </tr> </tbody> </table>												ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL		NOTE		DWG.	ZX	DATE		SIZE	A4	UNITS	mm	SHEET/OF 1 / 1	CHK.		DATE		SCALE	3:1				APP.		DATE			NAME KSE-222-413				KEEN SIDE ELECTRONICS					DWGNO.																																
ITEM	NAME OF PART		NO. OF PART	Q'TY	MATERIAL		NOTE																																																																														
DWG.	ZX	DATE		SIZE	A4	UNITS	mm	SHEET/OF 1 / 1																																																																													
CHK.		DATE		SCALE	3:1																																																																																
APP.		DATE			NAME KSE-222-413																																																																																
KEEN SIDE ELECTRONICS					DWGNO.																																																																																
<table border="1"> <thead> <tr> <th colspan="10">Total Pitch Tolerances in mm</th> <th colspan="10">Nominal dimension range in mm</th> <th>⊥</th> <th>=</th> <th>-</th> <th>//</th> </tr> <tr> <th>over 0</th><th>over 30</th><th>over 53</th><th>over 70</th><th>over 90</th><th>over 115</th><th>over 150</th><th>over 250</th><th>over 350</th><th>over 500</th> <th>over 0</th><th>over 30</th><th>over 53</th><th>over 70</th><th>over 90</th><th>over 115</th><th>over 150</th><th>over 200</th><th>over 250</th><th>over 320</th> <th>over 0</th><th>over 10</th><th>all</th><th>over 0</th><th>over 100</th><th>over 150</th> </tr> </thead> <tbody> <tr> <td>±0.18</td><td>? .25</td><td>±0.30</td><td>±0.35</td><td>±0.40</td><td>? .45</td><td>±0.60</td><td>±0.70</td><td>? .85</td><td>±0.20</td> <td>±0.25</td><td>±0.30</td><td>±0.35</td><td>±0.44</td><td>±0.55</td><td>±0.70</td><td>±0.80</td><td>±0.90</td><td>0.2</td><td>0.3</td> <td>0.3</td><td>0.2</td><td>0.3</td><td>0.5</td> </tr> </tbody> </table>												Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	=	-	//	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150	±0.18	? .25	±0.30	±0.35	±0.40	? .45	±0.60	±0.70	? .85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5
Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	=	-	//																																																														
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 10	all	over 0	over 100	over 150																																																												
±0.18	? .25	±0.30	±0.35	±0.40	? .45	±0.60	±0.70	? .85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5																																																														