







REV	CONTENT	CHK	DATE
V0.0	CONTENT	CXL	14.11.06

NOTES:

1. Rating: 300V 10A;
2. Insulation Withstands Voltage: AC1600V / MIN;
3. Insulation Resistance: 500MΩ or more at DC500V;
4. Using Temperature Range: -40°C / +105°C;
5. Suitable Electric Wire: 22-14 AWG
6. insulation stripping length: 7 mm.
7. RoHS compliance
8. "★" the important dimension.



SECTION A-A



DIM \ P	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L	12.70	17.78	22.86	27.94	33.02	38.10	43.18	48.26	53.34	58.42	63.50	68.58	73.66	78.74	83.82	88.90	93.98	99.06	104.14	109.22	114.30	119.38	124.46
A	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84

Total Pitch Tolerances in mm										Nominal dimension range in mm										⊥	≡	—	//			
over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 250	over 350	over 500	over 0	over 30	over 53	over 70	over 90	over 115	over 150	over 200	over 250	over 320	over 0	over 100	over 150	over 0	over 100	over 150	
±0.18	±0.20	±0.25	±0.3	±0.35	±0.44	±0.60	±0.70	±0.85	±0.20	±0.25	±0.30	±0.35	±0.44	±0.55	±0.70	±0.80	±0.90	0.2	0.3	0.3	0.2	0.3	0.5	0.3	0.3	0.5

			P	STAINLESS	
			P	BRASS	Sn Plated
			1	PA66(UL94V-0)	GREEN
			P	POM-V2	ORANGE
			P	PA66(UL94V-0)	GREEN
ITEM	NAME OF PART		NO. OF PART		Q'TY
DWG.	CXL	DATE	14.10.30		SIZE
CHK.		DATE			A4 UNITS mm
APP.		DATE			SHEET/OF 1 / 1
KEEN SIDE ELECTRONICS					SCALE 1 : 1
					NAME KSE-142V-5.08-XX
					DWGNO.