




P-Channel Enhancement Mode Field Effect Transistor



Top View

SOT-23


Product Summary

- V_{DS} -60 V
- I_D -0.17 A
- $R_{DS(ON)}$ (at $V_{GS}=-10V$) < 8 mohm
- $R_{DS(ON)}$ (at $V_{GS}=-4.5V$) < 10 mohm

General Description

- Trench Power LV MOSFET technology
- Low $R_{DS(ON)}$
- Low Gate Charge

Applications

- Video monitor
- Power management

■ Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Maximum	Unit
Drain-source Voltage	V_{DS}	-60	V
Gate-source Voltage	V_{GS}	± 20	V
Drain Current	I_D	$T_A=25^\circ\text{C}$ @ Steady State	-0.17
		$T_A=70^\circ\text{C}$ @ Steady State	-0.14
Pulsed Drain Current ^A	I_{DM}	-0.68	A
Total Power Dissipation @ $T_A=25^\circ\text{C}$	P_D	225	mW
Thermal Resistance Junction-to-Ambient ^B	$R_{\theta JA}$	556	$^\circ\text{C}/\text{W}$
Junction and Storage Temperature Range	T_J, T_{STG}	-55 ~ +150	$^\circ\text{C}$

■ Ordering Information (Example)

PREFERRED P/N	PACKING CODE	Marking	MINIMUM PACKAGE(pcs)	INNER BOX QUANTITY(pcs)	OUTER CARTON QUANTITY(pcs)	DELIVERY MODE
BSS84	F2	B84	3000	45000	180000	7" reel

■ Electrical Characteristics ($T_J=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Static Parameter						
Drain-Source Breakdown Voltage	BV_{DSS}	$V_{GS}=0V, I_D=-250\mu A$	-60			V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=-60V, V_{GS}=0V, T_C=25^{\circ}\text{C}$			-1	μA
Gate-Body Leakage Current	I_{GSS}	$V_{GS}=\pm 20V, V_{DS}=0V$			± 5	μA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=-250\mu A$	-0.9	-1.4	-2.0	V
Static Drain-Source On-Resistance	$R_{DS(on)}$	$V_{GS}=-10V, I_D=-0.15A$			8	Ω
		$V_{GS}=-4.5V, I_D=-0.15A$			10	
Diode Forward Voltage	V_{SD}	$I_S=-0.17A, V_{GS}=0V$			-1.2	V
Maximum Body-Diode Continuous Current	I_S				-0.17	A
Dynamic Parameters						
Input Capacitance	C_{iss}	$V_{DS}=-30V, V_{GS}=0V, f=1\text{MHz}$		30		μF
Output Capacitance	C_{oss}			10		
Reverse Transfer Capacitance	C_{rss}			5		
Switching Parameters						
Turn-on Delay Time	$t_{D(on)}$	$V_{GS}=-4.5V, V_{DD}=-30V, I_D=-0.15A, R_{GEN}=2.5\Omega$		2.5		ns
Turn-on Rise Time	t_r			1		
Turn-off Delay Time	$t_{D(off)}$			16		
Turn-off Fall Time	t_f			8		

A. Pulse Test: Pulse Width $\leq 300\mu s$, Duty cycle $\leq 2\%$.

B. Device mounted on FR-4 PCB, 1 inch x 0.85 inch x 0.062 inch.

■ Typical Performance Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Drain-Source on Resistance




Figure4. Drain-Source on Resistance




Figure5. Diode Forward Voltage vs. current






Figure6. Gate Threshold vs. Junction Temperature

■ SOT-23 Package information


Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°

■ SOT-23 Suggested Pad Layout

Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.