

SSM1A16BDR

Harmony, Solid state modular relay, 6 A, DIN rail mount, random switching, input 4...32 V DC, output 24...280 V AC



Main

| | |
|---------------------------|------------------------------|
| Range of Product | Harmony Solid State Relays |
| Product or Component Type | Solid state relay up to 10 A |
| Device short name | SSM |
| Number of Channels | 1 |
| Number of phases | 1 phase |
| Output switching mode | Random voltage switching |

Complementary

| | |
|-------------------------------------|---|
| Mounting Support | Symmetrical DIN rail |
| Line Rated Current | 6 A |
| Output voltage | 24...280 V AC |
| [Uc] control circuit voltage | 4...32 V DC |
| Tightening torque | 0.5...0.8 N.m for input 0.5...0.8 N.m for output |
| Connections - terminals | Screw terminals 1 x 0.3...1 x 1.5 mm ² , AWG 22...AWG 16) input Screw terminals 1 x 0.3...1 x 2.5 mm ² , AWG 22...AWG 14) output |
| Maximum capacitance | 10 pF for input/output |
| Insulation resistance | 1000 MOhm at 500 V DC |
| Local signalling | For input status LED (green) |
| Minimum switching voltage | 4 V DC turn-on |
| Maximum switching voltage | 1 V DC turn-off |
| Input current | 8...11 mA |
| Solid state output type | SCR output Random voltage switching |
| Load current | 0.15...6 A |
| Transient overvoltage | 600 V |
| Surge current | 285 A 16.6 ms 300 A 20 ms |
| Maximum voltage drop | <1.3 V on-state |
| Maximum Horse Power Rating | 0.16 hp 104 °F (40 °C) 240 V AC |
| Maximum I ² t for fusing | 410 A ² .S for 10 ms at 50 Hz 375 A ² .s for 8.33 ms at 60 Hz |
| Maximum leakage current | 0.1 mA off-state |
| DV/dt | 500 V/μs off-state at maximum voltage |
| Response time | 0.5 cycle (turn-off) 0.1 ms (turn-on) |
| Power factor | 0.5 (with maximum load) |
| Overvoltage category | III |
| Width | 0.43 in (11 mm) |
| Height | 3.56 in (90.3 mm) |
| Depth | 3.30 in (83.7 mm) |
| Net Weight | 0.11 lb(US) (0.05 kg) |

Environment

| | |
|---------------------------------------|---|
| Flame retardance | V0 conforming to UL 94 |
| Dielectric strength | 4 KV AC for input/output 4 kV AC for input or output to case |
| Pollution degree | 2 |
| Standards | IEC 62314 IEC 60950-1 IEC 61000 |
| Product Certifications | UL CSA |
| Marking | CE |
| IP degree of protection | IP20 |
| Ambient Air Temperature for Operation | -22...176 °F (-30...80 °C) |
| Ambient Air Temperature for Storage | -22...212 °F (-30...100 °C) |

Ordering and shipping details

| | |
|-----------------------|---------------------------------|
| Category | 22375-INTERFACE MODULE(ABA,R,S) |
| Discount Schedule | CP2 |
| GTIN | 3606480579417 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 2.29 oz (65.0 g) |
| Returnability | Yes |
| Country of origin | MX |


Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.79 in (2 cm) |
| Package 1 width | 3.54 in (9 cm) |
| Package 1 Length | 3.54 in (9 cm) |
| Unit Type of Package 2 | S02 |
| Number of Units in Package 2 | 96 |
| Package 2 Weight | 14.88 lb(US) (6.749 kg) |
| Package 2 Height | 5.91 in (15 cm) |
| Package 2 width | 11.81 in (30 cm) |
| Package 2 Length | 15.75 in (40 cm) |


Offer Sustainability

| | |
|----------------------------|---|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End Of Life Information |

Dimensions



Derating Curves



- A : Load Current (Amperes)
- B : Ambient Temperature (°C)
- 1 : Multiple units, no minimum spacing between components
- 2 : Installed single unit, distance to adjacent components more than 11 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SSM1A16BDR](#)