# San Ace Controller

## Features

## **Preventive maintenance of equipment (IoT functionality)**

- $\cdot$  Easy to connect to user's terminal devices. (Wireless LAN / wired LAN)
- Enables users to monitor the status of fans and sensors from remote terminal devices.
- Enables users to control the fan speed remotely via terminal devices.
- $\cdot$  Detects outlier sensor measurements and sends alerts.
- Saves the fan's cumulative operating time and other fan measurement data to the cloud for later use.
- Prevents heat problems with user equipment, contributing to reducing maintenance time and costs.

## Low noise and high energy efficiency (Automatic control)

- Stores temperature, humidity, and air pressure measurements for automatic fan speed control based on the setting conditions.
- Makes fan cooling and ventilation more efficient, reducing noise and improving efficiency.

## **Optimized fan settings (Manual control)**

- · Can connect and control a maximum of four fans, enabling different speed settings for individual fans.
- Optimizes the airflow and static pressure of individual fans in multi-fan systems.




Specifications
----------------


	With wireless I AN	Without wireless I AN	With wireless LAN, cUL certified	
	9CT1-001		9CT1-U001 <sup>(1)</sup>	
			12/24	
V]	3.1 <sup>(2)</sup>			
-	970 W or less		64 W or less (At 12 VDC) 100 W or less (At 24 VDC)	
ge [VDC]	7 to 60		7 to 27.6	
e range [°C]	-20 to +70			
	Manual / automatic			
	PWM signal High-level voltage (V <sub>он</sub> ): 3.3/5 V Frequency: 25 kHz			
	Fan speed, fan current, fan operation hours, sensor detection value, external input			
IS	Max. 4			
erminal	5 A		5 A (At 12 VDC) 4 A (At 24 VDC)	
Total) 20 A		5 A (At 12 VDC) 4 A (At 24 VDC)		
nsors	Max. 4			
	Temperature / humidity, air pressure, acceleration			
Input	Photocoupler-isolated input, ON: 15 to 28.8 VDC, OFF: 0 to 5 VDC			
Output	Photocoupler-isolated open-collector output, load voltage: 28.8 VDC or less, output current: 0.1 A or less			
Wireless	IEEE 802.11b/g/n, frequer 2.4 GHz <sup>(4)</sup>	ncy:	IEEE 802.11b/g/n, frequency: 2.4 GHz <sup>(4)</sup>	
Wired	Ethernet 10BASE-T, 100BASE-TX			
	50 (W) × 135 (D) × 180 (H)			
	450			
Material Casing: Plastic				
	ge [VDC] e range [°C] e range [°C] serminal otal) nsors Input Output Wireless	12/24/48    V]  3.1 <sup>(2)</sup> 970 W or less    ge [VDC]  7 to 60    e range [°C]  -20 to +70    Manual / automatic    PWM signal    High-level voltage (V <sub>OH</sub> ):    Frequency: 25 kHz    Fan speed, fan current, fans    Max. 4    erminal    5 A    otal)    20 A    isors    Max. 4    remperature / humidity, a    Input    Photocoupler-isolated inp    Output  Photocoupler-isolated op    output current: 0.1 A or la    Wireless  IEEE 802.11b/g/n, frequer    2.4 GHz <sup>(4)</sup> 50 (W) × 135 (D) × 180 (H)	9CT1-001  9CT1-002    12/24/48	

(1) Use a UL Class 2 power supply. (2) For use of this product alone, at  $20^{\circ}$ C ambient temperature (3) Use our dedicated sensors (options). (4) Available channels: Ch. 1 to 11






System Configuration




# Graphical User Interface (GUI) Screens

Settings, control, monitoring, and data download can be done through web browsers.

## Sample screens



#### Graphs




#### Alarms

lenn Tipe	Duite	
1 fan Retationel Social	2019/02/05 09 02/06	diffwer
-r -an koranonal kored		- [e] [e, ( a in
13 Fan Robblon, I Sowel		MENT
et eau Richtmark Scool		
FL Teo Current	2019/02/01 09:29:06	STI FASE
2 lan Covart		<b>MILLNE</b>
C) The Current		STI DASE
n lan Conart		
-1NN COVERSIMINAT		
12 Tan Overconvert		ALEXSE
e en la companya de l		

۲

۲

## Dimensions (unit: mm)



# Options

# Sensors

Sensor type	Temperature / Humidity sensor	Air pressure sensor	Accelerometer			
Model no.	9CT1-T	9CT1-P	9CT1-A			
Measurement range	Temperature: -20 to +70°C Humidity: 20 to 85% RH*	Air pressure: 800 to 1100 hPa	Acceleration: 0 to 60 m/s <sup>2</sup> **			
Operating temperature range [°C]	-20 to +70					
Operating humidity range [% RH]	20 to 85*					
Size [mm]	53 (W)×46 (D)×22 (H)					
Mass [g]	35					
Material	Casing: Plastic					



\* Non-condensing \*\* Total acceleration from three axes

## • Dimensions (unit: mm)

