

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0479502011](#)  
**Status:** **Active**  
**Overview:** Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee  
**Description:** 2.4GHz / 5GHz Wi-Fi Stand Alone Antenna, 16.00mm Width, 200.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-47950-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Antennas
Series	<a href="#">47950</a>
Component Type	Flexible Antenna with Cable
Function	Signal
Mates With	<a href="#">734120110 Microcoaxial RF, 50 Ohm</a>
Overview	<a href="#">Internet of Things (IoT) Antennas: Wi-Fi, Bluetooth, Zigbee</a>
Product Name	2.4GHz SMD Stand Alone
Protocol	BLE, BT, Thread, Wi-Fi, Wireless Hart, Zigbee
Type	Wi-Fi Antenna
UPC	884982682054

**Physical**

Cable Length	200.00mm
Length	35.90mm
Mounting Style	Adhesive
Net Weight	0.960/g
Packaging Type	Tray
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	15.90mm


**Electrical**

Band#1 F_End (MHz)	2483.5
Band#1 F_Start (MHz)	2400
Band#2 F_End (MHz)	5900
Band#2 F_Start (MHz)	4800
Electrical Connectivity	Cable
Peak Gain (dBi)	2.6 @ 2.4 GHz, 4.4 @ 5 GHz
Return Loss - S11 (dB)	< -10, < -9
Total Efficiency	>75% @ 5 GHz, >80% @ 2.4 GHz

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-47950-001-001
Sales Drawing	SD-47950-011-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[47950 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**