
www.vishay.com

Vishay Semiconductors

Optocoupler, Phototransistor Output, with Base Connection



DESCRIPTION

The CNY17 is an optically coupled pair consisting of a gallium arsenide infrared emitting diode optically coupled to a silicon NPN phototransitor.

Signal information, including a DC level, can be transmitted by the device while maintaining a high degree of electrical isolation between input and output.

The CNY17 can be used to replace relays and transformers in many digital interface applications, as well as analog applications such as CRT modulation.


FEATURES

- Isolation test voltage: 5000 V_{RMS}
- · Long term stability
- Industry standard dual-in-line package
- Material categorization: For definitions of compliance please see www.vishay.com/doc?99912
 COMPLIANT

AGENCY APPROVALS

Safety application model number covering all products in this datasheet is CNY17. This model number should be used when consulting safety agency documents.

- UL file no. E52744
- cUL tested to CSA 22.2 bulletin 5A
- DIN EN 60747-5-5 (VDE 0884-5)
- BSI IEC 60950, IEC 60065
- FIMKO EN60950
- CQC GB8898-2011



Note

⁽¹⁾ Also available in tubes, do not put T on the end.

SMD-6, option 9

1

CNY17-2X019T⁽¹⁾

_

For technical questions, contact: <u>optocoupleranswers@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



ABSOLUTE MAXIMUM RATINGS (T _{amb} = 25 °C, unless otherwise specified)							
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT			
INPUT							
Reverse voltage		V _R	6	V			
Forward current		I _F	60	mA			
Forward surge current	t _p ≤ 10 µs	I _{FSM}	2.5	А			
LED power dissipation	at 25 °C	P _{diss}	100	mW			
OUTPUT							
Collector emitter breakdown voltage		BV _{CEO}	70	V			
Emitter base breakdown voltage		BV _{EBO}	7	V			
Collector current		Ι _C	50	mA			
	$t_p/T = 0.5, t_p \le 10 \text{ ms}$	Ι _C	100	mA			
Power dissipation		P _{diss}	150	mW			
COUPLER							
Isolation test voltage between emitter and detector	t = 1 min	V _{ISO}	5000	V _{RMS}			
Storage temperature		T _{stg}	-55 to +150	°C			
Operating temperature		T _{amb}	-55 to +110	°C			
Soldering temperature ⁽¹⁾	2 mm from case, \leq 10 s	T _{sld}	260	°C			
Total power dissipation		P _{diss}	250	mW			

Notes

Stresses in excess of the absolute maximum ratings can cause permanent damage to the device. Functional operation of the device is not
implied at these or any other conditions in excess of those given in the operational sections of this document. Exposure to absolute
maximum ratings for extended periods of the time can adversely affect reliability.

⁽¹⁾ Refer to reflow profile for soldering conditions for surface mounted devices (SMD). Refer to wave profile for soldering conditions for through hole devices (DIP).




Fig. 1 - Total Power Dissipation vs. Ambient Temperature

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)									
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT		
INPUT									
Forward voltage	I _F = 60 mA		V _F		1.39	1.65	V		
Breakdown voltage	I _R = 10 μΑ		V _{BR}	6			V		
Reverse current	$V_R = 6 V$		I _R		0.01	10	μA		
Capacitance	V _R = 0 V, f = 1 MHz		Co		25		pF		
Thermal resistance			R _{th}		750		K/W		

Rev. 2.1, 08-Jan-14

2

CNY17



www.vishay.com

Vishay Semiconductors

ELECTRICAL CHARACTERISTICS (T _{amb} = 25 °C, unless otherwise specified)									
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT		
OUTPUT									
Collector emitter capacitance	$V_{CE} = 5 V$, f = 1 MHz		C _{CE}		5.2		pF		
Collector base capacitance	$V_{CE} = 5 V$, f = 1 MHz		C _{CB}		6.5		pF		
Emitter base capacitance	V _{CE} = 5 V, f = 1 MHz		C _{EB}		7.5		pF		
Thermal resistance			R _{th}		500		K/W		
COUPLER									
Collector emitter, saturation voltage	$V_{F} = 10 \text{ mA}, I_{C} = 2.5 \text{ mA}$		V _{CEsat}		0.25	0.4	V		
Coupling capacitance			C _C		0.6		pF		
Collector emitter, leakage current	V _{CE} = 10 V	CNY17-1	I _{CEO}		2	50	nA		
		CNY17-2	I _{CEO}		2	50	nA		
		CNY17-3	I _{CEO}		5	100	nA		
		CNY17-4	I _{CEO}		5	100	nA		

Note

• Minimum and maximum values were tested requierements. Typical values are characteristics of the device and are the result of engineering evaluations. Typical values are for information only and are not part of the testing requirements.

CURRENT TRANSFER RATIO ($T_{amb} = 25 \text{ °C}$, unless otherwise specified)							
PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
IC/IF	$V_{CE} = 5 \text{ V}, I_F = 10 \text{ mA}$	CNY17-1	CTR	40		80	%
		CNY17-2	CTR	63		125	%
		CNY17-3	CTR	100		200	%
		CNY17-4	CTR	160		320	%
	V _{CE} = 5 V, I _F = 1 mA	CNY17-1	CTR	13	30		%
		CNY17-2	CTR	22	45		%
		CNY17-3	CTR	34	70		%
		CNY17-4	CTR	56	90		%

PARAMETER	TEST CONDITION	PART	SYMBOL	MIN.	TYP.	MAX.	UNIT
LINEAR OPERATION	(without saturation)	•					
Turn-on time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω		t _{on}		3		μs
Rise time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω		t _r		2		μs
Turn-off time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω		t _{off}		2.3		μs
Fall time	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω		t _f		2		μs
Cut-off frequency	I_F = 10 mA, V_{CC} = 5 V, R_L = 75 Ω		f _{CO}		110		kHz
SWITCHING OPERA	FION (with saturation)	•					
Turn-on time	I _F = 20 mA	CNY17-1	t _{on}		3		μs
	I _F = 10 mA	CNY17-2	t _{on}		4.2		μs
		CNY17-3	t _{on}		4.2		μs
	I _F = 5 mA	CNY17-4	t _{on}		6		μs
	I _F = 20 mA	CNY17-1	t _r		2		μs
Rise time	I _F = 10 mA	CNY17-2	t _r		3		μs
		CNY17-3	t _r		3		μs
	I _F = 5 mA	CNY17-4	t _r		4.6		μs
	I _F = 20 mA	CNY17-1	t _{off}		18		μs
Turn off times	10	CNY17-2	t _{off}		23		μs
Turn-off time	I _F = 10 mA	CNY17-3	t _{off}		23		μs
	I _F = 5 mA	CNY17-4	t _{off}		25		μs
Fall time	I _F = 20 mA	CNY17-1	t _f		11		μs
	I _F = 10 mA	CNY17-2	t _f		14		μs
		CNY17-3	t _f		14		μs
	I _F = 5 mA	CNY17-4	t _f		15		μs


Rev. 2.1, 08-Jan-14

3

Document Number: 83606

For technical questions, contact: <u>optocoupleranswers@vishay.com</u>

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishay.com/doc?91000



www.vishay.com

95 10804-3

Fig. 2 - Test Circuit, Non-Saturated Operation





Fig. 3 - Test Circuit, Saturated Operation



SAFETY AND INSULATION RATINGS VALUE UNIT PARAMETER SYMBOL MAXIMUM SAFETY RATINGS Output safety power 700 mW P_{SO} Input safety current 400 mΑ I_{SI} °C 175 Safety temperature T_{SI} Comparative tracking index CTI 175 **INSULATION RATED PARAMETERS** 5000 V_{RMS} Maximum withstanding isolation voltage VISO Maximum transient isolation voltage 8000 VIOTM Vpeak Maximum repetitive peak isolation voltage VIORM 890 V_{peak} $T_{amb} = 25 \text{ °C}, V_{DC} = 500 \text{ V}$ Insulation resistance ≥ 10¹² R_{IO} Ω $T_{amb} = 100 \ ^{\circ}C, V_{DC} = 500 \ V$ ≥ 10¹¹ Isolation resistance RIO Ω Climatic classification (according to IEC 68 part 1) 55/115/21 Environment (pollution degree in accordance to DIN VDE 0109) 2 Standard DIP-4 ≥7 mm Creepage distance SMD ≥7 mm Standard DIP-4 ≥8 mm Clearance distance SMD ≥8 mm DTI Insulation thickness ≥ 0.4 mm

Note

• As per DIN EN 60747-5-5, § 7.4.3.8.2, this optocoupler is suitable for "safe electrical insulation" only within the safety ratings. Compliance with the safety ratings shall be ensured by means of protective circuits.

4



TYPICAL CHARACTERISTICS ($T_{amb} = 25$ °C, unless otherwise specified)




Fig. 5 - Forward Voltage vs. Forward Current




Fig. 6 - Collector Current vs. Collector Emitter Voltage (NS)




Fig. 7 - Collector Current vs. Collector Emitter Voltage (sat)




Fig. 8 - Leakage Current vs. Ambient Temperature




Fig. 9 - Normalized CTR (NS) vs. Ambient Temperature




Fig. 10 - Normalized CTR (sat) vs. Ambient Temperature

Rev. 2.1, 08-Jan-14

5

For technical questions, contact: <u>optocoupleranswers@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>






Fig. 11 - Normalized CTR (NS) vs. Forward Current




Fig. 12 - Normalized CTR (sat) vs. Forward Current




Fig. 13 - CTR Frequency vs. Phase Angle




Fig. 14 - CTR -3 dB Frequency vs. Collector Current





Fig. 15 - Switching Time vs. Load Resistance


6

For technical questions, contact: <u>optocoupleranswers@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



PACKAGE DIMENSIONS in millimeters








Option 6


Option 7


Option 9












20802-34

PACKAGE MARKING




Notes

- VDE logo is only marked on option 1 parts. Option information is not marked on the part.
- Tape and reel suffix (T) is not part of the package marking.



TUBE AND TAPE INFORMATION



Downloaded from Arrow.com.



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.