

Han Q 5/0 HighTemp-F-c



Image is for illustration purposes only. Please refer to product description.

Part number	09 12 805 3104
Specification	Han Q 5/0 HighTemp-F-c
HARTING eCatalogue	https://b2b.harting.com/09128053104

Identification

Category	Inserts
Series	Han [®] Q High Temp
Identification	5/0

Version

Termination method	Crimp termination
Gender	Female
Size	3 A
Number of contacts	5
PE contact	Yes
Details	Please order crimp contacts separately. Coding pins on request

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	16 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +200 °C With Han [®] High Temp components



Pushing Performance

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 60664-1
	IEC 61984

Commercial data

Packaging size	1
Net weight	15 g
Country of origin	Romania
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors