

3A, 50V - 600V Ultra Fast Surface Mount Rectifier

FEATURES

- Glass passivated chip junction
- Ideal for automated placement
- Ultra fast recovery time for high efficiency
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- High frequency rectification
- Freewheeling application
- Switching mode converters and inverters in computer, and telecommunication

MECHANICAL DATA

- Case: DO-214AB (SMC)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.210g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	3	A
V_{RRM}	50 - 600	V
I_{FSM}	75	A
T_{JMAX}	175	°C
Package	DO-214AB (SMC)	
Configuration	Single die	



DO-214AB (SMC)



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)								
PARAMETER	SYMBOL	MUR 305S	MUR 310S	MUR 315S	MUR 320S	MUR 340S	MUR 360S	UNIT
Marking code on the device		MUR 305S	MUR 310S	MUR 315S	MUR 320S	MUR 340S	MUR 360S	
Repetitive peak reverse voltage	V_{RRM}	50	100	150	200	400	600	V
Reverse voltage, total rms value	$V_{R(RMS)}$	35	70	105	140	280	420	V
Forward current	I_F	3						A
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I_{FSM}	75						A
Junction temperature	T_J	- 55 to +175						°C
Storage temperature	T_{STG}	- 55 to +175						°C

THERMAL PERFORMANCE			
PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	11	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage ⁽¹⁾	MUR305S MUR310S MUR315S MUR320S	$I_F = 3\text{A}, T_J = 25^\circ\text{C}$	V_F	-	0.875	V
	MUR340S MUR360S			-	1.250	V
	MUR305S MUR310S MUR315S MUR320S	$I_F = 3\text{A}, T_J = 150^\circ\text{C}$	V_F	-	0.710	V
	MUR340S MUR360S			-	1.050	V
Reverse current @ rated V_R ⁽²⁾	MUR305S MUR310S MUR315S MUR320S	$T_J = 25^\circ\text{C}$	I_R	-	5	μA
	MUR340S MUR360S			-	10	μA
	MUR305S MUR310S MUR315S MUR320S	$T_J = 150^\circ\text{C}$	I_R	-	150	μA
	MUR340S MUR360S			-	250	μA
Reverse recovery time	MUR305S MUR310S MUR315S MUR320S	$I_F = 0.5\text{A}, I_R = 1.0\text{A}$ $I_{rr} = 0.25\text{A}$	t_{rr}	-	25	ns
	MUR340S MUR360S			-	50	ns

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION		
ORDERING CODE⁽¹⁾	PACKAGE	PACKING
MUR3xS	DO-214AB (SMC)	3,000 / Tape & Reel

Notes:

1. "x" defines voltage from 50V(MUR305S) to 600V(MUR360S)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics




Fig.5 Typical Reverse Characteristics






Fig.6 Typical Forward Characteristics



CHARACTERISTICS CURVES



(T_A = 25°C unless otherwise noted)

Fig.7 Maximum Non-Repetitive Forward Surge Current



PACKAGE OUTLINE DIMENSIONS

DO-214AB (SMC)



MARKING DIAGRAM

P/N = MARKING CODE
G = GREEN COMPOUND
YW = DATE CODE
F = FACTORY CODE

SUGGESTED PAD LAYOUT

NOTES: UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS ARE IN MILLIMETERS.
2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.
3. PACKAGE OUTLINE REFERENCE: JEDEC DO-214, VARIATION AB, ISSUE D.
4. MOLDED PLASTIC BODY DIMENSIONS DO NOT INCLUDE MOLD FLASH.
5. MOLDED PLASTIC BODY LATERAL DIMENSIONS TO BE DETERMINED AT DATUM PLANE H.
6. DWG NO. REF: HQ2SD07-DO214SMC-036 REV A.

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[MUR305S R7](#) [MUR310S R7](#) [MUR315S R7](#) [MUR320S R7](#) [MUR340S R7](#) [MUR360S R7](#) [MUR310S R7G](#)
[MUR320S R6](#) [MUR310S R6G](#) [MUR320S R7G](#) [MUR315S R6](#) [MUR310S R6](#) [MUR315S R6G](#) [MUR305S R6G](#)
[MUR360S R6](#) [MUR305S R6](#) [MUR305S R7G](#) [MUR340S R6G](#) [MUR360S R7G](#) [MUR360S R6G](#) [MUR340S R6](#)
[MUR320S R6G](#) [MUR315S R7G](#) [MUR340S R7G](#) [MUR320S V6G](#) [MUR320S V7G](#) [MUR340S V6G](#) [MUR340S V7G](#)
[MUR360S V7G](#) [MUR315S V7G](#) [MUR305S V6G](#) [MUR305S V7G](#) [MUR310S V6G](#) [MUR310S V7G](#) [MUR315S V6G](#)
[MUR360S V6G](#) [MUR305S](#) [MUR310S](#) [MUR315S](#) [MUR320S](#) [MUR340S](#) [MUR360S](#)