



[CONNECTORS](#)

[CONNECTOR HOUSINGS](#)



✓ Active

TE CONNECTIVITY (TE)

MQS STIFT-GEH 2P

[AMP](#) | [MQS](#)

1-968699-1

TE Internal Number: 1-968699-1

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Connector System Wire-to-Wire

Connector Style Housing for male terminals

Mating Tab Width .63 mm [.025 in]

Centerline (Pitch) (in) .1

Number of Positions 2

[↓ PRODUCT DRAWING](#)
English

[↓ 3D PDF](#)

DOCUMENTATION

Product Drawings

MQS,PIN HOUSING, 2 POS. MQS,Stiftgehaeuse, 2-Polig

PDF

English

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

PRODUCT SPECIFICATION, MICRO QUADLOK SYSTEM PIN AND SOCKET HOUSING WITH INTEGRATED RETAINER

TIF

German

PRODUCT SPECIFICATION, MICRO QUADLOK SYSTEM PIN AND SOCKET HOUSING WITH INTEGRATED RETAINER

PDF

German

Application Specification

MICRO QUADLOK SYSTEM PIN- AND SOCKET HOUSING WITH INTEGRATED RETAINER

PDF

English

MICRO QUADLOK SYSTEM PIN- AND SOCKET HOUSING WITH INTEGRATED RETAINER

TIF

English

Product Environmental Compliance

TE Material Declaration

MD_1-968699-1_05052015455_dmtec

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Wire

Connector Style Housing for male terminals

Sealed No

Hybrid Connector No

Primary Locking Feature On the terminal

Strain Relief No

Configuration Features

Number of Positions 2

Number of Rows 1

Body Features

Color Black

Cable Exit Angle 180°

Body Material PBT GF

Contact Features

Mating Tab Width .63 mm [.025 in]

Mechanical Attachment

Mounting Feature No

Terminal Position Assurance Yes

Polarized No

Housing Features

Centerline (Pitch) (in) .1

Pitch (mm) 2.54

Dimensions

Width 26.6 mm [1.047 in]

Height 8.2 mm [.323 in]

Length 10.2 mm [.402 in]

Operation/Application

Circuit Application Signal

Industry Standards

UL Flammability Rating UL 94-HB

Packaging Features

Packaging Method Box

Other

Connector Position Assurance Capable No

Serviceable No

Statement of Compliance

Statement of Compliance

PDF