

# GRM155R60G475ME87#

“#” indicates a package specification code.



< List of part numbers with package codes >

GRM155R60G475ME87D      GRM155R60G475ME87J

## Appearance & Shape



## References

Packaging	Specifications	Standard Packing Quantity
D	180mm Paper Tape	10000
J	330mm Paper Tape	40000

Mass (typ.)	
1 piece	2.5mg
φ180mm Reel	135g

### Attention

- This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM155R60G475ME87#

“#” indicates a package specification code.



## Specifications

Length	1.0±0.15mm
Width	0.5±0.15mm
Thickness	0.5±0.15mm
Capacitance	4.7µF ±20%
Distance between external terminals g	0.3mm min.
External terminal size e	0.15 to 0.35mm
Operating Temperature Range	-55°C to 85°C
Rated Voltage	4Vdc
Size code in inch(mm)	0402 (1005M)
Capacitance change rate	±15.0%
Temperature characteristics (complied standard)	X5R(EIA)
Temperature range of temperature characteristics	-55°C to 85°C

### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.


# GRM155R60G475ME87#

“#” indicates a package specification code.




## Characteristic Data


The charts below may show another part number which shares its characteristics.




GRM155R60G475ME87 |Z| DCOV, 25degC



GRM155R60G475ME87 R DCOV, 25degC



GRM155R60G475ME87 C-DC bias capchange, 25.0degC, A




GRM155R60G475ME87 C-AC Voltage capchange, DCOV, 25

**Attention**


- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# GRM155R60G475ME87#

“#” indicates a package specification code.



GRM155R60G475ME87 C-Temp. capchange, DC0.0V, AC0.2



GRM155R60G475ME87 Temp. rise — 100kHz — 500

**Attention**

- 1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2.This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.