

# HUBER+SUHNER® DATA SHEET

## Within Series Adaptor: 31\_PC35-50-0-2/199\_N



### Description

Adaptor jack/jack  
 PC 3.5 jack (female) / PC 3.5 jack (female)  
 For Test & Measurement applications  
 Precision adaptor  
 Interface standard  
 Series PC 3.5 - IEC 60169-23



### Technical Data

#### Electrical Data

Impedance	50 Ω		
Interface frequency max.	33 GHz		
Frequency range	DC to 1.5 GHz	1.5 to 6 GHz	6 to 18 GHz
Return loss	≥ 35 dB	≥ 30 dB	≥ 20 dB
Electrical Length	25.5 mm +/- 0.2		

#### Mechanical Data

Number of matings	500
Weight	0.0055 kg

#### Environmental Data

Operating Temperature	-60 °C to 100 °C
2002/95/EC (RoHS)	compliant

#### Material Data

##### Piece Parts

##### Interface - PC 3.5 jack (female)

	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PS	

##### Interface - PC 3.5 jack (female)

Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Stainless Steel	
Body	Stainless Steel	
Insulator	Air Dielectric - Bead - PS	

#### Related Documents

Outline drawing	DOU-00013873
-----------------	--------------

#### Ordering Information

Single package	31_PC35-50-0-2/199_NE
----------------	-----------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

**WAIVER!**  
 It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



**HUBER+SUHNER AG**  
**RF Technology**  
**9100 Herisau, Switzerland**  
 Phone +41 (0)71 353 41 11  
 Fax +41 (0)71 353 45 90  
[www.hubersuhner.com](http://www.hubersuhner.com)

**HUBER+SUHNER – Excellence in Connectivity Solutions**