

# FS 0,635/ 20-MV-R- 8,0 - SMD male connectors




1332124

<https://www.phoenixcontact.com/us/products/1332124>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

SMD male connector, nominal current: 0.5 A, Test voltage: 500 V AC, number of positions: 20, pitch: 0.635 mm, color: black, contact surface: Gold, type of contact: Pin, mounting: SMD soldering



## Your advantages

- Design-in support during device development through M-CAD/E-CAD data and a free sample service
- Cost and space savings with the comprehensive portfolio available in various stack heights
- Easy mating with integrated keyways and tolerance compensation for error-free production
- High-speed data transmission up to 20 Gbps for various possible applications
- Time savings during the development process with customer-specific simulations for data integrity
- Gold-plated contacts ensure transfer quality remains stable over the long term

## Commercial Data

Item number	1332124
Packing unit	600 pc
Minimum order quantity	600 pc
Product Key	AAWGCB
GTIN	4063151629649
Weight per Piece (including packing)	1.213 g
Weight per Piece (excluding packing)	1.213 g
Country of origin	CN

1332124

<https://www.phoenixcontact.com/us/products/1332124>

## Technical Data

### Product properties

Product type	SMD male connector
Product family	FS 0,635/...-MV-R- 8,0
Number of positions	20
Pitch	0.635 mm
Number of rows	2
Pin layout	Linear pad geometry

### Electrical properties

Nominal current $I_N$	0.5 A IEC 60512-5-2:2002-02 (40-pos. / 60-pos.)
Degree of pollution	3
Contact resistance	70 mΩ
Test voltage	500 V AC IEC 60512-4-1:2003
Rated voltage (I/1)	125 V
Rated surge voltage (I/1)	0.8 kV

### Mounting

Mounting type	SMD soldering
Pin layout	Linear pad geometry

### Processing notes

Process	Reflow soldering
Moisture Sensitive Level	MSL 1
Classification temperature $T_c$	260 °C
Solder cycles in the reflow	3

### Material specifications

#### Material data - contact

Note	WEEE/RoHS-compliant, free of whiskers according to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Surface characteristics	Selective coating
Metal surface contact area (top layer)	Gold (Au)
Metal surface contact area (middle layer)	Nickel (Ni)
Metal surface soldering area (top layer)	Tin (Sn)
Metal surface soldering area (middle layer)	Nickel (Ni)

#### Material data - housing

Color (Housing)	black (9005)
Insulating material	LCP

### Notes

# FS 0,635/ 20-MV-R- 8,0 - SMD male connectors



1332124

<https://www.phoenixcontact.com/us/products/1332124>

Notes on operation	The permissible voltage during operation depends on the application, taking into consideration the air clearances and creepage distances within the scope of insulation requirements in accordance with IEC 60664-1.
--------------------	--

## Dimensions

Dimensional drawing	
Pitch	0.635 mm
Width [w]	13.22 mm
Height [h]	8.6 mm
Length [l]	5.2 mm
Installed height	8 mm

## Application

Contact cover	0.6 mm
Center offset	± 0.5 mm in longitudinal and transverse direction
Stack height	9 mm Tolerance: +0.6 mm (in combination with Range of articles:FS 0,635-FV-R- 4,0)
	15 mm Tolerance: +0.6 mm (in combination with Range of articles:FS 0,635-FV-R-10,0)
Wipe length	0.6 mm
Angular tolerance	± 10 ° in longitudinal and transverse direction (when plugging in)
	± 2 ° in longitudinal and transverse direction (when plugged in)

## PCB design

Pad geometry	0.35 x 1.8 mm
--------------	---------------

## Electrical tests

### Thermal test | Test group C

Specification	IEC 60512-5-2:2002-02
Tested number of positions	60

### Insulation resistance

Specification	IEC 60512-3-1:2002-02
Insulation resistance, neighboring positions	≥ 5 GΩ

### Air clearances and creepage distances |

Specification	IEC 60664-1:2007-04
Minimum value for clearance and creepage distance	0.19 mm

## Environmental and real-life conditions

### Vibration test

# FS 0,635/ 20-MV-R- 8,0 - SMD male connectors



1332124

<https://www.phoenixcontact.com/us/products/1332124>

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 55 - 10 Hz
Sweep speed	1 octave/min
Amplitude	1.52 mm
Sweep speed	181 m/s <sup>2</sup>
Test duration per axis	2 h

## Durability test

Specification	IEC 60512-9-1:2010-03 (following)
Contact resistance R <sub>1</sub>	70 mΩ
Contact resistance R <sub>2</sub>	70 mΩ
Insertion/withdrawal cycles	50
Insulation resistance, neighboring positions	≥ 5 GΩ

## Climatic test

Specification	IEC 60068-2-60:2015-06
Corrosive stress	Method 4, 10 days
Thermal stress	125 °C/168 h
Power-frequency withstand voltage	500 V

## Ambient conditions


Ambient temperature (operation)	-55 °C ... 125 °C
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Relative humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 100 °C

1332124

<https://www.phoenixcontact.com/us/products/1332124>

## Drawings

Diagram



Type: FS 0,635/...-MV-R- 8,0 with FS 0,635/...-FV-R-10,0

# FS 0,635/ 20-MV-R- 8,0 - SMD male connectors




1332124

<https://www.phoenixcontact.com/us/products/1332124>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1332124>

 <b>cULus Recognized</b> Approval ID: E118976-20230512	Nominal Voltage $U_N$	Nominal Current $I_N$	Cross Section AWG	Cross Section $\text{mm}^2$
	29.9 V	0.5 A	-	-

# FS 0,635/ 20-MV-R- 8,0 - SMD male connectors



1332124

<https://www.phoenixcontact.com/us/products/1332124>

## Classifications

### ECLASS

ECLASS-11.0	27460201
ECLASS-12.0	27460201
ECLASS-13.0	27460201

### ETIM

ETIM 8.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# FS 0,635/ 20-MV-R- 8,0 - SMD male connectors



1332124

<https://www.phoenixcontact.com/us/products/1332124>

## Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values



## FS 0,635/ 20-MV-R- 8,0 - SMD male connectors

1332124

<https://www.phoenixcontact.com/us/products/1332124>



### Mandatory Accessories

#### FS 0,635/ 20-FV-R- 4,0 - SMD female connectors

1331962

<https://www.phoenixcontact.com/us/products/1331962>

SMD female connector, nominal current: 0.5 A, Test voltage: 500 V AC, number of positions: 20, pitch: 0.635 mm, color: black, contact surface: Gold, type of contact: Socket, mounting: SMD soldering




---

#### FS 0,635/ 20-FV-R-10,0 - SMD female connectors

1334089

<https://www.phoenixcontact.com/us/products/1334089>

SMD female connector, nominal current: 0.5 A, Test voltage: 500 V AC, number of positions: 20, pitch: 0.635 mm, color: black, contact surface: Gold, type of contact: Socket, mounting: SMD soldering



---

### Accessories

# FS 0,635/ 20-MV-R- 8,0 - SMD male connectors

1332124

<https://www.phoenixcontact.com/us/products/1332124>




## FS 0,635/ 20-FV-R-10,0 - SMD female connectors

1334089

<https://www.phoenixcontact.com/us/products/1334089>

SMD female connector, nominal current: 0.5 A, Test voltage: 500 V AC, number of positions: 20, pitch: 0.635 mm, color: black, contact surface: Gold, type of contact: Socket, mounting: SMD soldering



---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)