

# **SPECIFICATION**

Part No. : **CGGP.18.2.A.02** 

Description : GPS/GLONASS/GALILEO Dual-Band

Ceramic Patch Embedded Antenna

18x18x2mm

Features : Wide-band Operation 1575-1610MHz

3.23dBi Peak Gain for GPS/GALILEO Band

3.53dBi Peak Gain for GLONASS Band

Low profile – 2mm Height

Through-hole Mounting Pin type

Automotive TS16949 Production and

Quality Approved

**RoHS Compliant** 







### 1. Introduction

The CGGP.18.2.A.02 is a 18mm ceramic GPS/GLONASS/GALILEO embedded passive patch antenna, with a 2mm low profile. It is designed for vehicle telematic applications as well as other M2M/IoT devices. Typical applicable industries are transportation, defense, marine, agriculture, and navigation.

The antenna has been tuned and tested on a 70 x 70 mm ground plane, working at GPS 1575.42MHz and GLONASS 1602MHz, with 3.23dBi gain and 3.53dBi gain, respectively. The low profile design makes this antenna perfect for applications where space is limited. It can be easily through-hole mounted on PCB via pin. Double sided adhesive on the bottom of the patch helps to keep it in place while undergoing mounting. The CGGP.18.2.A.02 is manufactured and tested in a TS16949 first tier automotive approved facility.

Like all antennas, at least some detuning will occur when placed in a different device environment or on a different ground-plane.

For large volume GPS/GLONASS/GALILEO projects where performance is paramount, tuning for customer specific device environment and ground-plane size is needed, so custom tuned patch antennas should always be used. Taoglas can also provide different pin length for these antennas, all subject to potential NRE and MOQ. For more details please contact your regional Taoglas sales office.



# 2. Specification

| ELECTRICAL                |                            |         |  |  |  |
|---------------------------|----------------------------|---------|--|--|--|
| Application Bands         | GPS/GALILEO                | GLONASS |  |  |  |
| Operation Frequency (MHz) | 1575.42 ±1.023             | 1602±5  |  |  |  |
| Return Loss (dB)          | -10 max.                   |         |  |  |  |
| Gain at Zenith (dBi)      | 3.23                       | 3.53    |  |  |  |
| Efficiency (%)            | 54.88                      | 59.52   |  |  |  |
| Impedance                 | 50 ohms                    |         |  |  |  |
| MECHANICAL                |                            |         |  |  |  |
| Ceramic Dimension (mm)    | 18 x 18 x 2                |         |  |  |  |
| Pin Diameter (mm)         | 0.9                        |         |  |  |  |
| Pin Length (mm)           | 2.25                       |         |  |  |  |
| Weight (g)                | 2.5                        |         |  |  |  |
| ENVIRONMENTAL             |                            |         |  |  |  |
| Operation Temperature     | -40°C to 85°C              |         |  |  |  |
| Humidity                  | Non-condensing 65°C 95% RH |         |  |  |  |


<sup>\*</sup> Antenna properties were measured with the antenna mounted on 70\*70mm Ground Plane

Taoglas Part # CGGPD.18.D




### 3. Antenna Characteristics

#### 3.1. Return Loss




## 3.2. Efficiency






## 3.3. Average Gain



### 3.4. Peak Gain






## 4. Antenna Radiation Pattern

### 4.1. Measurement Setup


The CGGP.18.2.A.02 antenna is tested in free-space on a 70mm\*70mm ground plane in a CTIA certified ETS-Lindgren Anechoic Chamber. The test setup is shown below.






### 4.2. 2D Radiation Pattern

#### XY Plane




#### XZ Plane






### YZ Plane






### 4.3. 3D Radiation Pattern

#### 1575.42MHz




#### 1602MHz





# 5. Mechanical Drawing (Unit: mm)




NOTES:

1.Double sided adhesive area

|  |   | Name                  | P/N            | Material   | Finish      | QTY |
|--|---|-----------------------|----------------|------------|-------------|-----|
|  | 1 | Patch 18x18x2         | 001513C110007A | Ceramic    | Clear       | 1   |
|  | 2 | Double sided Adhesive | 001013C050007A | NITTO 5015 | White Liner | 1   |




### **5.1. Adhesive Thickness**





Red Line shows the adhesive without Liner - thickness 0.08~0.1mm




# 6. Evaluation Board (CGGPD.18.D) (Unit: mm)








## **Bottom View**



|   | Name                      | Material | Finish | QTY |
|---|---------------------------|----------|--------|-----|
| 1 | Patch(18x18x4mm)          | Ceramic  | Clear  | 1   |
| 2 | Ground-Plane(70x70x0.3mm) | Brass    | Silver | 1   |
| 3 | SMA(F) ST                 | Brass    | Gold   | 1   |



# 7. PCB Footprint Recommendation





# 8. Packaging


### 8.1. Inner Tray & Inner Carton


CGGP.18.2.A.02

**Packaging Specifications** 

25 pcs per tray Tray Dimensions - 250\*150\*11mm

8 Trays per inner box 200 pcs CGGP.18.2.A.02 Dimensions - 260\*160\*100mm









#### 8.2. Carton

4 inner boxes per outer carton 800 Pieces CGGP.18.2.A.02 per carton Carton Dimensions - 330\*280\*270mm



Pallet Dimensions 1100\*1100\*1500mm 60 Cartons per Pallet 12 Cartons per layer 5 Layers



Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.