

# LED/Buzzer Combination with acknowledgement function



- LED permanent light with additional continuous tone
- Silence the audible signal by lightly pressing the frontal area
- Life duration up to 50,000 hrs
- Potential-free output for transmission of the acknowledgement signal to the control unit
- Positive and negative logic possible

## **i** TECHNICAL SPECIFICATIONS:

Dimensions (Diameter x Height):	49.5 mm x 75 mm
Housing:	PC/ABS-Blend
Dome:	PC, transparent
Connection:	Screwable connection max. 0.5 mm <sup>2</sup>
Starting current:	< 0.5 A
Current consumption:	40 to 80 mA at 24 V
Signal input:	24 V =
Acknowledgement output:	Semiconductor-Relay $U_{max} = 30 V$ $I_{max} = 100 mA$ $R_{ON max} = 25 Ohm$
Tone type:	Continuous
Tone frequency:	3 kHz
Duty cycle:	100 %
Life duration:	up to 50,000 hrs
Fixing:	Installation mounting for $\varnothing 22,5 mm$ (M 22 x 1.5 mm) with anti-twist device

Life duration up to 50,000 hrs

Nut and seal included in assembly.

## **🛒** ORDER SPECIFICATIONS:

Voltage	24 V =
red	450 100 55
yellow	450 300 55



## **📏** TECHNICAL DIAGRAMS:

see page 243

