## **POSB12150A-WH** series

12V / 1.5A Wall mounted type AC/DC adaptor





• Universal AC input / Full range

ً ∑ ĵ ♥ □ (€

• ErP step II / CEC level VI compliance

• No load power consumption P < 0.075W

• Protections: Overload / Short circuit / Over Voltage

⊖—€—⊕

CONSTANT VOLTAGE

#### **ELECTRICAL SPECIFICATION**

MODEL	POSB 12150A-WH
OUTPUT	
Rated Voltage	12V
Rated Current	1.5A
Current Range	0÷1.5A
Rated Power	18W
Line Regulation	± 1%
Load Regulation	± 2%
Tolerance	± 8%
Ripple & Noise (max.)	120mV <sub>P-P</sub>
Setup, RiseTime	5000ms, 30ms / 230VAC at full load
Hold up Time (typ.)	4ms / 230VAC at full load

111

# INPUTVoltage Range90 ÷ 264VACFrequency Range47 ÷ 63HzEfiiciency (typ.)81,47%AC Current (typ.)0.3A / 230VACNo load Power Consumption (max.)0.075W

PROTECTIONS	
Overload	Range: 105-200%
	Auto-recovery.
Short Circuit	Type: hiccup mode, auto-recovery.
Over Voltage	Type: auto-recovery.

# **POSB12150A-WH** series

12V / 1.5A Wall mounted type AC/DC adaptor



WORKING ENVIRONMENT	
Working Temperature	-10°C ÷ 45°C
Working Humidity	5 ÷ 90% RH non-condensing
Storage Temperature and Humidity	-20°C ÷ 85°C, 5 ÷ 90% RH non-condensing

#### SAFETY and EMC REGULATIONS


Safety Standards	Compliance to EN 60950-1
Withstand Voltage	IN/OUT: 3.6kVAC
Isolation Resistance	IN/OUT: 50MΩ/500VDC/25°C/70%
EMC Emission	Compliance to EN55032
EMC Immunity	Compliance to EN61000-4-2, -3, -4, -5
Harmonic Current	Compliance to EN61000-3-3; EN61000-3-2


#### OTHERS

DC wire and plug	Wire: 20AWG*2C, length = 1200mm	Plug: 2.1/5.5, positive inside
Net Weight / Dimensions	89.3g / 67 x 38 x 74mm (L x W x H)	

Net Weight / Dimensions

**MECHANICAL SPECIFICATION** 






## **POSB12150A-WH** series

12V / 1.5A Wall mounted type AC/DC adaptor

#### MECHANICAL SPECIFICATION: DC wire and plug





1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.

2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1µF i 47µF parallel capacitor.

3. Tolerance includes set up tolerance, line regulation and load regulation.

 Setup and rise time is measured from 0 to 90% rated output voltage.
Setup and rise time is component not indented to apply by end-user. Power supply meets safety and EMC standards however the final equipment with power supply must be re-quality to comply with EMC Directives.