

# SB® 2/0

## SB®175 Sized Connector for 2/0 or 70mm<sup>2</sup> Wire



The SB $^{\circ}$  2/0 is an extension of the SB $^{\circ}$ 175 connector series with more power in the same footprint. The SB $^{\circ}$  2/0 features outer dimensions that are identical to the SB $^{\circ}$ 175, but has been designed to accept only a contact for 2/0 or 70mm<sup>2</sup> wire.


- Silver Plated Wire Contacts for 2/0 or 70mm<sup>2</sup> Wire Allows UL rated currents up to 340 amps
- Low Resistance Connection
  Silver plated power contacts are strongly forced together by stainless
  steel springs
- Same External Dimensions as SB®175

  Use as a drop-in replacement for SB®175 where larger wires are needed

### | ORDERING INFORMATION |

#### SB® 2/0 Housings


Genderless design mates with itself. Can be cross mated with gray SB®175 housing, but amperage capability is limited to the SB®175 rating with the wire and contact used.



#### **Silver Plated Wire Contacts**

Silver plated contacts offer superior electrical performance and durability up to 5,000 mating cycles.

					Dimensions							
					- A	-	- B	-	- C	-	- D	) _
Type	AWG	mm²	- Loose Piece	Part Numbers -	inches	mm	inches	mm	inches	mm	inches	mm
Minimum	Quantity		300	50								
Individua	I 2/0	70	1328G1-BK	1328G1	2.35	59.69	0.64	16.26	0.49	12.45	1.04	26.42



## SPECIFICATIONS |

Electrical						
Current Rating (Amperes) 1	UL 1977	CSA				
2/0 AWG	340	200				
70 mm²	315	185				
Voltage Rating (AC/DC)		600**				
Dielectric Withstanding Voltage (A	Dielectric Withstanding Voltage (AC)					
AVG Contact Resistance (milli-ohr	ms) ¹	0.045				

Materials					
Standard Housing	PC				
Flammability Rating	UL94 V-0				
Wire Power Contact	Copper alloy, silver plate				
Contact Termination Methods					
• Crimp <sup>3</sup>					
Hand Solder					

Mechanical		
Contact Wire Range	(AWG)	2/0
	(mm²)	70
MAX Wire Insulation Diameter	(in)	0.67
	(mm)	17.04
Operating Temperature <sup>2</sup>	°C	°F
PC Housing	-20° to 105°	-4° to 221°
AVG Contact Retention Force	(lbf)	150
for Standard PC Housing	(N)	667
Mating Cycles (no load)		5,000
Connector AVG Connect / Disconnect**	(lbf)	55
	(N)	245










<sup>&</sup>lt;sup>1</sup> Based on: 105°C rated or better cable of the largest size, Properly calibrated APP® recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise.

## | TEMPERATURE CHARTS |







<sup>&</sup>lt;sup>2</sup> Limited by the thermal properties of the connector plastic housing.


<sup>3</sup> Use APP® recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.


## | SB® 2/0 Accessories |

#### **Cable Clamps**


Durable metal cable clamps securely hold cables to prevent accidental strain or pulls from dislodging wire or contacts from the housing. Only Bolt On type clamps can be used with the handles. Cable clamps are recommended for solder terminated wires.

	Max / Min In.	Max / Min mm		
Description	Inches O.D.	mm O.D.	Part Nur	mbers
Minimum Quantity			100	50
Self Attaching for Discrete Conductor	0.55 to 0.24	14 to 6	105G3	945
Bolt On for Discrete Conductor	0.66 to 0.24	16.7 to 6.2	945G3-BK	945G3
Bolt On for Bundled Conductor	0.75 to 0.29	18.3 to 7.3	946G1-BK	946G1






The given wire O.D. information is an estimate. Cable clamps should be evaluated for performance with the actual wire to be used.



#### **Handles**

Handles are made out of durable PC plastic. Hardware to attach to connector body included in kits.

Description	Part Nur	nbers
Minimum Quantity	. 100	25
Gray Handle Kit	995G1-APP	995G1
Red Handle Kit	995G3-APP	995G3
Handle Only, Gray	3-5074P1	-
Handle Only, Red	3-5074P3	-
Handle Only, Black	3-5074P5	-
Hardware Bag	-	105G8



#### **Dust Cover**

Prevents dust and dirt from entering the mating interface of the connector when unmated. NOTE: Not a Hermetic Seal.


Description	Part Nun	nbers
Minimum Quantity	500	50
Dust Cover with Lanyard Strap,	Red 113890P2	134G2



#### SB®175 Lockout

Works with standard lockout - tagout equipment to prevent access to the mating interface of the connector. Made from durable PC plastic.


Description	Part Number
Minimum Quantity	25
Red Lockout - Tagout Kit	SB175-LOCKOUT



#### **Manual Release Bracket - Mounting Side**

Works with the Locking Side to ease mating and unmating connectors.

Description	Part	Numbers	
Minimum Quantity	96	25	10
Bracket and Hardware Kit	-	-	924
Bracket Only	B00333P1	-	-
Hardware Bag	-	105G1	-




#### Manual Release Bracket - Locking Side

Works with the Mounting Side to ease mating and unmating connectors.

	Cable Size		
	Max / Min	Max / Min	
Description	Inches O.D.	mm O.D.	- Part Number -
Minimum Quantity			10
Bracket and Hardware Kit w/ Clamp	0.50 to 0.21	12.6 to 5.4	923

The given wire O.D. information is an estimate. Cable clamps should be evaluated for performance with the actual wire to be used.



## | TOOLING INFORMATION |

Wire Size		Size	Loose Piece Part Numbers	Loose Piece Contact Crimp Tool				
	AWG	mm²	Silver Plating	Hand Tool or	Pneumatic Bench Tool		+ Locator	Number of Crimps
	2/0	53.5	1328G1	1368	1387G2	1303G12	1304G32	Double

NOTE: See website for the most current information.