



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: x.x=±0.4mm  
x.xx=±0.25mm
3. RATING: DC 30V, 0.3A
- ▲ 4. OPERATING FORCE: 300±150gf
5. TRAVEL: 3.5mm TO MAKE  
2.5mm TO LOCK
6. LIFE CYCLES: 10,000 CYCLES
7. OPERATING TEMPERATURE: -20°C TO 80°C
8. CONTACT RESISTANCE: 200mΩ MAX.
9. INSULATION RESISTANCE: 100MΩ MIN.
10. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 11. PLUNGER MATERIAL: NYLON 6/6
- ▲ 12. PLUNGER COLOR: WHITE(NATURAL)

C	15981	ADD DIMENSIONS	4/21/06	CT
B	15819	EDIT PLUNGER LENGTH	2/23/06	PH
A	15750	RELEASE	2/9/06	PH
REV	PCR NO	DESCRIPTION	DATE	BY

**E-SWITCH®**

TITLE LC2255EENP-NYLON 6/6

SCALE	DATE	DR	DWG	REV
3:1	2/9/2006	PH	P070182	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED