


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER RTS 645225	03/MAY/12	ECC	JDM



1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TE CONNECTIVITY STANDARD TEC-138-702.
2. CABLE ASSEMBLY TO BE 100% ELECTRICALLY TESTED FOR OPENS, SHORTS AND CONTINUITY.

HI-HOT: 200 VDC FOR 100ms  
 INSULATION RESISTANCE: 500M OHMS MIN  
 CONTINUITY RESISTANCE: 2 OHMS MAX  
 FREQUENCY RANGE: DC TO 6 GHz  
 VSWR: 1.5:1 MAX

2.0	26.0	2015698-8
2.0	140.0	2015698-5
2.0	50.0	2015698-4
3.0	200.0	2015698-3
2.0	100.0	2015698-2
2.0	39.0	2015698-1
"T" TOLERANCE	"A" LENGTH	TE P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.C. CLAYBAUGH 18/DEC/07	<b>STE</b> TE Connectivity	
DIMENSIONS: mm		CHK J. ORNER 18/DEC/07		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J. ORNER 18/DEC/07	NAME CABLE ASSY, UMCC R/A TO UMCC R/A, TYPE II, 0.80mm CABLE	
0 PLC ± -		PRODUCT SPEC	-	
1 PLC ± -		APPLICATION SPEC	-	
2 PLC ± -		WEIGHT	-	
3 PLC ± -		SIZE	A3	CAGE CODE
4 PLC ± -		DRAWING NO	C-2015698	
ANGLES ± -		RESTRICTED TO	-	
FINISH		SCALE	N.T.S.	
MATERIAL		SHEET	1 OF 1	
-		REV	B	
-		CUSTOMER DRAWING		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2015698-2](#)