

SPECIFICATIONS				
PARAMETERS	VALUES	UNIT		
DIRECTIVITY	OMINI	-		
SENSITIVTY	-42 ± 3	dB		
STANDARD OPERATING VOLTAGE	2	Vdc		
MAX OPERATING VOLTAGE	10	Vdc		
CURRENT CONSUMPTION (MAX)	0.5	mΑ		
IMPEDANCE	2.2	KOhm		
SIGNAL TO NOISE RATIO (MIN.)	58	dB		
TERMINAL	SOLDER PADS	-		
INTERNAL CAPACITOR	33&10	pF		


THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED.

©2003, Projects Unlimited Inc.


REVISION HISTORY					
LTR	DESCRIPTION	DATE	APPROVED		
-	RELEASED FROM ENGINEERING	10/25/2006			
Α	REVISED IP RATING	7/2/2008	B.R.		
В	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	10/25/2010	B.R.		
С	REVISED SIGNAL TO NOISE RATIO	2/19/2020	M.V.		











Date

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2002/95/EC COMPLIANT.
- 4. PART IS IP57 RATED.
- 5. ASSEMBLY IS WASHABLE WITH BOOT IN PLACE.

UNLESS OTHERWISE SPECIFIED:

DIMENSIONS ARE IN MILLIMETERS,

TOLERANCES ARE ±0.5 AND ANGLES ARE ±3°.

POW-2742L-C3310-B-R.idw

J.D.	10/25/2006	R
	pul) _{Inc}

Date

a projects unlimited company

Checked by

Designed by

W. 10/25/2006 B.R. 10/25/2006 10/25/2010 POW-2742L-C3310-B-R

Date

Drawn Date

1/1

Approved by

Microphone -