



SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830
Issue date: 05/05/2020 Revision date: 17/02/2021 Version: 9.1

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : SAPPHIRE Premier

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Industrial use, Professional use
Industrial/Professional use spec : Industrial
For professional use only
Use of the substance/mixture : Lubricants, Greases and Release Products

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

ROCOL a division of ITW Ltd
Rocol House
Wakefield Rd, Swillington
LS26 8BS Leeds - United Kingdom
T +44 (0)113 232 2600
customer.service@rocol.com - www.rocol.com

1.4. Emergency telephone number

Emergency number : +44 (0)113 232 2600

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

No labelling applicable

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

3.2. Mixtures

| Name | Product identifier | % | Classification according to Regulation (EC) No. 1272/2008 [CLP] |
|---|---|---------|---|
| DILITHIUM SEBACATE | (CAS-No.) 19370-86-6 (EC-No.) 242-999-8 (REACH-no) 01-2120119384-60 | 5 – 10 | Acute Tox. 4 (Oral), H302 |
| N-PHENYL-1,1,3,3-TETRAMETHYLBUTYLNAPHTHALEN-1-AMINE | (CAS-No.) 51772-35-1 (EC-No.) 257-406-8 (REACH-no) 01-2119972293-33 | 1 – 2.4 | Aquatic Chronic 4, H413 |

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

| | |
|---------------------------------------|---|
| First-aid measures general | : Never give anything by mouth to an unconscious person. |
| First-aid measures after inhalation | : Allow affected person to breathe fresh air. Allow the victim to rest. |
| First-aid measures after skin contact | : Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse. |
| First-aid measures after eye contact | : Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists. |
| First-aid measures after ingestion | : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention. |

4.2. Most important symptoms and effects, both acute and delayed

| | |
|------------------|--|
| Symptoms/effects | : Not expected to present a significant hazard under anticipated conditions of normal use. |
|------------------|--|

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

| | |
|--------------------------------|--|
| Suitable extinguishing media | : Foam. Dry powder. Carbon dioxide. Water spray. Sand. |
| Unsuitable extinguishing media | : Do not use a heavy water stream. |

5.2. Special hazards arising from the substance or mixture

No additional information available

5.3. Advice for firefighters

| | |
|--------------------------------|---|
| Firefighting instructions | : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment. |
| Protection during firefighting | : Do not enter fire area without proper protective equipment, including respiratory protection. |

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

| | |
|----------------------|-----------------------------------|
| Emergency procedures | : Evacuate unnecessary personnel. |
|----------------------|-----------------------------------|

6.1.2. For emergency responders

| | |
|----------------------|--|
| Protective equipment | : Equip cleanup crew with proper protection. |
| Emergency procedures | : Ventilate area. |

SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : On land, sweep or shovel into suitable containers. Minimise generation of dust.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep only in original container. Keep container closed when not in use.
Incompatible products : Strong bases. Strong acids.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

No additional information available

8.2.2. Personal protection equipment

Personal protective equipment:

Avoid all unnecessary exposure.

8.2.2.1. Eye and face protection

Eye protection:

Chemical goggles or safety glasses

8.2.2.2. Skin protection

SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Hand protection:

Wear protective gloves. Nitrile rubber gloves

8.2.2.3. Respiratory protection

Respiratory protection:

Not required for normal conditions of use

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

| | |
|---|-----------------------|
| Physical state | : Solid |
| Colour | : Pale brown. |
| Odour | : characteristic. |
| Odour threshold | : No data available |
| pH | : No data available |
| Relative evaporation rate (butylacetate=1) | : No data available |
| Melting point | : No data available |
| Freezing point | : No data available |
| Boiling point | : No data available |
| Flash point | : > 200 °C |
| Auto-ignition temperature | : > 200 °C |
| Decomposition temperature | : No data available |
| Flammability (solid, gas) | : Non flammable. |
| Vapour pressure | : No data available |
| Relative vapour density at 20 °C | : No data available |
| Relative density | : ≈ 0.88 |
| Solubility | : insoluble in water. |
| Partition coefficient n-octanol/water (Log Pow) | : No data available |
| Viscosity, kinematic | : No data available |
| Viscosity, dynamic | : No data available |
| Explosive properties | : No data available |
| Oxidising properties | : No data available |
| Explosive limits | : No data available |

9.2. Other information

VOC content : 0 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

Stable under normal conditions of use.

SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

N-PHENYL-1,1,3,3-TETRAMETHYLBUTYLNAPHTHALEN-1-AMINE (51772-35-1)

| | |
|-----------------|---|
| LD50 oral rat | > 2000 mg/kg bodyweight Animal: rat, Animal sex: female, Guideline: OECD Guideline 423 (Acute Oral toxicity - Acute Toxic Class Method), Guideline: EPA OPPTS 870.1100 (Acute Oral Toxicity), Guideline: other:Japan MAFF 8147, Guideline: other:Commission Regulation (EC) No 440/2008 |
| LD50 dermal rat | > 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity), Guideline: EPA OPPTS 870.1200 (Acute Dermal Toxicity), Guideline: other:Commission Regulation (EC) No 440/2008, Guideline: other:Japan MAFF 8147 |

DILITHIUM SEBACATE (19370-86-6)

| | |
|-----------------|------------------|
| LD50 oral rat | 300 – 2000 mg/kg |
| LD50 dermal rat | > 2000 µl/kg |

Skin corrosion/irritation : Not classified
Additional information : Based on available data, the classification criteria are not met
Serious eye damage/irritation : Not classified
Additional information : Based on available data, the classification criteria are not met
Respiratory or skin sensitisation : Not classified
Additional information : Based on available data, the classification criteria are not met
Germ cell mutagenicity : Not classified
Additional information : Based on available data, the classification criteria are not met
Carcinogenicity : Not classified
Additional information : Based on available data, the classification criteria are not met

Reproductive toxicity : Not classified
Additional information : Based on available data, the classification criteria are not met

STOT-single exposure : Not classified
Additional information : Based on available data, the classification criteria are not met

STOT-repeated exposure : Not classified
Additional information : Based on available data, the classification criteria are not met

N-PHENYL-1,1,3,3-TETRAMETHYLBUTYLNAPHTHALEN-1-AMINE (51772-35-1)

| | |
|----------------------------|--|
| NOAEL (oral, rat, 90 days) | 1000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test), Guideline: other:The United States Environmental Protection Agency (EPA) Health Effects Test Guidelines, OPPTS 870.3650, Combined Repeated Dose Toxicity Study with the Reproduction/Developmental Toxicity Screening Test, July 2000. |
|----------------------------|--|

SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

| | |
|---|--|
| Aspiration hazard | : Not classified |
| Additional information | : Based on available data, the classification criteria are not met |
| Potential adverse human health effects and symptoms | : Based on available data, the classification criteria are not met |

SECTION 12: Ecological information

12.1. Toxicity

| | |
|---|------------------|
| Hazardous to the aquatic environment, short-term (acute) | : Not classified |
| Hazardous to the aquatic environment, long-term (chronic) | : Not classified |

| N-PHENYL-1,1,3,3-TETRAMETHYLBUTYLNAPHTHALEN-1-AMINE (51772-35-1) | |
|--|---|
| LC50 - Fish [1] | > 100 mg/l Test organisms (species): Danio rerio (previous name: Brachydanio rerio) |
| EC50 - Crustacea [1] | > 100 mg/l Test organisms (species): Daphnia magna |
| EC50 - Other aquatic organisms [1] | > 100 mg/l |
| EC50 72h - Algae [1] | > 100 mg/l Test organisms (species): Desmodesmus subspicatus (previous name: Scenedesmus subspicatus) |

| DILITHIUM SEBACATE (19370-86-6) | |
|---------------------------------|------------|
| LC50 - Fish [1] | > 100 mg/l |
| EC50 - Crustacea [1] | ≥ 100 mg/l |
| EC50 72h - Algae [1] | 23 mg/l |

12.2. Persistence and degradability

| SAPPHIRE Premier | |
|-------------------------------|------------------|
| Persistence and degradability | Not established. |

12.3. Bioaccumulative potential

| SAPPHIRE Premier | |
|---------------------------|------------------|
| Bioaccumulative potential | Not established. |

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

| | |
|------------------------|-------------------------------------|
| Additional information | : Avoid release to the environment. |
|------------------------|-------------------------------------|

SECTION 13: Disposal considerations

13.1. Waste treatment methods

| | |
|--|---|
| Product/Packaging disposal recommendations | : Dispose in a safe manner in accordance with local/national regulations. |
| Ecology - waste materials | : Avoid release to the environment. |

SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

| ADR | IMDG | IATA | ADN | RID |
|---|---------------|---------------|---------------|---------------|
| 14.1. UN number | | | | |
| Not regulated | Not regulated | Not regulated | Not regulated | Not regulated |
| 14.2. UN proper shipping name | | | | |
| Not regulated | Not regulated | Not regulated | Not regulated | Not regulated |
| 14.3. Transport hazard class(es) | | | | |
| Not regulated | Not regulated | Not regulated | Not regulated | Not regulated |
| 14.4. Packing group | | | | |
| Not regulated | Not regulated | Not regulated | Not regulated | Not regulated |
| 14.5. Environmental hazards | | | | |
| Not regulated | Not regulated | Not regulated | Not regulated | Not regulated |
| No supplementary information available | | | | |

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

VOC content : 0 g/l

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SAPPHIRE Premier

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

| Full text of H- and EUH-statements: | |
|-------------------------------------|---|
| Acute Tox. 4 (Oral) | Acute toxicity (oral), Category 4 |
| Aquatic Chronic 4 | Hazardous to the aquatic environment — Chronic Hazard, Category 4 |
| H302 | Harmful if swallowed. |
| H413 | May cause long lasting harmful effects to aquatic life. |

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.