



Neohm | Neohm CFR

TE Internal #: 3-1623929-4

390 Ω, Carbon Film / Thin Film, General Purpose Resistor, 5 %, 16 x 5.5 mm, 2 Termination, Ammo Packed, 2 W, -450 – 0 ppm/°C, Neohm CFR

[View on TE.com >](#)

Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Passive Component Dimensions: **16 x 5.5 mm**

Number of Terminations: **2**

Packaging Method: **Ammo Packed**

Passive Component Tolerance: **5 %**

Features

Product Type Features

| | |
|---------------|--------------------------|
| Resistor Type | General Purpose Resistor |
| Element Type | Carbon Film, Thin Film |

Configuration Features

| | |
|---------------------|---|
| Number of Resistors | 1 |
|---------------------|---|

Electrical Characteristics

| | |
|-----------------------------|-----------|
| Operating Voltage | 500 V |
| Passive Component Tolerance | 5 % |
| Resistance Class | Up to 1kΩ |
| Resistance Value | 390 Ω |
| Power Rating | 2 W |

Body Features

| | |
|-----------|--------------|
| Lead Type | Axial-Leaded |
|-----------|--------------|

Termination Features

| | |
|--------------------------------|--------|
| Number of Terminations | 2 |
| Termination Area Base Material | Copper |

Dimensions

| | |
|------------------------------|-------------|
| Passive Component Dimensions | 16 x 5.5 mm |
|------------------------------|-------------|

Usage Conditions

| | |
|-----------------------------|-----------------|
| Operating Temperature Range | -55 – 155 °C |
| Temperature Coefficient | -450 – 0 ppm/°C |

Packaging Features

| | |
|------------------|-------------|
| Packaging Method | Ammo Packed |
|------------------|-------------|

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

| | |
|---|--|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2024 (240) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Wave solder capable to 265°C |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1623930-3
CFR25 5% 10K



TE Part # 1623927-8
CFR16 5% 120R



TE Part # 1623932-8
CFR50 5% 10K



TE Part # 1623925-2
CFR100 5% 100R



TE Part # 2-1623929-2
CFR200 5% 22K

Also in the Series | Neohm CFR



[Through-Hole Resistors\(379\)](#)

Customers Also Bought



TE Part #1-1415899-1
RZ01-1C4-D024



TE Part #2-1879022-9
SMF3 4K7 5%



TE Part #3-84984-0
1mm FFC DIP V ASSY 30P TUBE



TE Part #1825006-7
GDS04S04=DIP SW,SLIDE,SMT



TE Part #8-1676481-7
CPF 0603 33K 0.1% 25PPM 1K RL



TE Part #1622853-1
CRG0603 1% 15K



TE Part #1623261-1
CRG0805 1% 5K6



Documents

Product Drawings

[CFR200 5% 390R](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_3-1623929-4_BA.2d_dxf.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_3-1623929-4_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-1623929-4_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Ceramic Film Fixed Resistors - Type CFR Series - Tyco Electronics Passives](#)

English