Miniature Reflective Object Sensor

Features

- Phototransistor Output
- No Contact Surface Sensing
- Miniature Package
- Lead Form Style: Gull Wing
- Two Leadform Options:
 - ◆ Through Hole (QRE1113)
 - SMT Gull Wing (QRE1113GR & QRE1114GR)
- Two Packaging Options:
 - ◆ Tube (QRE1113)
 - Tape and Reel (QRE1113GR & QRE1114GR)

MAXIMUM RATINGS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Value	Unit
T _{OPR}	Operating Temperature	-40 to +85	°C
T _{STG}	Storage Temperature	-40 to +90	°C
T _{SOL-I}	Soldering Temperature (Iron) (Notes 2, 3, 4)	240 for 5 s	°C
T _{SOL-F}	Soldering Temperature (Flow) (Notes 3, 4)	260 for 10 s	°C

EMITTER

I _F	Continuous Forward Current	50	mA
V_{R}	Reverse Voltage	5	V
I _{FP}	Peak Forward Current (Note 5)	1	Α
P_{D}	Power Dissipation (Note 1)	75	mW

SENSOR

V _{CEO}	Collector-Emitter Voltage	30	V
V _{ECO}	V _{ECO} Emitter-Collector Voltage		٧
I _C	Collector Current	20	mA
P_{D}	Power Dissipation (Note 1)	50	mW

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

- 1. Derate power dissipation linearly 1.00 mW/°C above 25°C.
- 2. RMA flux is recommended.
- 3. Methanol or isopropyl alcohols are recommended as cleaning agents.
- 4. Soldering iron 1/16" (1.6 mm) from housing.
- 5. Pulse conditions: tp = 100 μ s; T = 10 ms.


This document, and the information contained herein, is CONFIDENTIAL AND PROPRIETARY and the property of Semiconductor Components Industries, LLC., dba ON Semiconductor. It shall not be used, published, disclosed or disseminated outside of the Company, in whole or in part, without the written permission of ON Semiconductor. Reverse engineering of any or all of the information contained herein is strictly prohibited.

© 2020, SCILLC. All Rights Reserved.



ON Semiconductor®


www.onsemi.com



Pin 1: Anode Pin 2: Cathode Pin 3: Collector Pin 4: Emitter



REFLECTIVE RECTANGULAR SURFACE MOUNT CASE 100CY



REFLECTIVE RECTANGULAR THROUGH HOLE CASE 100AQ

ORDERING INFORMATION

Device	Package	Shipping [†]
QRE1113	Reflective Rectangular (Through Hole)	1600 / Tube
QRE1113GR & QRE1114GR	Reflective Rectangular (Surface Mount)	1000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

ELECTRICAL/OPTICAL CHARACTERISTICS (T_A = 25°C unless otherwise noted)

Symbol	Parameter	Conditions			Тур	Max	Unit
INPUT DIO	DE			•		•	•
V _F	Forward Voltage	I _F = 20 mA			1.2	1.6	V
I _R	Reverse Leakage Current	V _R = 5 V				10	μΑ
λ _{PE}	Peak Emission Wavelength	I _F = 20 mA			940		nm
OUTPUT T	RANSISTOR						
Ι _D	Collector-Emitter Dark Current	$I_F = 0 \text{ mA}, V_{CE} = 20 \text{ V}$				100	nA
COUPLED				•		•	•
I _{C(ON)} On-State Collector		I _F = 20 mA, V _{CE} = 5 V QRE1113 & QRE1113GF QRE1114GR	QRE1113 & QRE1113GR	0.10	0.90		mA
	Current		QRE1114GR	0.30		0.60	mA
I _{CX}	Cross-Talk Collector Current	I _F = 20 mA, V _{CE} = 5 V (Note 7)				1	μΑ
V _{CE(SAT)}	Saturation Voltage	$I_F = 20 \text{ mA}, I_C = 50 \mu A \text{ (Note 6)}$				0.3	٧
t _r	Rise Time	V_{CC} = 5 V, $I_{C(ON)}$ = 100 μ A, R_L = 1 $k\Omega$			20		μs
t _f	Fall Time				20		μs

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

6. Measured using an aluminum alloy mirror at d = 1 mm.

- 7. No reflective surface at close proximity.

REFLOW PROFILE




Figure 1. Reflow Profile

TYPICAL PERFORMANCE CURVES




Figure 2. Normalized Collector Current vs. Distance between Device and Reflector




Figure 4. Normalized Collector Current vs. Collector to Emitter Voltage




Figure 3. Collector Current vs. Forward Current




Figure 5. Collector Emitter Dark Current (Normalized) vs. Ambient Temperature

TYPICAL PERFORMANCE CURVES (Continued)




Figure 6. Forward Current vs. Forward Voltage




Figure 7. Rise and Fall Time vs. Load Resistance




Figure 8. Forward Voltage vs. Ambient Temperature




Figure 9. Radiation Diagram

TAPING DIMENSIONS FOR GR OPTION




Figure 10. Taping Dimensions for GR Option

REEL DIMENSIONS




Figure 11. Reel Dimensions


Precautionary Notes


- 1. Refer to application note AND8003/D, "Storage and Handling of Dry Packed Surface Mounted Devices" for details of handling procedure.
- 2. Product soldering terminals are silver plated and oxidization may occur with prolonged exposure to ambient environment. Oxidized terminal may have poor solderability performance. Keep unsealed devices in moisture barrier bag sealed with desiccant or in dry cabinet at <5% relative humidity.
- Store PCB in sealed moisture barrier bag together with desiccant or store in dry cabinet at <5% relative humidity. Mounted device that has been exposed to ambient environment for long period of time may suffer moisture related damage if PCB is subjected to subsequent high temperature processes.



REFLECTIVE RECTANGULAR THROUGH HOLE CASE 100AQ ISSUE O

DATE 30 SEP 2016





Notes:


- 1. Dimensions for all drawings are in millimeters.
- 2. Tolerance of ±0.15mm on all non-nominal dimensions


DOCUMENT NUMBER:	98AON13409G	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	REFLECTIVE RECTANGULAR THROUGH HOLE		PAGE 1 OF 1

ON Semiconductor and III are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

ARUSM-313 / REFLECTIVE RECTANGULAR SURFACE MOUNT CASE 100CY ISSUE O

DATE 31 JAN 2017





A. NO INDUSTRY STANDARD APPLIES
TO THIS PACKAGE

B. ALL DIMENSIONS ARE IN MILLIMETERS
C. TOLERANCE OF ±0.15MM ON ALL
NON-NOMINAL DIMENSIONS

DOCUMENT NUMBER:	Printed versions are uncontrolled except when accessed directly from the Document Reposition Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	ARUSM-313 / REFLECTIVE RECTANGULAR SURFACE MOUNT PAGE		PAGE 1 OF 1

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer pu

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi

QRE1113GR QRE11113 QRE1114GR