




FINISHED LENGTH (SEE TABLE)



CONNECTOR SPECIFICATION:

VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	max. 4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C

ITEM	COMPONENT	MATERIAL	FINISH
6	LABLE	MYLAR	BLACK/YELLOW
5	COUPLER	BRASS	NICKEL PLATED
4	PIN CONTACT	COPPER ALLOY	GOLD OVER NICKEL
3	INSERT	PUR	BLACK
2	OVERMOLD	POLYURETHANE (PUR)	YELLOW
1	CABLE- 22/3-5 (COPPER STRANDING) 3/4/5 CONDUCT. 300V	JACKET: PUR	BLACK




DESCRIPTION EC NO.: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHK'D: NS APPR: NSTAUDIG 2010/01/26	QUALITY SYMBOLS ▽ = 0 ▽ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
		4 PLACES ±--- ±---	3 PLACES ±--- ±---	2 PLACES ±--- ±.01	1 PLACE ±0.3 ±---	DRAWN BY: _____ DATE: _____ CHECKED BY: _____ DATE: 2010/01/21		MICRO-CHANGE CORDSET 3/4/5-P. M 90 SE 22/3-5 BLACK PUR CABLE		
		ANGULAR ± --- °				APPROVED BY: _____ DATE: 2010/01/25 NSTAUDIG				
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				SEE TABLE SHEET 2		MATERIAL NO.	DOCUMENT NO. SD-120065-045	SHEET NO. 1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
3	1200060288	803007P03M020	6.56' +3.5" -0 [2.0M +89 -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
4	1200060592	804007P03M020	6.56' +3.5" -0 [2.0M +89 -0]
4	1200652145	804007P03M040	13.12' +6.5" -0 [4.0M +165 -0]
4	1200060594	804007P03M050	16.40' +6.5" -0 [5.0M +165 -0]
4	1200652146	804007P03M060	19.69' +6.5" -0 [6.0M +165 -0]
4	1200060595	804007P03M100	32.81' +12.5" -0 [10.0M +318 -0]

POL	MATERIAL NUMBER	ENGINEERING NUMBER	FINISHED LENGTH
5	1200060697	805007P03M020	6.56' +3.5" -0 [2.0M +89 -0]
5	1200060699	805007P03M040	13.12' +6.5" -0 [4.0M +165 -0]
5	1200658186	805007P03M050	16.40' +6.5" -0 [5.0M +165 -0]
5	1200652149	805007P03M060	19.69' +6.5" -0 [6.0M +165 -0]
5	1200655006	805007P03M100	32.81' +12.5" -0 [10.0M +318 -0]

DESCRIPTION EC NO: WEU2010-0284 DRWN: LSTEMMLE 2010/01/20 CHKD: NS APPR: NSTAUDIG 2010/01/26 REV 1	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION																		
	$\nabla = 0$ $\nabla \text{C} = 0$	<table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>±---</td> <td>±---</td> </tr> <tr> <td>3 PLACES</td> <td>±---</td> <td>±---</td> </tr> <tr> <td>2 PLACES</td> <td>±---</td> <td>±.01</td> </tr> <tr> <td>1 PLACE</td> <td>±0.3</td> <td>±---</td> </tr> <tr> <td colspan="3">ANGULAR ± --- °</td> </tr> </table>		mm	INCH	4 PLACES	±---	±---	3 PLACES	±---	±---	2 PLACES	±---	±.01	1 PLACE	±0.3	±---	ANGULAR ± --- °			IN/MM	2:1	METRIC	
		mm	INCH																					
	4 PLACES	±---	±---																					
	3 PLACES	±---	±---																					
2 PLACES	±---	±.01																						
1 PLACE	±0.3	±---																						
ANGULAR ± --- °																								
			DRAWN BY	DATE	MICRO-CHANGE CORDSET 3/4/5-P. M 90 SE 22/3-5 BLACK PUR CABLE																			
			RE	2010/01/21																				
			APPROVED BY	DATE	 <b>MOLEX INCORPORATED</b>																			
			NSTAUDIG	2010/01/25																				
			MATERIAL NO.	SEE TABLE	DOCUMENT NO.	SHEET NO.																		
			SIZE	A3	SD-120065-045	1 OF 1																		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	